



A CSW Industrials Company

SAFETY DATA SHEET

PYROSEAL™

Furnace and retort cement

SECTION 1 - PRODUCT AND COMPANY INFORMATION

Product name
Pyroseal

Product Codes
68616, 68618

Chemical Family
Inorganic

Use
Dual purpose retort and furnace cement

Manufacturer's Name
RectorSeal LLC
2601 Spenwick Drive
Houston, Texas 77055 USA

Date of validation
July 27, 2021

Date of Preparation
July 27, 2021

HMIS Codes
Health 1
Flammability 0
Reactivity 0
PPI B

Emergency Telephone No.
Chemtrec 24 Hours
(800) 424-9300 USA
(703) 527-3887 International

Technical Service Telephone No.
(800) 231-3345 or (713) 263-8001

SECTION 2 - HAZARDS IDENTIFICATION

GHS Classification

Physical Hazards
None

HEALTH HAZARDS

Acute Toxicity

Oral: Not Classified
Dermal: Not Classified
Inhalation: Not Classified
Skin Corrosion/Irritation: Category 2
Serious Eye Damage/Eye Irritation: Category 2A
Respiratory or Skin Sensitization: Not Classified

Germ Cell Mutagenicity: Not Classified
Carcinogenicity: Not Classified
Reproductive Toxicology: Not Classified
Target Organ Systemic Toxicity - Single Exposure: Not Classified
Target Organ Systemic Toxicity - Repeated Exposure: Not Classified
Aspiration Toxicity: Not Classified Aspiration Toxicity: Not Classified

GHS Label elements, including precautionary statements



GHS07: Exclamation Mark
Signal Word: WARNING

Hazard Statements:

H315 - Causes skin irritation.
H318 - Causes serious eye damage.

Precautionary Statements:

P102 - Keep out of reach of children.
P262 - Do not get in eyes, on skin, or on clothing.
P264 - Wash hands thoroughly after handling.
P280 - Wear protective gloves/protective clothing/eye protection/face protection.

Response:

P303 + P351 + P353 - IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower.
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove easy to do. Continue rinsing
P337+P313 - If eye irritation persists get medical advice/attention
P332+P313 - If skin irritation occurs: Get medical advice/attention.
P362+P364 - Take off contaminated clothing and wash it before reuse.

Storage:

There are no precautionary storage phrases assigned.

Disposal:

P501 - Dispose of contents/container in accordance with local/regional/national/international regulations.

SUMMARY OF ACUTE HAZARDS

Exposure from dust may cause eye and respiratory irritation.

ROUTE OF EXPOSURE, SIGNS AND SYMPTOMS

INHALATION - May cause respiratory irritation.

EYE CONTACT - Contact may cause eye irritation.

SKIN CONTACT - Contact may cause skin irritation.

INGESTION - Possible irritation to mucous membranes of the mouth, throat, and stomach.

SUMMARY OF CHRONIC HAZARDS - NONE KNOWN.

MEDICAL CONDITIONS AGGRAVATED BY EXPOSURE - Persons with impaired pulmonary function and/or pre-existing eye or skin conditions may be more susceptible to the effects of this product.

SECTION 3 - COMPOSITION/INFORMATION ON INGREDIENTS

Ingredient:	Sodium Silicate
Percentage By Weight:	15.77
CAS Number:	1344-09-8
EINEC:	229-912-9
Ingredient:	Calcium Magnesium Silicate
Percentage By Weight:	25.42
CAS Number:	13983-17-0
EINECS:	237-772-5

SECTION 4 - FIRST AID MEASURES

IF INHALED:	Remove to fresh air. Administer oxygen or artificial respiration if needed. Seek immediate medical attention.
IF ON SKIN:	Wash with soap and water. If irritation occurs, seek medical attention.
IF IN EYES:	Immediately flush with large amounts of water. If irritation occurs, seek medical attention.
IF SWALLOWED:	If swallowed, call a physician immediately. Only induce vomiting at the instruction of a physician. Never give anything by mouth to an unconscious person.

SECTION 5 - FIRE FIGHTING MEASURES

Extinguishing media

Foam, dry chemical, carbon dioxide or water fog.

Special fire fighting procedures

Wear self-contained breathing apparatus (SCBA) and other protective clothing.

Unusual fire and explosion hazards

None known.

SECTION 6 - ACCIDENTAL RELEASE MEASURES

Steps to be taken in case material is released or spilled:

Wipe up spills to prevent footing hazard. Avoid flushing into sewers, drains, waterways and soil. Wear protective clothing during clean up.

SECTION 7 - HANDLING AND STORAGE

Precautions to be taken in handling and storing:

Keep container closed and upright when not in use.

Other precautions:

Avoid prolonged or repeated contact with skin or clothing.

KEEP OUT OF REACH OF CHILDREN.

SECTION 8 - EXPOSURE CONTROLS/PERSONAL PROTECTION

Ingredient	Units
------------	-------

Sodium Silicate

ACGIH TLV	N/D
-----------	-----

OSHA PEL	N/D
----------	-----

Calcium Magnesium Silicate

ACGIH TLV	N/D
-----------	-----

OSHA PEL	N/D
----------	-----

RESPIRATORY PROTECTION (SPECIFY TYPE): NIOSH/MSHA approved dust mask.

VENTILATION - LOCAL EXHAUST: Acceptable

SPECIAL: N/A

MECHANICAL (GENERAL): Preferable

OTHER: N/A

PROTECTIVE GLOVES: Wear rubber gloves.

EYE PROTECTION: Safety glasses (ANSI Z-87.1 or equivalent)

OTHER PROTECTIVE CLOTHING OR EQUIPMENT: Coveralls recommended.

WORK/HYGIENIC PRACTICES: Where use can result in skin contact, wash exposed areas thoroughly before eating, drinking, smoking, or leaving work area. Launder contaminated clothing before reuse.

SECTION 9 - PHYSICAL AND CHEMICAL PROPERTIES

BOILING POINT:	N/A
SPECIFIC GRAVITY (H2O = 1):	1.439
VAPOR PRESSURE (MMHG):	NA
MELTING POINT:	N/A
VAPOR DENSITY (AIR = 1):	N/A
EVAPORATION RATE (ETHYL ACETATE = 1):	N/A
APPEARANCE/ODOR:	Gray/No odor
SOLUBILITY IN WATER:	Insoluble
VOLATILE ORGANIC COMPOUNDS (VOC) CONTENT (THEORETICAL PERCENTAGE BY WEIGHT):	0% or (0 g/L)
FLASH POINT:	None
LOWER EXPLOSION LIMIT:	N/D
UPPER EXPLOSION LIMIT:	N/D

SECTION 10 - STABILITY AND REACTIVITY

Stability:

Stable

Conditions to avoid:

None known.

Incompatibility (materials to avoid):

None known.

Hazardous decomposition products:

None Known.

Hazardous polymerization:

Will not occur.

SECTION 11 - TOXICOLOGY INFORMATION

Chronical Health Hazards:

No ingredient in this product is an IARC, NTP or OSHA Lister carcinogen.

Toxicology Data:

Ingredient name

Sodium Silicate

Oral-Rat LD50: 2000-3000 mg/kg

Inhalation-Rat LC50: N/D

Calcium Magnesium Silicate

Oral-Rat LD50: N/D

Inhalation-Rat LC50: N/D

SECTION 12 - ECOLOGICAL INFORMATION

Ecology Data:

Ingredient name

Sodium Silicate

Food Chain Concentration Potential N/D

Waterfowl Toxicity N/D

BOD N/D

Aquatic Toxicity N/D

Calcium Magnesium Silicate

Food Chain Concentration Potential N/D

Waterfowl Toxicity N/D

BOD N/D

Aquatic Toxicity N/D

SECTION 13 - DISPOSAL CONSIDERATIONS

Waste Classification: Non-regulated liquid waste

Disposal Method: Approve landfill

Waste from this product is not considered hazardous as defined under the Resource Conservation and Recovery Act (RCRA) 40 CFR 261. Dispose of in accordance with Federal, State, and Local regulation regarding pollution.

SECTION 14 - TRANSPORTATION INFORMATION

DOT:	Non-Regulated
OCEAN (IMDG):	Non-Regulated
AIR (IATA):	Non-Regulated
WHMIS (CANADA):	Non-Regulated

SECTION 15 - REGULATORY INFORMATION

Regulatory Data

Ingredient	Sodium Silicate
SARA 313	No
TSCA Inventory	Yes
CERCLA RQ	N/A
RCRA Code	N/A
Ingredient	Calcium Magnesium Silicate
SARA 313	No
TSCA Inventory	Yes
CERCLA RQ	N/A
RCRA Code	N/A

SECTION 16 - OTHER INFORMATION

This document is prepared pursuant to the OSHA Hazard Communication Standard (29 CFR 1910.1200). The information herein is given in good faith, but no warranty, expressed or implied is made. Consult RectorSeal for further information: (713) 263-8001