



SAFETY DATA SHEET

1. Identification

Product identifier Diesel 1-Tank Power Renew®

Other means of identification

Product Code No. 05832 (Item# 1003867)

Recommended use Diesel fuel additive

Recommended restrictions None known.

Manufacturer/Importer/Supplier/Distributor information

Manufactured or sold by:

Company name CRC Industries, Inc.

Address 885 Louis Dr.
Warminster, PA 18974 US

Telephone

General Information 215-674-4300

Technical Assistance 800-521-3168

Customer Service 800-272-4620

24-Hour Emergency 800-424-9300 (US)

(CHEMTREC) 703-527-3887 (International)

Website www.crcindustries.com

2. Hazard(s) identification

Physical hazards Flammable liquids Category 4

Health hazards Acute toxicity, inhalation Category 4

Skin corrosion/irritation Category 2

Serious eye damage/eye irritation Category 2A

Aspiration hazard Category 1

Environmental hazards Hazardous to the aquatic environment, acute hazard Category 2

Hazardous to the aquatic environment, long-term hazard Category 2

OSHA defined hazards Not classified.

Label elements



Signal word Danger

Hazard statement Combustible liquid. May be fatal if swallowed and enters airways. Causes skin irritation. Causes serious eye irritation. Harmful if inhaled. Toxic to aquatic life. Toxic to aquatic life with long lasting effects.

Precautionary statement

Prevention Keep away from flames and hot surfaces-No smoking. Use with adequate ventilation. Open doors and windows or use other means to ensure a fresh air supply during use and while product is drying. If you experience any symptoms listed on this label, increase ventilation or leave the area. Avoid breathing vapors. Wash thoroughly after handling. Wear protective gloves/eye protection/face protection. Avoid release to the environment.

Response	If swallowed: Immediately call a poison center/doctor. Do NOT induce vomiting. If on skin: Wash with plenty of water. If skin irritation occurs: Get medical advice/attention. Take off contaminated clothing and wash before reuse. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center/doctor if you feel unwell. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. In case of fire: Do not use water jet as an extinguisher, as this will spread the fire. Collect spillage.
Storage	Store in a well-ventilated place. Keep cool. Store locked up.
Disposal	Dispose of contents/container in accordance with local/regional/national regulations.
Hazard(s) not otherwise classified (HNOC)	None known.
Supplemental information	None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
2-ethylhexyl nitrate		27247-96-7	40 - 50
naphtha (petroleum), hydrotreated heavy		64742-48-9	10 - 20
2-ethylhexanol		104-76-7	5 - 10
distillates (petroleum), hydrotreated heavy paraffinic		64742-54-7	1 - 3
oleic acid		112-80-1	1 - 3

Specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Oxygen or artificial respiration if needed. Call a POISON CENTER or doctor/physician if you feel unwell.
Skin contact	Remove contaminated clothing. Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention. Wash contaminated clothing before reuse.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention if irritation develops and persists.
Ingestion	Call a physician or poison control center immediately. Rinse mouth. Do not induce vomiting. If vomiting occurs, keep head low so that stomach content doesn't get into the lungs.
Most important symptoms/effects, acute and delayed	Aspiration may cause pulmonary edema and pneumonitis. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause redness and pain.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim warm. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Water fog. Alcohol resistant foam. Dry chemical powder. Carbon dioxide (CO2).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	The product is combustible, and heating may generate vapors which may form explosive vapor/air mixtures. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.
Fire-fighting equipment/instructions	In case of fire and/or explosion do not breathe fumes. Move containers from fire area if you can do so without risk. Use standard firefighting procedures and consider the hazards of other involved materials.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.
General fire hazards	Combustible liquid.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Wear appropriate protective equipment and clothing during clean-up. Avoid inhalation of vapors. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.

Methods and materials for containment and cleaning up

Use water spray to reduce vapors or divert vapor cloud drift. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. The product is immiscible with water and will spread on the water surface. Prevent product from entering drains.

Small Spills: Absorb with earth, sand or other non-combustible material and transfer to containers for later disposal. Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.

Environmental precautions

Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling

Keep away from open flames, hot surfaces and sources of ignition. When using do not smoke. Avoid breathing vapors. Avoid contact with eyes, skin, and clothing. Avoid prolonged exposure. Use only outdoors or in a well-ventilated area. Wear appropriate personal protective equipment. Wash hands thoroughly after handling. Avoid release to the environment. Observe good industrial hygiene practices. For product usage instructions, see the product label.

Conditions for safe storage, including any incompatibilities

Keep away from heat, sparks and open flame. Store in a cool, dry place out of direct sunlight. Keep container tightly closed. Store in a well-ventilated place. Keep in an area equipped with sprinklers. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

U.S. - OSHA Components

Components	Type	Value
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	TWA	5 mg/m ³

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value	Form
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	PEL	5 mg/m ³	Mist.
naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)	PEL	400 mg/m ³	
		100 ppm	

ACGIH

Components	Type	Value	Form
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	TWA	5 mg/m ³	Inhalable fraction

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	TWA	5 mg/m ³	Inhalable fraction.

U.S. - NIOSH**Components**

distillates (petroleum),
hydrotreated heavy
paraffinic (CAS 64742-54-7)

Type

STEL

Value

10 mg/m3

Form

Mist

TWA

5 mg/m3

Mist

US. NIOSH: Pocket Guide to Chemical Hazards**Components**

distillates (petroleum),
hydrotreated heavy
paraffinic (CAS 64742-54-7)

STEL

10 mg/m3

Mist.

TWA

5 mg/m3

Mist.

naphtha (petroleum),
hydrotreated heavy (CAS
64742-48-9)

TWA

400 mg/m3

100 ppm

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Eye wash facilities and emergency shower should be available when handling this product.

Individual protection measures, such as personal protective equipment**Eye/face protection**

Wear safety glasses with side shields (or goggles).

Skin protection**Hand protection**

Wear protective gloves such as: Nitrile. Neoprene.

Other

Wear appropriate chemical resistant clothing.

Respiratory protection

If engineering controls are not feasible or if exposure exceeds the applicable exposure limits, use a NIOSH-approved cartridge respirator with an organic vapor cartridge. Use a self-contained breathing apparatus in confined spaces and for emergencies. Air monitoring is needed to determine actual employee exposure levels.

Thermal hazards

Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties**Appearance****Physical state**

Liquid.

Form

Liquid.

Color

Dark brown.

Odor

Mild petroleum.

Odor threshold

Not available.

pH

Not available.

Melting point/freezing point

-104.8 °F (-76 °C) estimated

Initial boiling point and boiling range

546.8 °F (286 °C) estimated

Flash point

152 °F (66.7 °C) Setaflash

Evaporation rate

Slow.

Flammability (solid, gas)

Not available.

Upper/lower flammability or explosive limits**Flammability limit - lower (%)**

Not available.

Flammability limit - upper (%)

Not available.

Vapor pressure

0.5 hPa estimated

Vapor density	> 1 (air = 1)
Relative density	0.92
Solubility(ies)	
Solubility (water)	Insoluble.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	419 °F (215 °C) estimated
Decomposition temperature	Not available.
Percent volatile	95 % estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Avoid heat, sparks, open flames and other ignition sources. Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	Carbon oxides. Nitrogen oxides (NOx).

11. Toxicological information

Information on likely routes of exposure

Inhalation	Harmful if inhaled.
Skin contact	Causes skin irritation.
Eye contact	Causes serious eye irritation.
Ingestion	Droplets of the product aspirated into the lungs through ingestion or vomiting may cause a serious chemical pneumonia.

Symptoms related to the physical, chemical and toxicological characteristics	Aspiration may cause pulmonary edema and pneumonitis. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause redness and pain.
---	--

Information on toxicological effects

Acute toxicity	May be fatal if swallowed and enters airways. Harmful if inhaled.
-----------------------	---

Components	Species	Test Results
2-ethylhexanol (CAS 104-76-7)		
<u>Acute</u>		
Dermal		
LD50	Rabbit	1986 mg/kg
Oral		
LD50	Rat	2053 mg/kg
2-ethylhexyl nitrate (CAS 27247-96-7)		
<u>Acute</u>		
Inhalation		
LC50	Rat	10 - 20 mg/l, 4 hours
naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)		
<u>Acute</u>		
Dermal		
LD50	Rabbit	> 2000 mg/kg
Skin corrosion/irritation	Causes skin irritation.	
Serious eye damage/eye irritation	Causes serious eye irritation.	
Respiratory or skin sensitization		
Respiratory sensitization	Not a respiratory sensitizer.	

Skin sensitization	This product is not expected to cause skin sensitization.
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.
Carcinogenicity	Not classifiable as to carcinogenicity to humans.
IARC Monographs. Overall Evaluation of Carcinogenicity	
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)	3 Not classifiable as to carcinogenicity to humans.
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)	
Not regulated.	
US. National Toxicology Program (NTP) Report on Carcinogens	
Not listed.	
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.
Specific target organ toxicity - single exposure	Not classified.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	May be fatal if swallowed and enters airways.
Chronic effects	Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity	Toxic to aquatic life with long lasting effects.		
Components	Species		Test Results
2-ethylhexanol (CAS 104-76-7)			
Aquatic			
Fish	LC50	Bluegill (Lepomis macrochirus)	10 - 33 mg/l, 96 hours
Acute			
Crustacea	EC50	Water flea (Daphnia magna)	39 mg/l, 48 hours
2-ethylhexyl nitrate (CAS 27247-96-7)			
Aquatic			
Acute			
Fish	LC50	Bluegill (Lepomis macrochirus)	4.5 mg/l, 96 hours
distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)			
Aquatic			
Acute			
Crustacea	EC50	Water flea (Daphnia magna)	> 10000 mg/l, 48 hours
Fish	LC50	Fathead minnow (Pimephales promelas)	> 100 mg/l, 96 hours
naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)			
Aquatic			
Crustacea	EC50	Water flea (Daphnia pulex)	2.7 - 5.1 mg/l, 48 hours
Fish	LC50	Rainbow trout,donaldson trout (Oncorhynchus mykiss)	8.8 mg/l, 96 hours
			8.8 mg/l, 96 hours
oleic acid (CAS 112-80-1)			
Aquatic			
Acute			
Fish	LC50	Rainbow trout,donaldson trout (Oncorhynchus mykiss)	56 mg/l, 96 hours
Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.		
Bioaccumulative potential			
Mobility in soil	No data available.		
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.		

13. Disposal considerations

Hazardous waste code	Not regulated.
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.
Disposal instructions	This product is not a RCRA hazardous waste (See 40 CFR Part 261.20 – 261.33). Empty containers may be recycled. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose in accordance with all applicable regulations.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1052)

Not regulated.

US EPCRA (SARA Title III) Section 313 - Toxic Chemical: Listed substance

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

CERCLA Hazardous Substances: Reportable quantity

Not listed.

Spills or releases resulting in the loss of any ingredient at or above its RQ require immediate notification to the National Response Center (800-424-8802) and to your Local Emergency Planning Committee.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA) Not regulated.

Food and Drug Administration (FDA) Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

Not listed.

SARA 313 (TRI reporting)

Not regulated.

US state regulations

US. New Jersey Worker and Community Right-to-Know Act

naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)

US. Massachusetts RTK - Substance List

2-ethylhexanol (CAS 104-76-7)

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)

naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)

US. Pennsylvania Worker and Community Right-to-Know Law

2-ethylhexanol (CAS 104-76-7)

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)

oleic acid (CAS 112-80-1)

US. Rhode Island RTK

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)

naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)

oleic acid (CAS 112-80-1)

California Proposition 65



WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

California Proposition 65 - CRT: Listed date/Carcinogenic substance

ethylene oxide (CAS 75-21-8)

Listed: July 1, 1987

propylene oxide (CAS 75-56-9)

Listed: October 1, 1988

California Proposition 65 - CRT: Listed date/Developmental toxin

ethylene oxide (CAS 75-21-8)

Listed: August 7, 2009

methanol (CAS 67-56-1)

Listed: March 16, 2012

California Proposition 65 - CRT: Listed date/Female reproductive toxin

ethylene oxide (CAS 75-21-8)

Listed: February 27, 1987

California Proposition 65 - CRT: Listed date/Male reproductive toxin

ethylene oxide (CAS 75-21-8)

Listed: August 7, 2009

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

distillates (petroleum), hydrotreated heavy paraffinic (CAS 64742-54-7)

naphtha (petroleum), hydrotreated heavy (CAS 64742-48-9)

Volatile organic compounds (VOC) regulations

EPA

VOC content (40 CFR 100 %

51.100(s))

Consumer products Not regulated

(40 CFR 59, Subpt. C)

State

Consumer products Not regulated

VOC content (CA) 95 %

VOC content (OTC) 95 %

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	No
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	No
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Toxic Chemical Substances (TCS)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	05-26-2015
Revision date	04-11-2018
Prepared by	Allison Yoon
Version #	03
Further information	CRC # 908E/1002899
Disclaimer	The information contained in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. This information is accurate to the best of CRC's knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. For further clarification of any information contained on this (M)SDS consult your supervisor, a health & safety professional, or CRC Industries, Inc..
Revision information	This document has undergone significant changes and should be reviewed in its entirety.