### **SAFETY DATA SHEET**

# SECTION 1 – PRODUCT AND COMPANY IDENTIFICATION

Product Identifier : Henry® 345 Premixed Patch n' Level

Product ID No. : 70012012 Trade Name/Synonyms : Henry 345

Material Use : Floor Patch and Smoothing Compound.

Uses Advised Against : Use only as recommended in the product's Technical Data Sheet.

Manufacturer's name and address:

ARDEX L P

400 Ardex Park Drive

Aliquippa, PA 15001 USA

Information Telephone No. : (724) 203-8000

Website Address : <a href="http://www.ardexamericas.com">http://www.ardexamericas.com</a>

24 Hr Emergency Telephone # : CHEM-TEL: 1-800-255-3924 OR 1-813-248-0585 (call collect)

# **SECTION 2 – HAZARDS IDENTIFICATION**

## GHS Classification per 29 CFR 1910.1200 (OSHA HCS 2012) and HPR (WHMIS 2015)

Skin corrosion/irritation, Category 2 (Irritant)

Serious eye damage/eye irritation, Category 2B (Irritant).

Carcinogenicity, Category 2

**GHS Pictograms** 



Signal Word

Warning.

**Hazard Statements** 

Suspected of causing cancer.

Causes skin irritation. Causes eye irritation.

**Precautionary Statements** 

Do not handle until all safety precautions have been read and understood. Wear protective gloves/protective clothing/eye protection. Wash hands and exposed skin thoroughly after handling. Do not subject to grinding. Store locked up. Dispose of contents / container in accordance with federal, state,

and local laws. Do not allow product to enter drains.

During normal usage of the product as recommended, airborne dusts and mists will not be present. See Section 7 (Handling and Storage) for further details.

**Hazards Not Otherwise Classified** 

None

% With Unknown Acute Toxicity: Up to 80% by weight of this product is comprised of ingredients with unknown

acute toxicity.

# **SECTION 3 – COMPOSITION/INFORMATION ON INGREDIENTS**

Ingredients	CAS#	% (by weight)
Crystalline silica	14808-60-7	60. – 100.
2-Butoxyethanol	111-76-2	0.10 - 1.00

The exact percentages of the ingredients have been withheld by the manufacturer as trade secrets.

## **SECTION 4 – FIRST AID MEASURES**

General : Call a doctor if you feel unwell.

Inhalation : If breathing problems occur, move person to fresh air and keep at rest in a position

comfortable for breathing. If breathing difficulties persist, seek immediate medical

attention/advice.

**Skin contact** : Wash with plenty of soap and water. If irritations or symptoms develop, seek

medical attention/advice.

Eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present

and easy to do. Continue rinsing. Get medical advice/attention.

Ingestion : Rinse mouth. Do NOT induce vomiting. Call a doctor/physician if you feel unwell.

Notes for Physician : Treat symptomatically.

#### Signs and symptoms of short-term (acute) exposure

Inhalation : May cause minor, temporary irritation to respiratory tract. Symptoms may include

coughing and shortness of breath.

Skin : May cause skin irritation. Symptoms may include redness and itching.

Eyes : Causes irritation to eyes. Symptoms may include redness, itching, blurred vision or pain.

Ingestion : Symptoms such as gastric pain, nausea, vomiting, and diarrhea may occur.

#### Effects of long-term (chronic) exposure

Prolonged inhalation may cause adverse lung effects with symptoms including coughing

and shortness of breath.

### Indication of need for immediate medical attention or special treatment

: Difficulty breathing persists after removing the person to fresh air.

Any exposure to the eye which causes irritation.

Ingestion.

## **SECTION 5 – FIRE FIGHTING MEASURES**

Suitable extinguishing media

: Carbon dioxide, dry chemical powder, water, appropriate foam or water fog.

Unsuitable extinguishing media

: None known.

**Hazardous combustion products** 

Carbon monoxide, carbon dioxide, and other toxic vapors and gases which are

common to thermal degradation of organic compounds.

### Special fire-fighting procedures/equipment

: Firefighters should wear proper protective equipment and self-contained breathing apparatus with full face piece operated in positive pressure mode. Move containers from fire area if safe to do so. Water spray may be useful in cooling equipment exposed to heat and flame. After fires have been extinguished, carefully clean all

equipment and surfaces exposed to fumes.

**Environmental precautions** : Do not allow material to enter drains or contaminate ground water system.

#### Fire hazards/conditions of flammability

: Not flammable under normal conditions of use. Closed containers may rupture if exposed to excess heat or flame due to a build-up of internal pressure.

### Flammability classification (OSHA 29 CFR 1910.1200, WHMIS2015)

: Not flammable

## **SECTION 6 – ACCIDENTAL RELEASE MEASURES**

Personal precautions : Restrict access to area until completion of clean-up. All persons dealing with

clean-up should wear the appropriate chemically protective equipment.

Protective equipment : Refer to Section 8 for additional information on acceptable personal protective

equipment.

Emergency Procedures : This product does not contain chemicals requiring EPA notification for spills. In

case of a spill, call the emergency telephone number listed in Section 1.

US CERCLA Reportable quantity (RQ): None reported.

Methods and materials for containment and cleaning up

: Ventilate area of release. Stop spill or leak at source if safely possible. Contain product with inert absorbent material, preventing it from entering sewer lines or waterways. Gather up spilled material and place in suitable container for later disposal (see Section 13). Residual of product, while still wet, can be cleaned up

with warm soapy water. Notify the appropriate authorities as required.

**Prohibited materials** : Avoid strong oxidizing agents

Environmental precautions : Do not allow product to enter drains or waterways. Do not allow material to

contaminate ground water system.

**Reference to other sections** : See Section 13 for disposal information.

# **SECTION 7 – HANDLING AND STORAGE**

Safe handling procedures : Observe good hygiene standards. Use only with adequate ventilation. Do not eat,

drink or smoke in the work area. Wash thoroughly after handling. Do not get in eyes, on skin, or on clothing. Avoid repeated or prolonged skin contact. Avoid breathing vapors or mists of this product. Sanding and grinding dusts may be harmful if inhaled. When removing this product from existing flooring (i.e. during a renovation), wear safety goggles and respiratory protection from dust due to blasting, chipping, or mechanically pulverizing. Wear protective clothing to prevent skin contact. Promptly remove any clothing that becomes contaminated. Clean

contaminated clothing before reuse. Keep container tightly closed.

Storage requirements : Store in a cool, dry, well-ventilated area. Store away from heat and open flame.

Avoid storing in direct sunlight. Store in original container. Keep tightly closed when not in use. Do not reuse empty container without commercial cleaning or

reconditioning.

Incompatible materials : See Section 10.

Special packaging materials : Always keep in containers made of the same materials as the supply container.

### SECTION 8 – EXPOSURE CONTROLS AND PERSONAL PROTECTION

Permissible Exposure Limits : No exposure limits have been established for the product itself. Below are exposure limits for the components in the product.

Ingredients	CAS#	ACGIH TLV		OSHA PEL	
		TWA	STEL	PEL	STEL
Crystalline silica	14808-60-7	0.025 mg/m <sup>3</sup> (respirable fraction)	N/Av	0.05 mg/m³ (respirable) (Final rule limit)	N/Av
2-Butoxyethanol	111-76-2	20 ppm	N/Av	50 ppm (skin)	N/Av

Engineering Controls : Use general or local exhaust ventilation to maintain air concentrations below recommended exposure limits. Ventilation should effectively remove and prevent

buildup of any vapor or mist generated from the handling of this product.

**Personal Protection Equipment** 

Eye / face protection : Safety glasses must be worn when using this product. During operations where

airborne dust is generated, wear chemical goggles.

Skin protection : Wear chemical resistant protective clothing and impervious gloves. Glove materials

such as nitrile rubber or Viton (fluorocarbon rubber) are recommended. Consult

with the glove manufacturer regarding breakthrough time for the components listed

in Section 3.

**Body protection** : Where extensive exposure to product is possible, use resistant coveralls, apron and

boots to prevent contact.

Respiratory protection : If work process generates excessive quantities of vapor or dust, or exposures in

excess of any PEL, wear an appropriate organic vapor respirator or particulate respirator (dust mask) rated N-95 or higher, appropriate for the conditions.

Site safety equipment : An eyewash station and safety shower should be made available in the immediate

working area.

General hygiene considerations : Avoid contact with eyes, skin and clothing. Avoid breathing vapors/dust. Do not

eat, drink or smoke when using this product. Clean all equipment and clothing at

end of each work shift.

## **SECTION 9 – PHYSICAL AND CHEMICAL PROPERTIES**

Physical state : Paste Appearance : off-white paste

 Odor
 : Mild
 Odor threshold
 : N/Av

 pH
 : 7.2 - 7.4
 Specific gravity
 : 1.53 - 1.64

 Boiling point
 : > 212°F (> 100°C) Coefficient of water/oil distribution
 : N/Av

Melting/Freezing point : N/Av Solubility in water : Slightly soluble

Vapor pressure (mm Hg @  $20^{\circ}$ C /  $68^{\circ}$ F) : N/Av Evaporation rate (*n*-Butyl acetate = 1) : N/Av Vapor density (Air = 1) : N/Av Volatiles (% by weight) : 14 - 16

Volatile Organic Compounds (VOCs): 12.5 g/L SCAQMD Rule 1168

Particle size Flammability classification : N/Av : Not flammable Flash point : >212°F (100°C) Lower flammable limit (% by vol) : Not available Flash point method Setaflash closed Upper flammable limit (% by vol) : Not available **Auto-ignition temperature Decomposition temperature** : Not available : N/Av **Viscosity** : Not available **Oxidizing properties** : Not available

Explosion data: Sensitivity to mechanical impact / static discharge

: Not expected to be sensitive to mechanical impact or static discharge.

## **SECTION 10 – REACTIVITY AND STABILITY INFORMATION**

Reactivity : Does not react.

Stability : Stable under the recommended storage and handling conditions prescribed.

**Hazardous reactions** : Hazardous polymerization does not occur.

Conditions to avoid : High temperatures.

Materials to avoid and incompatability

: Oxidizing agents.

**Hazardous decomposition products** 

: None known, refer to hazardous combustion products in Section 5.

## **SECTION 11 – TOXICOLOGICAL INFORMATION**

Routes of exposure : Inhalation: YES Skin Absorption: NO Skin and Eyes: Yes Ingestion: YES

Symptoms of exposure : See Section 4.

Calculated Acute Toxicity Estimates for the Product

 Inhalation
 : > 30 mg/L

 Oral
 : > 3000 mg/kg

 Dermal
 : > 3000 mg/kg

**Toxicological data** : See below for individual ingredient acute toxicity data.

	LC50 (4 hr)	LD50		
Ingredients	Inhalation, rat	Oral, rat	Dermal, rabbit	
2-Butoxyethanol	450 ppm	250 mg/kg	220 mg/kg	
Crystalline silica, quartz	N/Av	N/Av	N/Av	

Skin corrosion or irritation : May cause irritation to skin.

Serious eye damage / eye irritation : May cause irritation to eyes.

Respiratory or skin sensitization : None known.

Germ cell mutagenicity : None known.

Carcinogenic status : This product contains Crystalline silica - Quartz. Crystalline silica - Quartz is

classified as carcinogenic by inhalation by IARC (Group 1), ACGIH (Group A2), NTP (Group 1) and OSHA (OSHA Select carcinogen). During normal usage of the product as recommended, airborne dusts will not be present. Do not sand/grind/chip off excess material, following initial application, unless wearing proper

respiratory and eye protection. (See Section 8.)

This product contains 2-Butoxyethanol. 2-Butoxyethanol is not listed as a carcinogen by NTP or OSHA, classified as Category 3 (not classifiable as to carcinogenicity) by IARC, classified by EPA as "Not likely to be carcinogenic to humans at environmental concentrations at or below the RfC [RfC = 1.6 mg/m³]", and classified by ACGIH as A3 – Animal Carcinogen (with unknown relevance to

humans).

Reproductive toxicity : None known.

Specific Target Organ Toxicity, Single Exposure

: Not considered to be a hazard during normal usage of the product as

recommended.

Specific Target Organ Toxicity, Repeated Exposure

: None known.

**Aspiration hazard** : None known. **Additional information** : N/Av

# **SECTION 12 – ECOLOGICAL INFORMATION**

Environmental effects : The product should not be allowed to enter drains or water courses, or be

deposited where it can affect ground or surface waters.

Ecotoxicity : No data available.
Biodegradability : No data available.
Bioaccumulative potential : No data available.
Mobility in soil : No data available.
PBT and vPvB assessment : No data available.
Other adverse effects : No data available.

# **SECTION 13 – DISPOSAL CONSIDERATION**

Handling for disposal : Handle waste according to recommendations in Section 7.

Methods of disposal : Dispose in accordance with all applicable federal, state, provincial and local

regulations. Contact your local, state, provincial or federal environmental agency

for specific rules.

Packaging : Handle contaminated packaging in the same manner as the product.

RCRA : For disposal of unused or waste material, check with local, state and federal

environmental agencies.

# **SECTION 14 – TRANSPORTATION INFORMATION**

Regulatory	UN			Packing	
Information	Number	Shipping Name	Class	Group	Label

TDG	None	This product is not regulated according to Canadian TDG regulations.	None	None	None
TDG Additional Information	None				
49 CFR/DOT	None	This product is not regulated according to US DOT regulations.	None	None	None
49 CFR/DOT Additional Information	None	•		•	•

IATA : Not regulated for Air Transport

IMDG : Not regulated for Ocean Transport

Marine Pollutant : Not a Marine Pollutant

# SECTION 15 – REGULATORY INFORMATION

#### **Canadian Information:**

This product has been classified according to the hazard criteria of the Hazardous Products Regulations (HPR). This SDS contains all information required by the HPR.

Canadian Environmental Protection Act (CEPA) information: All ingredients listed appear on either the Domestic Substances List (DSL) or the Non- Domestic Substances List (NDSL).

#### **US Federal Information:**

TSCA: All listed ingredients appear on the Toxic Substances Control Act (TSCA) inventory.

CERCLA Reportable Quantity (RQ) (40 CFR 117.302): None reported.

SARA TITLE III: Sec. 311 and 312, SDS Requirements, 40 CFR 370 Hazard Classes:

Immediate (Acute) Health Hazard

Chronic Health Hazard.

Under SARA Sections 311 and 312, the EPA has established threshold quantities for the reporting of hazardous chemicals. The current thresholds are 500 pounds or the threshold planning quantity (TPQ), whichever is lower, for extremely hazardous substances and 10,000 pounds for all other hazardous chemicals.

SARA TITLE III: Sec. 313, Toxic Chemicals Notification, 40 CFR 372: This material is not subject to SARA notification requirements, since it does not contain any Toxic Chemical constituents above de minimus concentrations.

### U.S. State Right To Know Laws

California Proposition 65: See product label for information regarding Proposition 65.

# Other State Right to Know Laws:

Ingredient on State RTK Law?	CAS#	CA	MA	MN	NJ	NY	PA	RI
Crystalline silica, quartz	14808-60-7	No	YES	YES	YES	No	YES	YES
2-Butoxyethanol	111-76-2	YES	YES	YES	YES	No	YES	YES

## **SECTION 16 – OTHER INFORMATION**

HMIS Rating : \*- Chronic Hazard 0 - Minimal 1 - Slight 2 - Moderate 3 - Serious 4 - Severe

Health: \*2 Flammability 1 Physical Hazard 0 PPE: Gloves, safety glasses

Legend : ACGIH: American Conference of Governmental Industrial Hygienists

CAS: Chemical Abstract Services

CERCLA: Comprehensive Environmental Response, Compensation, and Liability

Act of 1980

CFR: Code of Federal Regulations DOT: Department of Transportation DSL: Domestic Substances List EPA: Environmental Protection Agency GHS: Globally Harmonized System HPR: Hazardous Products Regulations

IARC: International Agency for Research on Cancer

Inh: Inhalation N/Av: Not Available N/Ap: Not Applicable

NIOSH: National Institute of Occupational Safety and Health

NTP: National Toxicology Program

OSHA: Occupational Safety and Health Administration

PEL: Permissible exposure limit

RCRA: Resource Conservation and Recovery Act SARA: Superfund Amendments and Reauthorization Act

STEL: Short Term Exposure Limit

TDG: Canadian Transportation of Dangerous Goods Act & Regulations

TLV: Threshold Limit Values TSCA: Toxic Substance Control Act TWA: Time Weighted Average

WHMIS: Workplace Hazardous Materials Identification System

### **Disclaimer of Liability**

The Information presented herein is supplied as a guide to those who handle or use this product and has been prepared in good faith by technically knowledgeable personnel. It is not intended to be all-inclusive. The manner and conditions of use and handling may involve other and additional considerations. Safe work practices must be employed when working with any materials. It is important that the end user determines the adequacy of the safety procedures employed during the use of this product. No warranty of any kind is given or implied. ARDEX L.P. will not be liable for any damages, losses, injuries or consequential damages which may result from the use or reliance on any information contained herein.

Prepared By: ARDEX L.P. 400 Ardex Park Drive Aliquippa, PA, U.S.A. 15001

(724) 203-8000

Visit our Website: http://www.ardexamericas.com

Revision date: : 13-May-2019

**End of Document**