

EXTRAFLEX®

04-002

SPECIFICATION SHEET



SPECIFICATIONS:

- **Liner Materials:** 15g Gray Nylon Liner
- **Coating Materials:** Black HCT® MicroFoam Nitrile
- **Wrist Design:** Continuous Knit
- **Origin:** PRC
- **Sizes:** XS-XXL

Armor Guys Reference Number: 04-002

PACKAGING:

GLOVE SIZE	XS	S	M	L	XL	XXL
CUFF COLOR	Purple	Red	Yellow	Brown	Black	Blue
PER CASE	10DZ	10DZ	10DZ	10DZ	10DZ	10DZ
CASE WEIGHT	11.01/lbs	11.89/lbs	12.56/lbs	15.42/lbs	16.52/lbs	17.62/lbs

PERFORMANCE LEVEL:

EN388: 4131 – EN Level 1 Cut Resistance

ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

ATTRIBUTES:

- 15g Gray Nylon Liner
- Black HCT® MicroFoam Nitrile Knuckle Coating

FEATURES:

- Knuckle Coating for Added Back of Hand Liquid Resistance
- Enhanced Grip & Abrasion Resistance
- Breathable Coating for Superior Comfort

APPLICATIONS:

- General Assembly
- Automotive Assembly
- Light Manufacturing
- Maintenance
- Warehousing
- Landscaping

CATEGORY:

- **Extraflex®**

CARE INSTRUCTIONS:

Recommended washing temperature is between 40°C and 60°C (104 - 140°F) with mild detergent.

The drying process may cause felting on the fabric surface. Drying temperatures should not exceed 70°C (158°F).

TECHNOLOGIES:



ARMOR GUYS

• PROTECTED •