






Note that all unique customer requirements (i.e tolerance) need to be verified thru Alfa Laval.

Z80  
Alloy 316  
S3,S4



Z 25  
Carbon Steel  
S1,S2,T3,T4



T1 T2 T3 T4 locations on back side  
correspond to S1 S2 S3 S4 on front side

HEATING SURFACE  
NETWEIGHT 45.4 kg  
OPERATING WEIGHT  
PLATE MATERIAL Alloy 316  
PLATE GROUPING 1\*29H/1\*30H

ALL DIMENSIONS IN MILLIMETERS

| SIDE | MEDIA | INLET | TEMP. | OUTLET | TEMP. | FLOW RATE | PRESSURE DROP | LIQUID VOL.          |
|------|-------|-------|-------|--------|-------|-----------|---------------|----------------------|
| 1    |       |       |       |        |       |           |               | 7.25 dm <sup>3</sup> |
| 2    |       |       |       |        |       |           |               | 7.5 dm <sup>3</sup>  |

PRESSURE VESSEL APPROVAL

ASME 302 degr F/CRN

AlfaNova HP 76-60H (3287131345)

www.alfalaval.com

CUSTOMER NAME / REF. NO.

TOTAL LENGTH 257.0 mm  
TOTAL WIDTH 191.0 mm  
TOTAL HEIGHT 699.0 mm

COMPANY / REF.

6/27/2017  
REV 0