





Note that all unique customer requirements (i.e tolerance) need to be verified thru Alfa Laval.



T1 T2 T3 T4 locations on back side correspond to S1 S2 S3 S4 on front side

HEATING SURFACE
NETWEIGHT 38.8 kg
OPERATING WEIGHT
PLATE MATERIAL Alloy 316
PLATE GROUPING 1*34AMH/1*35AML

ALL DIMENSIONS IN MILLIMETERS

SIDE	MEDIA	INLET	TEMP.	OUTLET	TEMP.	FLOW RATE	PRESSURE DROP	LIQUID VOL.
1								5.44 dm ³
2								7 dm ³

PRESSURE VESSEL APPROVAL UL/CRN
ACH220EQ-70AM-F S62 (3287155309)

www.alfalaval.com

CUSTOMER NAME / REF. NO.

TOTAL LENGTH 200.2 mm
TOTAL WIDTH 190.0 mm
TOTAL HEIGHT 616.0 mm

COMPANY / REF.

3/15/2017
REV 0