




This document and its contents are subject to copyrights and other intellectual property rights owned by Alfa Laval (publ) or any of its affiliates (Alfa Laval). No part of this document may be copied, reproduced or transmitted in any form or by any means, or for any purpose, without Alfa Laval's prior express written permission. Information and services provided in this document are made as a benefit and service to the user, and no representations or warranties are made about the accuracy or suitability of this information and these services for any purpose. All rights are reserved.

OPID 240 es 8240171453

PRESSURE PLATE
(MOVABLE)





Space between pressure plate and supporting column should be kept free from fixed installations!



ASME B1.20.1 - 2-11.5 NPT, ALLOY 316L, 101 mm
S1, S2, S3, S4

A-A:




ASME B1.20.1 - 2-11.5 NPT

NO. OF UNITS

1

null GPM
null GPM



FRAME PLATE



*)
Recommended
free space
for opening
and closing
to be applied
on both sides

**)
Free space can
be reduced to
this distance on
one of the sides

All dimensions in inches



APPROX. OUTER DIMENSIONS
LENGTH 6.7 in
WIDTH 10.2 in
HEIGHT 27.6 in
APPROX. WEIGHTS
NET WEIGHT, EMPTY 148 lb
WEIGHT FULL OF WATER 154 lb
PLATE MATERIAL ALLOY 316
PLATE THICKNESS 0.5 mm
GASKET NBRP Clip-on

CHANNEL ARRANGEMENT 1*7 MH
/ 1*7 ML




www.alfalaval.com

DRAWING
GASKETED PLATE HEAT EXCHANGER

T5-BFG

ASME
Code Section VIII Div.1

MAWP 145 psi at 150.1 °F
MDMT 32.0 °F at 145 psi
Designed and constructed in accordance with the 2019 ASME Code.



8240171453
T5-BFG, 15 plates

Do not use this drawing for foundation bolting or piping layout

DATE 6/1/22
REVISION 0