



| Code            | W.L.L.<br>t | A<br>mm | B<br>mm | C<br>mm | D<br>mm | E<br>mm | F<br>mm | G<br>mm | H<br>mm | Welding thickness<br>HV + $\Delta a$ | Weight<br>Kg |
|-----------------|-------------|---------|---------|---------|---------|---------|---------|---------|---------|--------------------------------------|--------------|
| <b>C820X04</b>  | 4           | 14      | 65      | 48      | 29      | 134     | 14      | 60      | 79      | HV 4+3                               | 0,73         |
| <b>C820X067</b> | 6,7         | 20      | 83      | 60      | 39      | 169     | 16      | 88      | 103     | HV 5,5+3                             | 1,8          |
| <b>C820X10</b>  | 10          | 22      | 96      | 65      | 48      | 196     | 19,5    | 98      | 118     | HV 6+4                               | 3            |
| <b>C820X16</b>  | 16          | 31      | 126     | 90      | 55      | 264     | 29      | 127     | 155     | HV 8,5 + 4                           | 5,75         |
| <b>C820X30</b>  | 30          | 42      | 175     | 130     | 79      | 371     | 45      | 157     | 217     | HV 15+4                              | 16           |