

CRAFTSMAN®

1 YEAR LIMITED WARRANTY
WE BUILD PRIDE™

3 GALLON HOTDOG AIR COMPRESSOR

This CRAFTSMAN CMO200341 3 gallon air compressor has the power you need in the house and on the job site. It's the same power as the larger compressors, only smaller air capacity which makes it more mobile. Its Oil-free pump requires less maintenance for your convenience. It can do most any job you need it to do.



Light compact design with carrying handle for each move

LARGE REGULATOR KNOB FOR EASY OPERATION

HIGH PERFORMANCE MOTOR
EASILY STARTS IN COLD WEATHER
OIL-FREE PUMP
FOR LONG LIFE AND LITTLE MAINTENANCE

3 GAL TANK | 2.6 SCFM* @ 90 PSI
LONG RUNTIME AND QUICK RECOVERY

SPECIFICATIONS

- 3 Gallon*
- 60 Hz
- 1.5 HP**
- Airflow: 2.6CFM@90PSI, 3.7CFM@40PSI
- Ball Valve
- Handle Type: Rubber Reinforce
- Decibel Rating: ≤ 87 dBA
- Life Cycle: ≥ 300 Hours@ 50% Duty Cycle
- Working Pressure: 125-155 PSI (8-10 Bar)
- Produce Size (LxWxH): 19.06 x 19.06 x 12.36 inch
48.4 x 48.4 x 31.4cm
- Packing Size (LxWxH): 19.49 x 19.49 x 13.19 inch
49.5 x 49.5 x 33.5 cm
- Gross Weight: 37.04 lbs / 16.8 kg
Net Weigh: 33.2 lbs / 15.1 kg
- UPC: 00810941030932***



- * Tank capacity refers to actual tank volume and does not reflect capacity available during operation.
- ** "Peak Horsepower" (PHP) is a term used in the wet/dry vacuum industry for consumer comparison purposes. It does not denote the operational horsepower of a wet/dry vacuum but rather the horsepower output of a motor, including the motor's inertial contribution, achieved in laboratory testing. In actual use, wet/dry vacuum motors do not operate at the peak horsepower shown.
- *** UPC Can vary by product or customer