



SAFETY DATA SHEET

PGO FGL-680

According to Appendix D, OSHA Hazard Communication Standard 29 CFR §1910.1200.

1. Identification

Product identifier

Product name PGO FGL-680

Product number L0815-057, L0815-060, L0815-062

NSF Registration Number 141196

Recommended use of the chemical and restrictions on use

Application Food grade lubricating oil

Uses advised against No specific uses advised against are identified.

Details of the supplier of the safety data sheet

Manufacturer Lubriplate Lubricants Co.
Corporate Headquarters
129 Lockwood Street
Newark, NJ 07105

Midwest Office & Plant
1500 Oakdale Ave.
Toledo, OH 43605
419-691-2491
419-693-3806

Emergency telephone number

Emergency telephone Chem-Tel: 1-800-255-3924 (US & Canada only)
01-813-248-0585 (Outside US & Canada)

2. Hazard(s) identification

Classification of the substance or mixture

Physical hazards Not Classified

Health hazards Not Classified

Environmental hazards Not Classified

Label elements

Hazard statements NC Not Classified

Other hazards

This product does not contain any substances classified as PBT or vPvB.

3. Composition/information on ingredients

Mixtures

Composition comments * The exact percentage withheld as a trade secret in accordance with 29 CFR 1910.1200.

PGO FGL-680

4. First-aid measures

Description of first aid measures

General information	Get medical attention immediately. Show this Safety Data Sheet to the medical personnel.
Inhalation	Remove affected person from source of contamination. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Place unconscious person on their side in the recovery position and ensure breathing can take place.
Ingestion	Rinse mouth thoroughly with water. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Do not induce vomiting unless under the direction of medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Never give anything by mouth to an unconscious person. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Place unconscious person on their side in the recovery position and ensure breathing can take place. Maintain an open airway. Loosen tight clothing such as collar, tie or belt.
Skin Contact	Rinse with water.
Eye contact	Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 10 minutes.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.

Most important symptoms and effects, both acute and delayed

General information	See Section 11 for additional information on health hazards. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	Prolonged inhalation of high concentrations may damage respiratory system.
Ingestion	Gastrointestinal symptoms, including upset stomach. Fumes from the stomach contents may be inhaled, resulting in the same symptoms as inhalation.
Skin contact	Prolonged contact may cause dryness of the skin.
Eye contact	May cause temporary eye irritation.

Indication of immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
-----------------------------	------------------------

5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media	The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

Special hazards arising from the substance or mixture

Specific hazards	Containers can burst violently or explode when heated, due to excessive pressure build-up.
Hazardous combustion products	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

Advice for firefighters

PGO FGL-680

Protective actions during firefighting	Avoid breathing fire gases or vapors. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapors and protect men stopping the leak.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Standard Firefighter's clothing including helmets, protective boots and gloves will provide a basic level of protection for chemical incidents.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions	No action shall be taken without appropriate training or involving any personal risk. Keep unnecessary and unprotected personnel away from the spillage. Wear protective clothing as described in Section 8 of this safety data sheet. Follow precautions for safe handling described in this safety data sheet. Wash thoroughly after dealing with a spillage. Ensure procedures and training for emergency decontamination and disposal are in place. Do not touch or walk into spilled material.
-----------------------------	---

Environmental precautions

Environmental precautions	Large Spillages: Inform the relevant authorities if environmental pollution occurs (sewers, waterways, soil or air).
----------------------------------	--

Methods and material for containment and cleaning up

Methods for cleaning up	Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Approach the spillage from upwind. Small Spillages: If the product is soluble in water, dilute the spillage with water and mop it up. Alternatively, or if it is not water-soluble, absorb the spillage with an inert, dry material and place it in a suitable waste disposal container. Large Spillages: If leakage cannot be stopped, evacuate area. Flush spilled material into an effluent treatment plant, or proceed as follows. Contain and absorb spillage with sand, earth or other non-combustible material. Place waste in labeled, sealed containers. Clean contaminated objects and areas thoroughly, observing environmental regulations. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.
--------------------------------	---

Reference to other sections	For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.
------------------------------------	---

7. Handling and storage

Precautions for safe handling

Usage precautions	Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimize spills. Keep container tightly sealed when not in use. Avoid the formation of mists. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment.
--------------------------	---

Advice on general occupational hygiene	Wash promptly if skin becomes contaminated. Take off contaminated clothing and wash before reuse. Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Wash at the end of each work shift and before eating, smoking and using the toilet. Change work clothing daily before leaving workplace.
---	---

Conditions for safe storage, including any incompatibilities

PGO FGL-680

Storage precautions

Store away from incompatible materials (see Section 10). Store in accordance with local regulations. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage. Utilize retaining walls to prevent soil and water pollution in the event of spillage. The storage area floor should be leak-tight, jointless and not absorbent.

Storage class

Unspecified storage.

Specific end uses(s)**Specific end use(s)**

The identified uses for this product are detailed in Section 1.

8. Exposure controls/Personal protection

Control parameters**Occupational exposure limits****diphenylamine**

Long-term exposure limit (8-hour TWA): ACGIH 10 mg/m³

A4

ACGIH = American Conference of Governmental Industrial Hygienists.

A4 = Not Classifiable as a Human Carcinogen.

Exposure controls**Protective equipment****Appropriate engineering controls**

Provide adequate ventilation. Personal, workplace environment or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Use process enclosures, local exhaust ventilation or other engineering controls as the primary means to minimize worker exposure. Personal protective equipment should only be used if worker exposure cannot be controlled adequately by the engineering control measures. Ensure control measures are regularly inspected and maintained. Ensure operatives are trained to minimize exposure.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Personal protective equipment for eye and face protection should comply with OSHA 1910.133. Unless the assessment indicates a higher degree of protection is required, the following protection should be worn: Tight-fitting safety glasses.

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. The most suitable glove should be chosen in consultation with the glove supplier/manufacture, who can provide information about the breakthrough time of the glove material. To protect hands from chemicals, gloves should comply with OSHA 1910.138 and be demonstrated to be impervious to the chemical and resist degradation. Considering the data specified by the glove manufacturer, check during use that the gloves are retaining their protective properties and change them as soon as any deterioration is detected. Frequent changes are recommended.

Other skin and body protection

Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.

PGO FGL-680

Hygiene measures	Provide eyewash station and safety shower. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reuse. Clean equipment and the work area every day. Good personal hygiene procedures should be implemented. Wash at the end of each work shift and before eating, smoking and using the toilet. When using do not eat, drink or smoke. Preventive industrial medical examinations should be carried out. Warn cleaning personnel of any hazardous properties of the product.
Respiratory protection	Respiratory protection complying with an approved standard should be worn if a risk assessment indicates inhalation of contaminants is possible. Ensure all respiratory protective equipment is suitable for its intended use and is NIOSH approved. Check that the respirator fits tightly and the filter is changed regularly. Gas and combination filter cartridges should comply with OSHA 1910.134. Full face mask respirators with replaceable filter cartridges should comply with OSHA 1910.134. Half mask and quarter mask respirators with replaceable filter cartridges should comply with OSHA 1910.134.
Environmental exposure controls	Keep container tightly sealed when not in use.

9. Physical and chemical properties

Information on basic physical and chemical properties

Appearance	Liquid.
Color	Straw.
Odor	Mild.
Odor threshold	Not available.
pH	Not available.
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	> 287°C/549°F Cleveland open cup.
Evaporation rate	< 0.01 (butyl acetate = 1)
Upper/lower flammability or explosive limits	Not available.
Vapor pressure	Not available.
Vapor density	Not available.
Relative density	1.07
Solubility(ies)	Insoluble in water.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	680 cSt @ 40°C
Explosive properties	Not applicable.
Oxidizing properties	Not available.
Other information	None.

10. Stability and reactivity

PGO FGL-680

Reactivity	See the other subsections of this section for further details.
Stability	Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.
Possibility of hazardous reactions	No potentially hazardous reactions known.
Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.
Materials to avoid	No specific material or group of materials is likely to react with the product to produce a hazardous situation.
Hazardous decomposition products	Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

11. Toxicological information

Information on toxicological effects

Acute toxicity - oral

Summary Based on available data the classification criteria are not met.

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Summary Based on available data the classification criteria are not met.

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Summary Based on available data the classification criteria are not met.

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Summary Based on available data the classification criteria are not met.

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Summary Based on available data the classification criteria are not met.

Serious eye damage/irritation Based on available data the classification criteria are not met.

Respiratory sensitization

Summary Based on available data the classification criteria are not met.

Respiratory sensitization Based on available data the classification criteria are not met.

Skin sensitization

Summary Based on available data the classification criteria are not met.

Skin sensitization Based on available data the classification criteria are not met.

Germ cell mutagenicity

Summary Based on available data the classification criteria are not met.

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

PGO FGL-680

Summary	Based on available data the classification criteria are not met.
Carcinogenicity	Based on available data the classification criteria are not met.
IARC carcinogenicity	None of the ingredients are listed or exempt.
<u>Reproductive toxicity</u>	
Summary	Based on available data the classification criteria are not met.
Reproductive toxicity - fertility	Based on available data the classification criteria are not met.
Reproductive toxicity - development	Based on available data the classification criteria are not met.
<u>Specific target organ toxicity - single exposure</u>	
Summary	Based on available data the classification criteria are not met.
STOT - single exposure	Not classified as a specific target organ toxicant after a single exposure.
<u>Specific target organ toxicity - repeated exposure</u>	
Summary	Based on available data the classification criteria are not met.
STOT - repeated exposure	Not classified as a specific target organ toxicant after repeated exposure.
<u>Aspiration hazard</u>	
Summary	Based on available data the classification criteria are not met.
Aspiration hazard	Based on available data the classification criteria are not met.
<u>General information</u>	
General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	Prolonged inhalation of high concentrations may damage respiratory system.
Ingestion	Gastrointestinal symptoms, including upset stomach. Fumes from the stomach contents may be inhaled, resulting in the same symptoms as inhalation.
Skin Contact	Prolonged contact may cause dryness of the skin.
Eye contact	May cause temporary eye irritation.
Route of exposure	Ingestion Inhalation Skin and/or eye contact
Target Organs	No specific target organs known.

12. Ecological information

Ecotoxicity	Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.
Toxicity	Based on available data the classification criteria are not met.
<u>Acute aquatic toxicity</u>	
Summary	Based on available data the classification criteria are not met.
<u>Chronic aquatic toxicity</u>	
Summary	Based on available data the classification criteria are not met.
<u>Persistence and degradability</u>	
Persistence and degradability	The degradability of the product is not known.
<u>Bioaccumulative potential</u>	

PGO FGL-680

Bio-Accumulative Potential No data available on bioaccumulation.

Partition coefficient Not available.

Mobility in soil

Mobility No data available.

Other adverse effects

Other adverse effects None known.

13. Disposal considerations

Waste treatment methods

General information

The generation of waste should be minimized or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. Disposal of this product, process solutions, residues and by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any local authority requirements. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.

Disposal methods

Do not empty into drains. Dispose of surplus products and those that cannot be recycled via a licensed waste disposal contractor. Waste, residues, empty containers, discarded work clothes and contaminated cleaning materials should be collected in designated containers, labeled with their contents. Waste packaging should be collected for reuse or recycling. Incineration or landfill should only be considered when recycling is not feasible.

14. Transport information

General

The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, DOT).

UN Number

UN No. (International) Not applicable.

UN proper shipping name

Proper shipping name (International) Not applicable.

Transport hazard class(es)

Transport Labels (International) No transport warning sign required.

Transport labels

No transport warning sign required.

DOT transport labels

No transport warning sign required.

Packing group

Packing group (International) Not applicable.

Environmental hazards

Environmentally Hazardous Substance

No.

PGO FGL-680

Special precautions for user

Not applicable.

DOT TIH Zone Not applicable.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

15. Regulatory information

Regulatory References OSHA Hazard Communication Standard 29 CFR §1910.1200

US Federal Regulations

SARA Section 302 Extremely Hazardous Substances Tier II Threshold Planning Quantities

None of the ingredients are listed or exempt.

CERCLA/Superfund, Hazardous Substances/Reportable Quantities (EPA)

None of the ingredients are listed or exempt.

SARA Extremely Hazardous Substances EPCRA Reportable Quantities

None of the ingredients are listed or exempt.

SARA 313 Emission Reporting

The following ingredients are listed or exempt:

diphenylamine

1.0 %

CAA Accidental Release Prevention

None of the ingredients are listed or exempt.

FDA - Essential Chemical

None of the ingredients are listed or exempt.

FDA - Precursor Chemical

None of the ingredients are listed or exempt.

SARA (311/312) Hazard Categories

None of the ingredients are listed or exempt.

OSHA Highly Hazardous Chemicals

None of the ingredients are listed or exempt.

US State Regulations

California Proposition 65 Carcinogens and Reproductive Toxins

None of the ingredients are listed or exempt.

California Air Toxics "Hot Spots" (A-I)

None of the ingredients are listed or exempt.

California Air Toxics "Hot Spots" (A-II)

None of the ingredients are listed or exempt.

California Directors List of Hazardous Substances

The following ingredients are listed or exempt:

diphenylamine

PGO FGL-680

Massachusetts "Right To Know" List

The following ingredients are listed or exempt:

diphenylamine

Rhode Island "Right To Know" List

The following ingredients are listed or exempt:

diphenylamine

Minnesota "Right To Know" List

The following ingredients are listed or exempt:

diphenylamine

New Jersey "Right To Know" List

The following ingredients are listed or exempt:

diphenylamine

Pennsylvania "Right To Know" List

The following ingredients are listed or exempt:

diphenylamine

Inventories

US - TSCA

The following ingredients are listed or exempt:

Synthetic isoparaffinic hydrocarbon

reaction mass of: triphenylthiophosphate and tertiary butylated phenyl derivatives

1-[2-[2-(3-methoxypropoxy)propoxy]ethoxy]butane

Ester

Nonhazardous ingredients (US only)

benzamine, n-phenyl-, reaction products with 2,4,4-trimethylpentene

diphenylamine

1-H benzotriazole-1-methanamine, N,N-bis(2-ethylhexyl)-methyl-

US - TSCA 12(b) Export Notification

None of the ingredients are listed or exempt.

16. Other information

Abbreviations and acronyms used in the safety data sheet TDG: The transport of dangerous goods act

IATA: International air transport association.

ICAO: Technical instructions for the safe transport of dangerous goods by air.

IMDG: International maritime dangerous goods.

CAS: Chemical abstracts service.

ATE: Acute toxicity estimate.

LC₅₀: Lethal concentration to 50 % of a test population.

LD₅₀: Lethal dose to 50% of a test population (median lethal dose).

EC₅₀: 50% of maximal effective concentration.

PBT: Persistent, bioaccumulative and toxic substance.

vPvB: Very persistent and very bioaccumulative.

PGO FGL-680

Training advice	Read and follow manufacturer's recommendations. Only trained personnel should use this material.
Revision comments	Rereleased through new GHS Software.
Revision date	4/5/2023
Revision	2
Supersedes date	10/4/2021
SDS No.	4814
End of SDS	

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.