



UPF 100

Oeko-Tex[®] Standard 100



SPECIFICATIONS:

- **Liner Materials:** 15g Gray Kyorene[®] Pro Graphene A5 Liner
- **Coating Materials:** Black HCT[®] MicroFoam Nitrile
- **Wrist Design:** Continuous Knit
- **Origin:** PRC
- **Sizes:** XS-XXXL

Armor Guys Reference Number: 00-857

PACKAGING:

GLOVE SIZE	XS	S	M	L	XL	XXL	XXXL
CUFF COLOR	Purple	Red	Yellow	Brown	Black	Blue	Gray
PER CASE	6DZ	6DZ	6DZ	6DZ	6DZ	6DZ	6DZ

PERFORMANCE LEVEL:

EN388: 4443E – EN Level 4 Cut Resistance

ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5
CUT TDM TEST	A	B	C	D	E	F

ATTRIBUTES:

- 15g Gray Kyorene[®] Pro Graphene A5 Liner
- Black HCT[®] MicroFoam Nitrile Palm Coating

FEATURES:

- Back of Hand TPV Protection
- Reinforced Thumb Crotch for Extended Wear
- No Stainless Steel or Fiberglass
- Ergonomically Shaped for Superior Fit
- Bacteriostatic Kills Harmful Bacteria
- Thermal Regulating to Keep the Hands Comfortable
- Odor Neutralizing to Keep the Gloves Smelling Fresh

APPLICATIONS:

- Oil & Gas
- Mining
- Construction

CATEGORY:

- Kyorene[®] Pro

CARE INSTRUCTIONS:

Recommended washing temperature is between 40°C and 60°C (104 - 140°F) with mild detergent.

The drying process may cause felting on the fabric surface. Drying temperatures should not exceed 70°C (158°F).

TECHNOLOGIES:

**KYORENE[®]
PRO GRAPHENE**

HCT
Hybrid Coating Technology



**VERIFIED GRAPHENE[®]
PRODUCER**
THE GRAPHENE COUNCIL

ARMOR GUYS
• PROTECTED •