

Typical G-Frame Circuit Breaker



**Contents**

<i>Description</i>	<i>Page</i>
Product Overview . . . . .	V4-T2-220
Standards and Certifications . . . . .	V4-T2-221
Quick Reference . . . . .	V4-T2-222
G-Frame (15–100 Amperes) . . . . .	V4-T2-225
F-Frame (10–225 Amperes) . . . . .	V4-T2-239
J-Frame (70–250 Amperes) . . . . .	V4-T2-257
K-Frame (70–400 Amperes) . . . . .	V4-T2-265
L-Frame (125–600 Amperes) . . . . .	V4-T2-289
M-Frame (300–800 Amperes) . . . . .	V4-T2-315
N-Frame (400–1200 Amperes) . . . . .	V4-T2-326
R-Frame (800–2500 Amperes) . . . . .	V4-T2-341
Motor Circuit Protectors (MCP) . . . . .	V4-T2-360
Motor Protection Circuit Breakers (MPCB) . . . . .	V4-T2-371
Type ELC Current Limiter Attachment (Size 0–4) . . . . .	V4-T2-373
Current Limiting Circuit Breaker Module . . . . .	V4-T2-374
Internal Accessories . . . . .	V4-T2-377
External Accessories . . . . .	V4-T2-410

**Type GD Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units (15–100 Amperes)**

**Product Description**

- Cable in, cable out
- Includes mounting hardware and BMHE

**Standards and Certifications**

- UL/CSA



**Product Selection**

**Type GD Thermal-Magnetic Circuit Breakers with Non-Interchangeable Trip Units**

Maximum Continuous Ampere Rating at 40 °C	480 Vac Maximum, 250 Vdc		Includes Binding Head Screws and Clamps 10–32 x 0.312
	14 kAIC at 480 Vac	22 kAIC at 480 Vac	
	Includes Line and Load Terminals		
	Two-Pole Catalog Number	Three-Pole Catalog Number	Three-Pole Catalog Number
15	GD2015	GD3015	GD3015D
20	GD2020	GD3020	GD3020D
25	GD2025	GD3025	GD3025D
30	GD2030	GD3030	GD3030D
35	GD2035	GD3035	GD3035D
40	GD2040	GD3040	GD3040D
45	GD2045	GD3045	GD3045D
50	GD2050	GD3050	GD3050D
60	—	GD3060	GD3060D
70	—	GD3070	GD3070D
80	—	GD3080	GD3080D
90	—	GD3090	GD3090D
100	—	GD3100	GD3100D