



Emergency-stop, Palm-tree shape, 60 mm, Key-release, MS2, 2 NC, Screw connection, Not suitable for master key systems



Part no. C22-PVS60P-MS2-K02
Catalog No. 136609
Alternate Catalog No. C22-PVS60P-MS2-K02

Delivery program

| | | | |
|---------------------------|---|----|--|
| Product range | | | RMQ Compact |
| Basic function | | | Controlled stop pushbuttons/emergency-stop buttons |
| Single unit/Complete unit | | | Complete unit |
| Design | | | Palm-tree shape |
| Diameter | ∅ | mm | 60 |
| Illumination | | | Non-illuminated |
| | | | Key-release |
| Connection type | | | Screw connection |
| Description | | | Tamper-proof according to ISO 13850/EN 418 |
| | | | Not suitable for master key systems |
| Lock mechanism | | | MS2 |

Colour

| | | | |
|----------------------------|--|--|------------------|
| Mushroom head | | | Red |
| | | | |
| Base | | | yellow |
| Degree of Protection | | | IP66, IP67, IP69 |
| Connection to SmartWire-DT | | | no |

Contacts

| | | | |
|-----------------------|--|--|--|
| N/C = Normally closed | | | 2 NC |
| Notes | | | = safety function, by positive opening to IEC/EN 60947-5-1 |

Actuator travel and actuation force as per DIN EN 60947-5-1, K.5.4.1

| | | | |
|------------------------------------|----|--|------|
| | mm | | 4.65 |
| Maximum travel | mm | | 5.7 |
| Minimum force for positive opening | N | | 30 |

| | | | |
|------------------|--|--|--|
| Contact sequence | | | |
|------------------|--|--|--|

Contact travel = Contact closed = Contact open

| | | | |
|-----------------------|--|--|-----------------|
| Contact diagram | | | Zw = 4.5 mm |
| Positive opening (ZW) | | | yes |

| | | |
|--------------------------------------|--|----------------------------|
| Information about equipment supplied | | 1 key included as standard |
|--------------------------------------|--|----------------------------|

Technical data

General

| | | | |
|--------------------------------------|--------------|-----------------|--|
| Standards | | | IEC/EN 60947-5-5 VDE 0660 |
| Lifespan, mechanical | Operations | $\times 10^6$ | > 0.05 |
| Operating frequency | Operations/h | | ≤ 300 |
| Actuating force | | n | ≤ 50 |
| Climatic proofing | | | Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30 |
| Degree of Protection | | | IP66, IP67, IP69 |
| Mounting position | | | As required |
| Terminal capacities | | mm ² | |
| Solid | | mm ² | 2 x 0.5 - 1.5 |
| Flexible with ferrule | | mm ² | 2 x 0.5 - 1.5 |
| Tightening torque for terminal screw | | Nm | 0.8 |

Contacts

| | | | |
|---|-----------|-------------------|---------------|
| Rated impulse withstand voltage | U_{imp} | V AC | 4000 |
| Rated insulation voltage | U_i | V | 250 |
| Rated conditional short-circuit current | I_q | kA | 1 |
| Overvoltage category/pollution degree | | | III/3 |
| Control circuit reliability | | | |
| at 24 V DC/5 mA | H_F | Fault probability | values follow |
| at 5 V DC/1 mA | H_F | Fault probability | values follow |
| Max. short-circuit protective device | | | |
| Fuse | gG/gL | A | 10 |


Technical data ETIM 7.0

| | | | |
|--|--|----|------------------|
| Low-voltage industrial components (EG000017) / Emergency stop complete (EC002034) | | | |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / EMERGENCY-STOP pushbutton, complete device (ecI@ss10.0.1-27-37-12-44 [ACN986011]) | | | |
| Unlocking method | | | Key-release |
| Number of contacts as normally closed contact | | | 2 |
| Number of contacts as normally open contact | | | 0 |
| Degree of protection (IP) | | | Other |
| Mounting method | | | Built-in |
| With lighting | | | No |
| Hole diameter | | mm | 22.5 |
| Connection type auxiliary circuit | | | Screw connection |
| Diameter cap | | mm | 60 |

Approvals

| | | | |
|-----------------------------|--|--|--|
| Product Standards | | | IEC/EN 60947-5-1; UL 508; CAN/CSA-C22.2 No. 14-05 und 94-M91; CE marking |
| UL File No. | | | E29184 |
| UL Category Control No. | | | NKCR |
| CSA File No. | | | 165628 |
| CSA Class No. | | | 321103 |
| North America Certification | | | UL listed, CSA certified |
| Degree of Protection | | | 1,3R,4X,12,13 |

Dimensions



Additional product information (links)

DGUV Test Mark Customer Information

http://www.dguv.de/medien/dguv-test-medien/_pdf_zip_doc_ppt/agb-und-pzo/dguv_test_zeichen_infoblatt_kunden.pdf