

H TIMING BELTS

0.500" Pitch


Standard Widths:

3/4", 1", 1-1/2", 2", 3"

Neoprene Construction

Fiberglass Reinforcements

(Note: Custom belt widths are available upon request.)



Timing Belts



Part Number	No. of Teeth	Pitch Length (in)
185H	37	18.500
210H	42	21.000
225H	45	22.500
230H	46	23.000
240H	48	24.000
245H	49	24.500
255H	51	25.500
270H	54	27.000
280H	56	28.000
300H	60	30.000
310H	62	31.000
315H	63	31.500
320H	64	32.000
330H	66	33.000
335H	67	33.500
340H	68	34.000
350H	70	35.000
360H	72	36.000
370H	74	37.000
375H	75	37.500
390H	78	39.000
395H	79	39.500
400H	80	40.000

Part Number	No. of Teeth	Pitch Length (in)
410H	82	41.000
415H	83	41.500
420H	84	42.000
430H	86	43.000
440H	88	44.000
445H	89	44.500
450H	90	45.000
455H	91	45.500
465H	93	46.500
480H	96	48.000
485H	97	48.500
490H	98	49.000
495H	99	49.500
510H	102	51.000
520H	104	52.000
525H	105	52.500
530H	106	53.000
540H	108	54.000
555H	111	55.500
560H	112	56.000
565H	113	56.500
570H	114	57.000
580H	116	58.000

Part Number	No. of Teeth	Pitch Length (in)
585H	120	60.000
600H	120	60.000
605H	121	60.500
615H	123	61.500
630H	126	63.000
640H	128	64.000
645H	129	64.500
650H	130	65.000
655H	131	65.500
660H	132	66.000
670H	134	67.000
680H	136	68.000
700H	140	70.000
730H	146	73.000
750H	150	75.000
760H	152	76.000
770H	154	77.000
775H	155	77.500
780H	156	78.000
800H	160	80.000
810H	162	81.000
820H	164	82.000
840H	168	84.000

Neoprene H timing belt part numbers can be determined as follows:
Pitch Length Code + H + Width Code + (G for fiberGlass reinforcements)