

H TIMING BELTS

0.500" Pitch


Standard Widths:

3/4", 1", 1-1/2", 2", 3"

Neoprene Construction

Fiberglass Reinforcements

(Note: Custom belt widths are available upon request.)



Part Number	No. of Teeth	Pitch Length (in)
850H	170	85.000
860H	172	86.000
880H	176	88.000
885H	177	88.500
900H	180	90.000
950H	190	95.000
960H	192	96.000
985H	197	98.500
1000H	200	100.000
1020H	204	102.000
1040H	208	104.000


Part Number	No. of Teeth	Pitch Length (in)
1050H	210	105.000
1100H	220	110.000
1120H	224	112.000
1130H	226	113.000
1140H	228	114.000
1170H	234	117.000
1180H	236	118.000
1250H	250	125.000
1320H	264	132.000
1325H	265	132.500
1345H	269	134.500

Part Number	No. of Teeth	Pitch Length (in)
1350H	270	135.000
1365H	273	136.500
1400H	280	140.000
1460H	292	146.000
1510H	302	151.000
1645H	329	164.500
1680H	336	168.000
1700H	340	170.000

Neoprene H timing belt part numbers can be determined as follows:
Pitch Length Code + H + Width Code + (G for fiberGlass reinforcements)



For H pitch pulley stock and flanges, see page 270.



For matching H pitch timing pulleys, see page 48.