

# 8 MM POWERHOUSE™ HTD® BELTS

Standard Widths:

20 mm, 30 mm, 50 mm, 85 mm

Neoprene Construction

Fiberglass Reinforcements

(Note: Custom belt widths are available upon request.)



Part Number	No. of Teeth	Pitch Length (mm)
320-8M	40	320.0
360-8M	45	360.0
376-8M	47	376.0
384-8M	48	384.0
424-8M	53	424.0
432-8M	54	432.0
472-8M	59	472.0
480-8M	60	480.0
512-8M	64	512.0
520-8M	65	520.0
536-8M	67	536.0
560-8M	70	560.0
576-8M	72	576.0
592-8M	74	592.0
600-8M	75	600.0
608-8M	76	608.0
624-8M	78	624.0
632-8M	79	632.0
640-8M	80	640.0
656-8M	82	656.0
672-8M	84	672.0
680-8M	85	680.0
712-8M	89	712.0

Part Number	No. of Teeth	Pitch Length (mm)
720-8M	90	720.0
760-8M	95	760.0
776-8M	97	776.0
784-8M	98	784.0
800-8M	100	800.0
824-8M	103	824.0
840-8M	105	840.0
848-8M	106	848.0
856-8M	107	856.0
880-8M	110	880.0
896-8M	112	896.0
912-8M	114	912.0
920-8M	115	920.0
936-8M	117	936.0
960-8M	120	960.0
968-8M	121	968.0
976-8M	122	976.0
1000-8M	125	1000.0
1040-8M	130	1040.0
1056-8M	132	1056.0
1064-8M	133	1064.0
1080-8M	135	1080.0
1096-8M	137	1096.0

Part Number	No. of Teeth	Pitch Length (mm)
1104-8M	138	1104.0
1120-8M	140	1120.0
1128-8M	141	1128.0
1136-8M	142	1136.0
1152-8M	144	1152.0
1160-8M	145	1160.0
1176-8M	147	1176.0
1184-8M	148	1184.0
1192-8M	149	1192.0
1200-8M	150	1200.0
1216-8M	152	1216.0
1224-8M	153	1224.0
1248-8M	156	1248.0
1256-8M	157	1256.0
1264-8M	158	1264.0
1280-8M	160	1280.0
1304-8M	163	1304.0
1320-8M	165	1320.0
1328-8M	166	1328.0
1344-8M	168	1344.0
1360-8M	170	1360.0
1392-8M	174	1392.0
1400-8M	175	1400.0

Neoprene 8 mm POWERHOUSE™ HTD® timing belt part numbers can be determined as follows:  
Pitch Length Code + -8M- + Width Code