



# BEVERAGE-AIR

Project: _____	AIA#
Item: _____	
Location: _____	SIS#
Approved: _____	

## SCHOOL MILK COLD WALL COOLER

SM49HC Single Access Cooler  
Hydrocarbon Series

**MODELS:**  
SM49HC-S  
SM49HC-W



**3 Year Parts/Labor Warranty**  
**Additional 4 Year Compressor Warranty**

### CABINET CONSTRUCTION

- SS units: Stainless steel exterior and interior
- White units: White coated steel exterior. Interior features a one-piece, stainless steel back, front, floor with galvanized side walls for maximum milk crate support
- Stainless steel lids, hinges doors and door latches
- Full electronic control
- Heavy-duty epoxy coated steel wire floor racks standard
- Floor drain is centrally located for easy cleaning, connecting to drain hose with hose adapter
- Flexible compression door gaskets ensure tight seal
- Self-latching doors/lids with safety bumpers
- Exterior thermometer
- Cylinder lock
- 4" Heavy-duty plate casters (2 with locks)
- Maintains product temperature between 36° to 40°F
- Cold wall milk coolers are designed to hold product temperature during service. Product should be removed at the end of service and moved to long-term, refrigerated storage

### OPTIONS & ACCESSORIES

- Stainless steel interior on white models -02
- Corner bumpers
- Graphics

### REFRIGERATION SYSTEM

- Uses environmentally friendly, energy efficient R290 refrigerant, and meets all regulatory requirements for CARB, SNAP, DOE & more

**SM49HC SINGLE ACCESS, COLD WALL: SCHOOL MILK SERIES**



Please verify qualifying units by visiting:  
[www.energystar.gov/cfs](http://www.energystar.gov/cfs)

3779 Champion Blvd., Winston-Salem, NC 27105  
1-888-845-9800 Fax: 1-336-245-6453  
Beverage-Air.com Sales@bevair.com




# BEVERAGE-AIR

MODEL		SM49HC (white & stainless steel models)
<b>EXTERNAL DIMENSIONAL DATA</b>		
Width Overall		49"
Depth Overall		30 <sup>5</sup> / <sub>8</sub> "
Height Overall with Casters		41 <sup>1</sup> / <sub>8</sub> "
Number of Lids/Doors		Single Access
<b>INTERNAL DIMENSIONAL DATA</b>		
NET Capacity (cubic ft.)		20.32
Internal Width Overall (in)		46"
Internal Depth Overall (in)		27"
Internal Height Usable (in)		25 <sup>3</sup> / <sub>4</sub> "
<b>CASE CAPACITY</b>		
13" X 13" 11"		12
19" X 13" 11"		8
<b>ELECTRICAL DATA</b>		
Full Load Amperes		2.2
<b>REFRIGERATION DATA</b>		
Horsepower		1/3
Capacity (BTU/Hr)*		1367
<b>SHIPPING DATA</b>		
Gross Weight - Crated		339 lbs
Height - Crated		48"
Width - Crated		33"
Depth - Crated		52"


## School Milk Cooler

Model: SM49HC


### Model Views



### PLAN VIEW



### ELEVATION VIEW



### SIDE VIEW

### \*ELECTRICAL CONNECTION



115/60/1  
NEMA 5-15P

Units pre-wired at  
factory and include 8'  
long cord and plug set.



3779 Champion Blvd., Winston-Salem, NC 27105 1-888-845-9800 Fax: 1-336-245-6453 Beverage-Air.com Sales@bevoir.com

an Ali Group Company



The Spirit of Excellence