

Declaration of Compliance

Business Operator

Vikan A/S
Rævevej 1
DK-7800 Skive
(+45) 96 14 26 00

Product name

Wall-/Floor Washing Brush, 18.5", Stiff, Green

Item Number

70622



Plastic Material

Polypropylene, 97 %

Color masterbatch

Green, 2 %

Foaming agent

Chemical foaming agent, 1 %

Bristles

Polybutylene terephthalate (PBT)

Stainless steel

The stainless steel staple is made from stainless steel Grade 1.4301 (AISI 304)

EU Compliance

Regulation (EC) No 1935/2004

In accordance with EU Commission Regulation no. 1935/2004 article 3, 11(5), 15 and 17 the product is intended for food contact. The product is marked with the "glass & fork" symbol on the packaging or on the product itself through moulding.

The stainless steel comply with European Standard EN 10088 and the specific release limits (SRLs) set out in the Council of Europe guide: "Metals and alloys used in food contact materials and articles".



AP(89)1

All pigments in the masterbatch comply with resolution AP 89(1)

Regulation (EC) No 2023/2006

The product is produced according to EU Commission Regulation no. 2023/2006 of 22. December 2006 on good manufacturing practices for materials and articles intended to come into contact with food (GMP).

Regulation (EU) No 10/2011

Monomers and intentionally added additives used to manufacture this product are listed in Annex I of Commission Regulation (EU) No. 10/2011 of 14. January 2011 on plastic materials and articles intended to come into contact with foodstuffs. Subsequent amendments up to (EU) 2023/1627 are included.

Monomers and/or additives with specific migration limit (SML) are used. The substances with a SML will not migrate in quantities that will exceed the SML, under the specified conditions of use. Upon request we will supply relevant information regarding these substances on a confidential basis.

Vikan A/S does not use multi-layer materials or articles with a functional barrier.



Regulations (EC) No 1333/2008
and (EC) No 1334/2008

This material contains intentionally added "dual use" additives for which restrictions or purity criteria are in place in accordance with Regulations (EC) 1333/2008 and (EC) 1334/2008. Upon request we will supply relevant information regarding these substances on a confidential basis.

US FDA Compliance

All raw materials in this product are in compliance with FDA (Food and Drug Administration in the USA) 21 CFR parts 170 to 199.

The polymers and additives complies with FDA 21 CFR part 174, 175, 176, 177, 178, 181, 182, 184, or 186. Additives are cleared according to FDA 21 CFR Part 178 (Indirect food additives), are generally recognised as safe (GRAS), are prior-sanctioned food ingredients, or are cleared on basis of regulations for food additives of before 1958.

The polypropylene complies with FDA 21 CFR 177.1520 "olefin polymers".

The PBT bristles comply with FDA 21 CFR 177.1660 „Poly(tetramethylene) terephthalate“.

The pigments in the masterbatch are listed under FDA 21 CFR 178.3297 „Colorants for Polymers“.

The stainless steel in this product is in compliance with FDA (Food and Drug Administration in the USA) Food Code 2017 and is listed in NSF/ANSI 51-2014 on Food Equipment Materials

UK Compliance

The product complies with The Materials and Articles in Contact with Food (Amendment) (EU Exit) Regulations 2019 No. 704.

Danish Compliance

The product complies with the Danish consolidation Act no. 681 of 25/05/2020.

Japanese Compliance

All substances (polymers, monomers and additives) used in Vikan products comply with Article 18(3) of the Japanese Food Sanitation Act and are listed in Tables 1 and 2 of Appendix 1 of the Positive List.

Migration analysis plastics

Samples of the product, or a similar product made from identical plastic material, have been tested for overall migration according to the test conditions specified in (EU) 10/2011, and the article comply with the overall migration limit of 10 mg/dm² or 60 mg/kg.

Test conditions for overall migration were OM3 (2 h at 70 °C)

Food simulants used for overall migration were 10 % ethanol (simulant A), 3 % acetic acid (simulant B) and olive oil (simulant D2).

Compliance with specific migration limits, and other restrictions, has been documented through testing, calculation or simulation.

Test conditions for specific migration was 30 min at 80 °C

Max ratio of food contact surface
area to volume

2.0 dm²/100 ml

Food contact types

The product is suitable for contact with the following types of food under the intended and foreseeable conditions of use:



- ☒ Aqueous
- ☒ Acidic
- ☒ Alcoholic
- ☒ Fatty
- ☒ Dry

Food contact usage time and temperature

Any food contact conditions up to 80 °C for 30 min

Non-food contact usage temperature

Minimum temperature: -20 °C
Maximum temperature: 100 °C

General

Equipment should be cleaned, disinfected and sterilised, as appropriate to its intended use, before use.

It is also important to clean, disinfect and sterilise equipment as appropriate after use, using the appropriate decontamination chemicals, concentrations, times and temperatures.

Appropriate equipment decontamination will minimise the risk of microbial growth and cross contamination and will maximise the efficiency and durability of the equipment.

Recommended sterilisation temperature (Autoclave): 121 °C

We will make the relevant background documentation available to the competent authorities, at their request.

Vikan A/S is registered with the Danish Veterinary and Food Administration (DVFA), and our mandatory Own Control System is subject to inspection by the DVFA.

Date

2024-05-31

Made By

Kim Gerhardt Aakermann
Materials & Compliance Specialist