

3 MM POWERHOUSE™ HTD® BELTS

Standard Widths:

6 mm, 9 mm

Neoprene Construction

Fiberglass Reinforcements

(Note: Custom belt widths are available upon request.)



Timing Belts



Part Number	No. of Teeth	Pitch Length (mm)
900-3M	300	900.0
915-3M	305	915.0
936-3M	312	936.0
945-3M	315	945.0
951-3M	317	951.0
960-3M	320	960.0
981-3M	327	981.0
1002-3M	334	1002.0
1026-3M	342	1026.0
1035-3M	345	1035.0
1038-3M	346	1038.0
1041-3M	347	1041.0
1050-3M	350	1050.0

Part Number	No. of Teeth	Pitch Length (mm)
1056-3M	352	1056.0
1062-3M	354	1062.0
1068-3M	356	1068.0
1071-3M	357	1071.0
1080-3M	360	1080.0
1110-3M	370	1110.0
1125-3M	375	1125.0
1155-3M	385	1155.0
1176-3M	392	1176.0
1188-3M	396	1188.0
1191-3M	397	1191.0
1227-3M	409	1227.0
1245-3M	415	1245.0

Part Number	No. of Teeth	Pitch Length (mm)
1260-3M	420	1260.0
1263-3M	421	1263.0
1335-3M	445	1335.0
1500-3M	500	1500.0
1512-3M	504	1512.0
1530-3M	510	1530.0
1569-3M	523	1569.0
1587-3M	529	1587.0
1800-3M	600	1800.0
1863-3M	621	1863.0
1926-3M	642	1926.0
1956-3M	652	1956.0
2004-3M	668	2004.0

Neoprene 3 mm POWERHOUSE™ HTD® timing belt part numbers can be determined as follows:
Pitch Length Code + -3M- + Width Code



For 3 mm POWERHOUSE™ HTD® pitch pulley stock and flanges, see page 288.



For 3 mm POWERHOUSE™ HTD® pitch timing pulleys, see page 90.