

# H TIMING PULLEY BAR STOCK

0.500" Pitch

Steel



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
14H-PS10S	14	56.6 mm	55.2 mm	2.228"	2.174"	0.750"	0.750"	10.000"	10.750"
15H-PS10S	15	60.6 mm	59.3 mm	2.387"	2.333"	0.750"	0.750"	10.000"	10.750"
16H-PS10S	16	64.7 mm	63.3 mm	2.546"	2.492"	1.000"	1.000"	10.000"	11.000"
17H-PS10S	17	68.7 mm	67.4 mm	2.706"	2.652"	1.000"	1.000"	10.000"	11.000"
18H-PS10S	18	72.8 mm	71.4 mm	2.865"	2.811"	1.000"	1.000"	10.000"	11.000"
19H-PS10S	19	76.8 mm	75.4 mm	3.024"	2.970"	1.000"	1.000"	10.000"	11.000"
20H-PS10S	20	80.8 mm	79.5 mm	3.183"	3.129"	1.000"	1.000"	10.000"	11.000"
21H-PS10S	21	84.9 mm	83.5 mm	3.342"	3.288"	1.000"	1.000"	10.000"	11.000"
22H-PS10S	22	88.9 mm	87.6 mm	3.501"	3.447"	1.000"	1.000"	10.000"	11.000"
23H-PS10S	23	93 mm	91.6 mm	3.662"	3.608"	1.000"	1.000"	10.000"	11.000"
24H-PS10S	24	97 mm	95.7 mm	3.820"	3.766"	1.000"	1.000"	10.000"	11.000"
25H-PS10S	25	101.1 mm	99.7 mm	3.980"	3.926"	1.000"	1.000"	10.000"	11.000"
26H-PS10S	26	105.1 mm	103.7 mm	4.138"	4.084"	1.000"	1.000"	10.000"	11.000"
27H-PS10S	27	109.2 mm	107.8 mm	4.299"	4.245"	1.000"	1.000"	10.000"	11.000"
28H-PS10S	28	113.2 mm	111.8 mm	4.456"	4.402"	1.000"	1.000"	10.000"	11.000"
29H-PS10S	29	117.3 mm	115.9 mm	4.617"	4.563"	1.000"	1.000"	10.000"	11.000"



Our veteran sales staff is available to help you make informed decisions on which precision mechanical or power transmission components are best for your project.

Let us help you!  
Call us today!

