

14 MM OPEN ENDED POWERHOUSE™ HTD® BELTS

Standard Widths:
40 mm, 55 mm, and 85 mm
Neoprene Construction
Fiberglass Reinforcements




Part Number	Width	Net Weight per Foot	Maximum Continuous Length
LL14M40	40 mm	.26	392 feet
LL14M55	55 mm	.35	392 feet
LL14M85	85 mm	.55	392 feet

Open ended belting is a money-saving, low upkeep alternative to roller chain and is most effective in long length conveying and positioning applications requiring protection from grime, grease, oil, and moisture.

14 MM POWERHOUSE™ HTD® CLAMPING PLATE

Standard Widths:
25 mm, 40 mm, 55 mm, 85 mm, 100 mm,
115 mm, 170 mm
Aluminum



Part Number	For Belt Width (mm)
CP-14M-25	25 mm
CP-14M-40	40 mm
CP-14M-55	55 mm

Part Number	For Belt Width (mm)
CP-14M-85	85 mm
CP-14M-100	100 mm
CP-14M-115	115 mm
CP-14M-170	170 mm

B&B Manufacturing offers an online, interactive competitor's part number cross reference tool on our website.

This powerful cross reference tool is intended to be used to determine an equivalent B&B Manufacturing part number given another manufacturer's part number. Most major precision mechanical component and power transmission manufacturers and distributors are included in this utility.

For this and other useful tools, visit our website at www.bbman.com.