



SKU # RS-16FT-5050-RGB

Part # 1003760

Description

16ft (5M) 20-Color RGB Multi-Color 5050 LED Custom Tape Strip w/ Remote - Includes NEW Heavy Duty 3M adhesive backing IP66

Categories

Golf Cart Lighting, Auto Interior & Exterior, LED Tape Strip Lighting, Marine Sport Lighting

Sub-Categories

Interior Accent Lighting, LED Tape & POD strips, 5050 Professional Tape Strip Reels, Interior Tape Strip LED

UPC 817363013963

Unit of Measure EA

Related Skus:
RSBHT01

Cross Sell Skus:

Condition	Manufacturer	EZ Category
New	Race Sport Lighting	5050 Tape Strip Lighting

Harmonization Code	Universal	Life Expectancy
8512.20.2080	YES	30,000 hours

SEMA Product	Interior Accent Light	Part Type ID	18826
--------------	-----------------------	--------------	-------

Reverse Polarity	Operating Voltage	Current Draw
Interior Accent Light	12VDC	

Wattage	Chip Type	IP Rating	LUX
		IP65	

Kelvin (ColorTemperature)	Universal or Vehicle Specific
RGB	Universal

Made In	Warranty	Lumens	Beam Pattern
China	1 year		Linear



Product Information

Super bright, universal lighting solution for your home, office, business, or any other application • 120° viewing angle, perfect for any area • Able to be cut at 3 LED intervals (approximately every 2") for virtually any application • Maintenance free, easy installation • Improved adhesive backing for better, longer lasting application • 100,000+ hour lifetime • IP65 Water Resistant • 1 Year Warranty

Est. Labor	Hours		
Gross Weight	2.20	Width	7.50
Net Weight	1.90	Height	2.00
DIM Weight	1.08	Depth	10.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov