

158 GPM

Features



EXTENDED RUN FUEL TANK

7.5 Hours run time**



HOSE KIT

Complete kit to get the water moving



WIDE PRIMING CAP

For quick startup



SILICON CARBIDE

Durable mechanical seal



0.5 in. SOLID WASTE

Handles solid waste up to 0.5 in. diameter



Specifications

PORT DIAMETER (in.)	2
PORT CONNECTION TYPE	NPT
DISCHARGE RATE (gal/min)	158
TOTAL HEAD (ft.)	92
SUCTION HEAD (ft.)	26
SOLIDS HANDLING (in.)	0.5
ENGINE SIZE (cc)	212
GASOLINE CAPACITY (gal.)	3
OIL TYPE	10W-30
OIL CAPACITY (fl. oz)	16.9

Champion's 2-inch Semi-Trash Water Transfer Pump includes everything you need except oil and gas to start pumping. Pump up to 158 gallons per minute, powered by the 212cc Champion OHV engine. The included complete hose kit provides everything you need to get your pump into action, including a 12-foot suction hose with filter, 25-foot discharge hose, quick cam lock coupler, clamps, adapters, fittings, nylon tape, along with a handy accessory bag to keep everything organized.

Inside the box

WATER PUMP	ADAPTERS	ACCESSORY BAG
12 FT. SUCTION HOSE	FITTINGS	OIL FUNNEL
25 FT. DISCHARGE HOSE	WHEEL KIT	OPERATOR'S MANUAL
CLAMPS		

What You Need

GASOLINE
ENGINE OIL (10W-30)
WRENCH/SOCKET SET

*Specifications, descriptions and illustrations are subject to change without notice. **Run time is for operation at 100% load.



PACKAGE (gross)
Weight: 86 lb.
Size: 25.4 x 21.9 x 19.9 in.



PRODUCT (net)
Weight: 62 lb.
Size: 21.1 x 16.5 x 21.3 in.

CHAMPION POWER EQUIPMENT, INC.
12039 Smith Ave., Santa Fe Springs, CA 90670, USA
www.championpowerequipment.com – Made In China