

## MRC21

### PARTS LIST

ITEM#	PART #	DESCRIPTION	08/01/14	GENERAL INFORMATION
1	40050	TUB WELDMENT	238.09	OVERALL DIMENSIONS 22-3/4"Lx16-3/4"W
2	40046	LEFT FIRE COVER	90.52	CLEANING CHAMBER 21"Lx15"Wx6-1/4"D
3	40047	RIGHT FIRE COVER	90.52	HEIGHT (LID OPEN) 48 1/2"
4	40016	LEFT LATCH BAR	20.27	SOLVENT CAPACITY 1.5 GAL MINIMUM
5	40017	RIGHT LATCH BAR	20.27	4.5 GAL MAXIMUM
6	12472	FUSIBLE LINK	8.85	PUMP SPECIFICATIONS 170 GAL PER HOUR
	99-12472-5	FUSIBLE LINK (5 PACK)	33.18	ELECTRICAL REQUIRED 120V/60Hz/.6AMP
7	40028	ELECTRICAL ASSEMBLY	81.97	SILL WORKING HEIGHT 37 1/2"
8	10848	POWER CORD	14.57	SHIPPING WEIGHT 56 POUNDS
9	40033	FLOW THRU BRUSH ASSY	54.20	
10	10568	3" LOCKING CASTER	15.32	
11	13284	RESERVOIR PAIL	52.54	
12	13288	RESERVOIR LEVER LOCK	19.82	
13	20132	RESERVOIR LID (DRILLED)	16.36	
14	14600	170 GPH PUMP & PLUG	123.54	
15	14544	PUMP PLUG ONLY	8.41	
16	40048	1/2" X 9" PUMP PIPE	24.92	
17	10808	1/2" CONDUIT LOCKNUT	0.90	
18	40045	3/4" X 6" DRAIN PIPE	15.61	
19	10800	3/4" CONDUIT LOCKNUT	0.90	
20	10638	#16 ADJUSTABLE HOSE CLAMP	1.81	
21	11664	RE-USABLE CLOTH FILTER BAG	4.66	
22	15856	1/4" FLOW REGULATING VALVE	21.02	
23	20349	1/2"ID x 1-1/2"OD WASHER	0.53	
24	11936	1/4"MNPT x 3/8" HOSE BARB	1.65	
25	10680	#170 EAR CLAMP	0.90	
26	15824	1/2" x 12"L CONNECTOR HOSE	3.91	

