



## Connected Smart-UPS with APC SmartConnect The First Cloud-enabled UPS For Distributed IT

### The world's most popular network and server UPS

APC™ award-winning Smart-UPS™ is the most popular UPS in the world for servers, storage and network power protection. Smart-UPS provides availability and manageability to your network allowing you to focus on business growth instead of business downtime. Trusted to protect critical data and equipment from power problems by supplying clean and reliable network-grade power.

Connected Smart-UPS units boast an ingenious networking feature that makes Smart-UPS even more adaptable and easier to deploy: APC SmartConnect — a feature which allows you to view the status of your UPS through a secure web portal. Through this innovative remote monitoring interface, you'll receive automatic notifications, firmware updates, and advanced support. APC SmartConnect's easy-to-use network connectivity provides added value — and more important — added peace of mind.

Life Is On 

**APC**<sup>®</sup>  
by Schneider Electric

# The world's most popular UPS just got smarter

Connected Smart-UPS is here:



## APC SmartConnect Enabled:

- Accessible from any internet connected device, on site or mobile
- Simple account login and Registration
- Proactive actionable alerts and lifecycle recommendations
- Compatible with major RMM platforms
- No special software, SNMP trap or coding required
- Connected Smart-UPS adhere to the latest industry standards in secure data collection

## Connected Smart-UPS Features:

### APC SmartConnect

APC SmartConnect is a proactive remote UPS cloud monitoring feature that is accessible from any internet connected device

### Pure Sinewave

Instant backup battery power with pure sinewave output during a power outage

### Intelligent Battery Management

Temperature compensated charging extends life and advanced algorithms recommend replacement date

### High-efficiency Greenmode

Optimum efficiency which saves utility and cooling costs

### Network-grade Power

Provides stable power conditions by filtering noise, automatic voltage regulation (AVR), and surge protection

### Emergency Power Off (EPO)

Provides for remote UPS shut-off in the event of a fire or other emergency (2,200 VA and above)

## Getting Started is Easy



### 1 Install your UPS

Install your SmartConnect-compatible UPS at your business site. Connect it to your network using a dedicated ethernet port.



### 2 Scan the QR code

Scan the QR Code printed on your Smart-UPS, and automatically register your device with the SmartConnect Web Portal.



### 3 Register your UPS

Create a Schneider Electric account to register your Smart-UPS. Your UPS will be automatically linked to your account.

## Certainty in a Connected World

Life Is 

**APC**<sup>®</sup>

by Schneider Electric

# Connected Smart-UPS SMC Features

Application optimized models ideal for entry level servers, point-of-sale (POS) and other small network devices



## APC SmartConnect

Proactive remote UPS cloud monitoring feature that is accessible from any internet connected device

## Pure Sine-wave Output

Simulates the utility when on battery for optimum device compatibility

## Advanced Battery Management

Temperature compensated charging extends life of internal batteries

## High Efficiency Green Mode

Save utility costs and reduces heat promoting longer component life

## Network Grade Power Conditioning

Automated voltage regulation (AVR), noise filtering and surge protection

## LCD Display

Intuitive interface provides comprehensive status information at a glance

## Communication Ports

USB and serial ports for UPS management

## Safety-agency Approved

Ensures the product has been tested and approved to national standards

## Generous Number of Outlets

All receptacles are surge and UPS protected

## Battery Disconnect

Convenient way to disconnect battery for transport (Tower models)




# Connected Smart-UPS SMC

The most affordable true sine-wave UPS's in the Smart-UPS family . Designed for entry level servers, it is compatible with today's active power factor corrected (PFC) power supplies.

Life Is 

**APC**<sup>®</sup>  
by Schneider Electric



## Connected Smart-UPS SMC Display

Comprehensive LCD interface for status at a glance



### LCD display

Comprehensive status at a glance

#### Status conditions:

- On line
- On battery
- Green mode
- Load graph
- Battery charge graph
- Audible alarm

#### Measure:

- Input & output voltage
- Load viewable in watts, VA and percentage
- Output current and frequency
- Event counter
- Estimated on battery runtime

1 On line / On battery

2 On / Off button

3 System fault LED

4 Mute button

5 Display button

Life Is On

**APC**  
by Schneider Electric

# Connected Smart-UPS SMT Features

Intelligent and efficient network power protection from entry level to scalable runtime. Ideal for servers, point-of-sale, routers, switches, hubs, and other network devices.



## In addition to Smart-UPS SMC features:

### SmartSlot™ Interface

Accepts a wide array of accessory cards for advanced management and environmental monitoring

### Switched Outlet Group

Controlled separately from the UPS for discrete reboot of hung devices, sequenced ON/OFF, and non-critical load shedding

### Configurable, Multi-lingual LCD Display

Provides UPS status and key measures at a glance. Clear and accurate, menu-driven display for easy set-up and customization with or without software installation

### Extended-range Automatic Voltage Regulation

Provides enhanced brownout protection, boosting incoming voltage up to 30% without using battery power

### Rack-mount Rails

All hardware provided to securely install in your IT rack

### Emergency Power Off (EPO)


Provides for remote UPS shut-off in the event of a fire or other emergency (2,200 VA and above)



**Connected Smart-UPS**  
Advanced line-interactive power protection for servers and network equipment

Life Is On

**APC**  
by Schneider Electric



# Connected Smart-UPS SMT Display

## Intuitive, easy-to-use LCD interface



### LCD display screen

Clear, consistent, and detailed information in your choice of basic or advanced menus

### Power status

Operating mode, efficiency, load, input / output frequency, battery capacity, runtime and more

### Configuration

Easily configure: language, power quality, alarms, delay and threshold settings

### Test and diagnostics

Initiate battery and runtime calibration tests

### Control

UPS and outlet group settings

### Logs

See explanation of last 10 transfers and faults

### Quick status indicators

Online, on battery, fault, and replace battery LEDs for quick status identification

### Escape, return and navigation buttons

Intuitive navigation to confirm, exit or adjust settings

### Load energy meter

Track energy usage in kilo watt hours

Life Is On



# Connected Smart-UPS Management Solutions

## APC SmartConnect

Automatically included in Connected Smart-UPS units, APC SmartConnect is an ingenious connectivity feature that makes Smart-UPS even more adaptable and easier to deploy: APC SmartConnect allows you to view the status of your UPS through a secure web portal. Through this innovative remote monitoring interface, you will receive automatic notifications, firmware updates, and advanced support.



### APC SmartConnect features:

- No special software or gateway required
- Accessible from any internet connected device
- Compatible with major RMM platforms
- Actionable alerts and lifecycle recommendations
- Enhanced troubleshooting and support
- Simple account login and registration

---

## PowerChute Business Edition For graceful UPS shutdown

### Built-in manageability for your UPS unit

PowerChute Business Edition software provides UPS management, safe system shutdown, and innovative energy reporting capabilities. Energy usage, cost, and CO2 reporting provides a greater understanding of the energy consumed by IT equipment, enabling improved energy efficiency. Advanced analysis features help to identify the causes of potential power-related problems before they occur, ensuring the health of your protected equipment.



### PowerChute Business Edition features:

- Graceful system shutdown
- Fault notifications
- Risk-assessment reporting
- Scheduled shutdowns
- Energy-usage reporting
- Centralized monitoring
- Recommended actions
- Battery status
- Outlet-aware shutdown
- Event and data logging
- Power-event summary
- Voltage analysis

---

Life Is On

**APC**<sup>®</sup>  
by Schneider Electric

# Connected Smart-UPS Management Solutions

## UPS Network Management Cards

For remote management and control



Connect to your network and enjoy direct control

APC UPS network management cards allow for secure connection and control of an individual APC UPS unit via web browser, command-line interface, or SNMP. The configurable notification features keep you informed of problems as they occur. For protected servers, the included PowerChute Network Shutdown software provides graceful, unattended shutdown in the event of an extended power outage, always keeping business information safe.

### Network management card features:

- **Browser accessible:** View the user interface with a browser for quick access from anywhere, on a secure network
- **Remote device management:** Enable management of your UPS by connecting it directly to the network
- **Fault notification:** Get real-time event notifications, minimizing response time to critical physical infrastructure situations – reducing meaintenance to repair, improving efficiency, and maximizing uptime
- **Reboot equipment remotely:** Eliminate the need to dispatch technicians to remote locations

---

## PowerChute Network Shutdown

Provides graceful network-based shutdown of physical and virtual IT architectures

PowerChute Network Shutdown Edition software provides UPS management, safe system shutdown, and innovative energy reporting capabilities. Energy usage, cost, and CO2 reporting provides a greater understanding of the energy consumed by IT equipment, enabling improved energy efficiency. Advanced analysis features help to identify the causes of potential power-related problems before they occur, ensuring the health of your protected equipment.



### PowerChute Network Shutdown features:

- Graceful network-based shutdown
- Sequenced server shutdown
- Integration with VMware and Microsoft Hyper-V
- Support for virtual clusters
- Virtual machine migration / shutdown
- IPv6 support
- Virtual machine prioritization
- Command file integration
- Redundant and parallel UPS support
- Event logging
- HTTPS communications
- Scalable architecture for host of client systems

---

Life Is On

**APC**<sup>®</sup>  
by Schneider Electric



# Connected Smart-UPS Services and Accessories

Schneider Electric Critical Power & Cooling Services (CPCS) provides the highest quality services and solutions by trained and trusted professionals. Our world-class services offer a smart way to build, operate, and maintain your critical applications, ensuring the right people, in the right place, at the right time.

## Management cards

- **AP9630:** UPS Network Management Card
- **AP9631:** UPS Network Management card with environmental monitoring



AP9631

## Additional accessories

- **AP9625:** APC Smart-UPS two-post rail kit



AP9625

## Service bypass panels

- **SBP1500RM** : APC service bypass PDU, 120V; 15 amp with (8) NEMA 5-15R
- **SBP300RM** : APC service bypass PDU, 120V; 30 amp with (4) NEMA 5-20R
- **SBP3000**: APC service bypass panel, 100–240V; 30 amp; BBM; hard-wire input /output



SBP3000RM

Life Is 

**APC**<sup>®</sup>  
by Schneider Electric

# APC Smart-UPS SMC

## Tower Technical Specifications



### SMC1000C

### SMC1500C

#### Output

Power Capacity	600W / 1000VA	900W / 1440VA
Nominal Output Voltage	120V	
Output Frequency	47-63 Hz	
Wave Form Type	Pure Sine Wave	
Output Connections	(8) NEMA 5-15R	

#### Input

Nominal Input Voltage	120V	
Input Voltage Range for main operations (Max adjustable range)	92 – 132 V (85-136V)	
Input Frequency	50 / 60 HZ +/- 3 Hz (auto-sensing)	
Input Connection	NEMA 5-15P, 6ft cord	

#### Batteries and Runtime

Battery Type	Maintenance-free sealed lead-acid battery with suspended electrolyte	
Runtime at Half Load	14 min	11 min
Runtime at Full Load	5 min	4 min
Replacement Battery	APCRBC142	RBC6

#### Communication and Management

APC SmartConnect Enabled	Yes	
Interface Ports	USB and Serial (RJ45)	
Control Panel and Audible Alarms	Etched glass LCD display with LED status indicators; alarm on battery, distinctive low battery alarm	

#### Surge Protection Filtering

Surge Energy Rating (Joules)	455 J	
Filtering	Full time multi-pole noise filtering 0.3% IEEE surge let-through, zero clamping response time, meets UL1449	

#### Physical

Dimensions (H x W x D)	8.5 x 6.72 x 17.3 in	8.45 x 6.7 x 17.3 in
Net Weight	38 lbs.	45 lbs.

#### Conformance

Regulatory	UL 1778, CSA FCC Part 15 Class A, BSMI, NOM	
Warranty	2 years repair or replace for unit and battery	
Equipment Protection Policy	\$150,00 lifetime	

Life Is On

**APC**  
by Schneider Electric

# APC Smart-UPS SMC

## Rackmount Technical Specifications



	SMC1000-2UC	SMC1500-2UC
<b>Output</b>		
Power Capacity	600W/ 1000VA	900W / 1440VA
Nominal Output Voltage	120V	
Output Frequency	47-63 Hz	
Wave Form Type	Pure Sine Wave	
Output Connections	(6) NEMA 5-15R	
<b>Input</b>		
Nominal Input Voltage	120V	
Input Voltage Range for main operations (Max adjustable range)	106 – 130 V (97-136V)	
Input Frequency	50 / 60 HZ +/- 3 Hz (auto-sensing)	
Input Connection	NEMA 5-15P, 8ft cord	
<b>Batteries and Runtime</b>		
Battery Type	Maintenance-free sealed lead-acid battery with suspended electrolyte	
Runtime at Half Load	14 min	18 min
Runtime at Full Load	5 min	6 min
Replacement Battery	APCRBC124	APCRBC132
<b>Communication and Management</b>		
APC SmartConnect Enabled	Yes	
Interface Ports	USB and Serial (RJ45)	
Control Panel and Audible Alarms	Etched glass LCD display with LED status indicators; alarm on battery, distinctive low battery alarm	
<b>Surge Protection Filtering</b>		
Surge Energy Rating (Joules)	455 J	
Filtering	Full time multi-pole noise filtering 0.3% IEEE surge let-through, zero clamping response time, meets UL1449	
<b>Physical</b>		
Dimensions (H x W x D)	3.5 x 18.9 x 16.0 in	3.5 x 18.9 x 18.0 in
Net Weight	38 lbs.	59 lbs.
<b>Conformance</b>		
Regulatory	UL 1778, CSA FCC Part 15 Class A, BSMI, NOM	
Warranty	2 years repair or replace for unit and battery	
Equipment Protection Policy	\$150,00 lifetime	

# APC Smart-UPS SMT

## Tower Technical Specifications



	SMT750	SMT1000	SMT1500	SMT2200	SMT3000
<b>Output</b>					
Power Capacity	500W / 750VA	700W / 1000VA	1000W / 1500VA	1980W / 2200VA	2700W / 3000VA
Nominal output voltage	120V				
Output frequency	47 – 53 Hz f or 50 Hz nominal; 57 – 63 Hz f or 60 Hz nominal				
Waveform type	Sine wave				
Output connections (NEMA)	(6) 5-15R	(8) 5-15R		(8) 5-15R, (2) 5-20R	
Switched outlet groups	N/A	1			
<b>Input</b>					
Nominal input voltage	120V				
Input voltage range for main operations (Max adjustable)	82 – 144 (75 – 154V)				
Input frequency	50 / 60 Hz +/- 3 HZ (auto-sensing)				
Input connection	5-15P			5-20P	L5-30P
<b>Batteries and runtime</b>					
Battery type	Maintenance-free sealed lead-acid battery with suspended electrolyte; leak proof				
Replacement battery	RBC48	RBC6	RBC7	RBC55	
<b>Runtime estimates</b>					
200W	:22	:45	1:24	2:17	2:29
500W	:05	:10	:23	:51	:55
700W	-	:06	:12	:34	:37
1000W	-	-	:07	:21	:23
1400W	-	-	-	:13	:14
1600W	-	-	-	:10	:12
Full load	:05	:06	:07	:07	:06
<b>Communications and management</b>					
APC SmartConnect Enabled	Yes				
Interface ports	Serial (RJ45), USB, and SmartSlot				
Control panel and audible alarms	Alpha-numeric LCD display with LED status indicators; alarm on battery, distinctive low battery alarm and configurable delays				
Emergency power off (EPO)	Optional			Yes	
<b>Physical</b>					
Maximum height (inches)	6.2	8.5	8.5	17.0	17.0
Maximum width (inches)	5.4	6.7	6.7	7.7	7.7
Maximum depth (inches)	14.1	17.3	17.3	21.5	21.5
Net weight (pounds)	29	42	53	11.2	116
<b>Conformance</b>					
Regulatory	UL 1778, CSA				
Warranty and equipment protection	3-year electronics, 2-year battery, and \$150,000 lifetime EPP				

Life Is On

**APC**  
by Schneider Electric

# APC Smart-UPS SMT

## Rackmount Technical Specifications



SMT750RM2U  
SMT750RM2UNC

SMT1000RM2U

SMT1500RM1U

SMT1500RM2U

SMT2200RM2U

SMT3000RM2U

### Output

Power Capacity	500W / 750VA	700W / 1000VA	1000W / 1500VA	1000W / 1500VA	1980W / 2200VA	2700W / 3000VA
Nominal output voltage	120V					
Output frequency	47 – 53 Hz for 50 Hz nominal; 57 – 63 Hz for 60 Hz nominal					
Waveform type	Sine wave					
Output connections (NEMA)	(6) 5-15R	(4) 5-15R	(6) 5-15R	(6) 5-15R, (2) 5-20R		
Switched outlet groups	1					

### Input

Nominal input voltage	120V					
Input voltage range for main operations (Max adjustable)	82 – 144 (75 – 154V)					
Input frequency	50 / 60 Hz +/- 3 HZ (auto-sensing)					
Input connection	5-15P			5-20P	L5-30P	

### Batteries and runtime

Battery type	Maintenance-free sealed lead-acid battery with suspended electrolyte; leak proof					
Replacement battery	APCRBC123	APCRBC132	APCRBC88	APCRBC133	RBC43	

### Runtime estimates

200W	:24	1:10	1:32	:27	1:24	1:26
500W	:05	:17	:26	:12	:35	:38
700W	-	:09	:14	:07	:24	:26
1000W	-	-	:07	:04	:15	:17
1400W	-	-	-	-	:09	:11
1600W	-	-	-	-	:07	:09
Full load	:06	:09	:07	:04	:05	:03

### Communications and management

APC SmartConnect Enabled	Yes	No	Yes			
Interface ports	Serial (RJ45), USB, and SmartSlot "NC" versions have AP9631 network management card pre-installed in the SmartSlot					
Control panel and audible alarms	Alpha-numeric LCD display with LED status indicators; alarm on battery, distinctive low battery alarm and configurable delays					
Emergency power off (EPO)	Optional				Yes	

### Physical

Maximum height (inches)	3.5	3.5	1.75	3.5	3.5	3.5
Maximum width (inches)	17.0	17.0	17.0	17.0	19.0	19.0
Maximum depth (inches)	16.0	18.0	26.0	18.0	27.0	17.0
Net weight (pounds)	38	62	53	63	93	97

### Conformance

Regulatory	UL 1778, CSA					
Warranty and equipment protection	3-year electronics, 2-year battery, and \$150,000 lifetime EPP					

Life Is On

**APC**  
by Schneider Electric