

# 325 Pink



## FROGTAPE® 325 PINK PERFORMANCE MASKING TAPE

SHURTAPE® PRODUCT TYPE: CP 325 PINK

### *Prep for Perfection™*

#### TYPICAL APPLICATIONS

- For demanding, high-temperature paint masking and metal fabrication applications in the transportation (auto, coaches, buses and marine) industry
- Also used for metal preparation, painting, coating and gel coat masking

#### PRODUCT FEATURES

- Medium-high adhesion
- Excellent adhesion to multiple surfaces and substrates, including metal, rubber, plastic and fiberglass
- Resistant to water, various solvents and gel coats
- Clean, flat edges for sharper paint lines
- Easy to unwind
- Highly conformable for rounding curves and contours
- Highly durable
- Temperature-resistant up to 325 F
- Residue-free removal
- Strong, smooth crepe paper backing is tear- and sliver-resistant
- UV-resistant for up to 3 days

#### CONSTRUCTION

- Overall Grade/Function: High Performance
- Backing: Fine structured crepe (FSC)
- Adhesive: Rubber-based

#### STANDARD WIDTH(S)

12 mm 18 mm 24 mm 36 mm 48 mm 72 mm

#### STANDARD LENGTH(S)

55 m

#### STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

#### COLOR(S)



#### PHYSICAL PROPERTIES

	STANDARD	METRIC
Tensile Strength	25 lbs/in width	43.8 N/10 mm
Adhesion to Stainless Steel	34 oz/in width	3.72 N/10 mm
Thickness	6.6 mils	0.17 mm
Elongation	12%	12%
Service Temperature Range	40 F to 325 F	4 C to 163 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

#### APPLICABLE STANDARDS

ASTM D 6123/D 6123M-97 (2012), Type I

DOES NOT  
contain  
PaintBlock®  
Technology



# Shurtape

TECHNOLOGIES