



6 MIL FENTANYL RESISTANT INDUSTRIAL BLACK NITRILE GLOVES

SINGLE USE HAND PROTECTION
SPECIFICATION SHEET



PRODUCT FEATURES:

- Fentanyl resistant
- Industrial grade
- 6 Mil black nitrile
- Provides incredible tensile strength, elongation, and puncture resistance
- Textured fingertips for improved grip
- Ambidextrous design with beaded cuff for easy donning and doffing
- Comfortable and durable for extended wear
- FDA 21 CFR for food handling

TECHNICAL DATA:

- Material:
 - 100% Nitrile
 - 100% Latex free
- Mil Thickness: 6 mil
- Color: Black
- Powder Free
- Beaded Cuff
- Textured Fingertips
- COO China

Physical Specifications				
	Size			
	S	M	L	XL
Hand Length	7.2-7.6 in	7.4-8.0 in	7.5-8.1 in	7.6-8.2 in
Palm Width	2.8 - 2.95 in	2.95 - 3.15 in	3.15 - 3.44 in	3.44 - 3.77in
Finger Length	2.65 - 2.7 in	2.7 - 2.75 in	2.75 - 2.8 in	2.8 - 2.85 in
Palm Circumference	7 - 8 in	8 - 9 in	9 - 10 in	10 - 11 in
Cuff Thickness	2.65 mil+/- 0.15mil	2.65 mil+/- 0.15mil	2.65 mil+/- 0.15mil	2.65 mil+/- 0.15mil
Palm Thickness	5.75 mil +/-0.25mil	5.75 mil +/-0.25mil	5.75 mil +/-0.25mil	5.75 mil +/-0.25mil
Finger Thickness	6 mils +/-0.2mil	6 mils +/-0.2mil	6 mils +/-0.2mil	6 mils +/-0.2mil

STANDARDS & COMPLIANCE:

- Fentanyl Resistant
- ASTM D6978
- ISO 10993 5,10 against irritation and sensitization
- FDA 21 CFR for food handling
- Drug List
 - Carmustine (BCNU), 3.3 mg/ml (3,300 PPM) 21.5
 - Cisplatin, 1 mg/ml (1,000 ppm) >240 min
 - Cyclophosphamide (Cytoxan), 20.0 mg/ml (20,000 ppm) >240 min
 - Dacarbazine, 10 mh/ml (10,000 ppm) >240 min
 - Doxorubicin HCl 2.0 mg/ml (2000 ppm)>240 min
 - Etoposide 20.0 mg/ml (20,000 ppm)>240 min
 - Fluorouracil 50.0 mg/ml (50,000 ppm)>240 min
 - Paclitaxel, 6.0 mg/ml (6,000 ppm)>240 min
 - Thiotepa, 10.0 mg/ml (10,000 ppm) 57.7 min

APPLICATIONS & CARE:

These thick nitrile gloves are the working professionals' choice! They are chemical rated, fentanyl resistant, 100% Latex-free and powder-free. Our gloves are manufactured for maximum protection and comfort. They meet and exceed cGMP standards for safety, quality, and strength. Featuring textured fingertips, improved dexterity and a more secure grip on slippery objects. These single use/disposable gloves are ideal for use in a multitude of industries such as first responders, tattoo artists, professionals, industrial, automotive, food handling, cleaning, and cosmetology.



NITRILE GLOVES

6 MIL FENTANYL RESISTANT INDUSTRIAL BLACK NITRILE GLOVES
SINGLE USE HAND PROTECTION
SPECIFICATION SHEET

Packaging and Logistics Information

SKU	SIZE	GLOVES PER BOX	BOXES PER CASE	PALLET QTY	CASE WT	UPC
DSG-BNS-02-S	S	100	10	70 CS	17.2 lbs.	069165847769
DSG-BNS-02-M	M	100	10	70 CS	18.8 lbs.	069165847776
DSG-BNS-02-L	L	100	10	70 CS	19.9 lbs.	069165847783
DSG-BNS-02-XL	XL	100	10	70 CS	21.7 lbs.	069165848216