

## Beverage & Frothing Thermometer

**Model: IRT220-F**

Color-coded target range indication. 5-inch stem. 1-inch magnified dial.  
Durable 304 stainless steel. Exclusive adjustable stainless steel vessel clip  
for small pitchers. Calibration tool and pocket clip on ABS sheath with BioCote<sup>®</sup>.  
Shatterproof lens. Safe for commercial dishwashers.



Features	Target range indication
Certification	NSF <sup>®</sup> Certified
Antimicrobial Protection	BioCote <sup>®</sup>
Measurement Range	0 to 220°F
Unit of Measure	°F
Accuracy	±2°F
Calibration	Field calibration
Water Resilience	Safe for commercial dishwashers
Response Time	15 second response (approximate)
Housing Material	304 stainless steel
Display Material	Shatterproof lens
Display Size	1 1/2" 2.5 cm magnified dial
Probe Type	Bimetal
Probe Material	304 stainless steel
Probe Length	5"/12.7 cm stem
Probe Diameter	3 mm tip
Resolution	2°F
Vessel Clip	Adjustable stainless steel clip AD-F
Casing	Sheath
Mounting	Pocket clip
Dimensions	1 W x 5.5 H x 1 D (in)/2.5 W x 14.0 H x 2.5 D (cm)
Weight	0.6 oz / 17 g
Warranty	5-Year Limited Warranty
Replacement Parts	AD-F