

COBALT
Fractional / Bronze



PACKAGING:
1/16" thru 9/32" - 12 per pack
5/16" thru 3/8" - 6 per pack

Series 300LH

135° SPLIT POINT / 3-FLAT SHANK

Constructed of M-42 Cobalt High Speed Steel for super abrasive resistance in tough metals. They are used in left hand screw machines and with screw extractors. Can be used to drill out broken bolts and other hardened fasteners. Sizes 3/16" and above have a 3-flat shank which reduces slippage in the drill chuck.




300LH



Size	Flute Length	Overall Length	300LH EDP No.
1/16"	5/8"	1-5/8"	300LH104
3/32"	3/4"	1-3/4"	300LH106
1/8"	7/8"	1-7/8"	300LH108
5/32"	1"	2-1/16"	300LH110
3/16"	1-1/8"	2-3/16"	300LH112

Size	Flute Length	Overall Length	300LH EDP No.
7/32"	1-1/4"	2-3/8"	300LH114
1/4"	1-3/8"	2-1/2"	300LH116
9/32"	1-1/2"	2-11/16"	300LH118
5/16"	1-5/8"	2-13/16"	300LH120
11/32"	1-11/16"	3"	300LH122
3/8"	1-13/16"	3-1/8"	300LH124



No. of Pcs.	Description	EDP No.
300LH Series Cobalt Screw Machine (Stub) Length Drill Sets		
11	1/16" - 3/8" BY 32nds	300LH11