



Item No.	H	L1	L2	Inner	W×H×D	g
001-0.71mm	0.71 (0.028")	8	34	—	—	—
001-0.89mm	0.89 (0.035")	10	34	—	—	—
001-1.27mm	1.27 (0.05")	14	46	—	—	—
001-1.4mm	1.4	11	50	—	—	—
001-1.5mm	1.5	12	52	—	—	—
001-2mm	2	12	58	—	—	—
001-2.5mm	2.5	15	60	—	—	—
001-3mm	3	20	65	—	—	—
001-3.5mm	3.5	22	68	—	—	—
001-4mm	4	25	72	—	—	—
001-4.5mm	4.5	27	76	—	—	—
001-5mm	5	28	80	—	—	—
001-5.5mm	5.5	30	85	—	—	—
001-6mm	6	32	90	—	—	—
001-7mm	7	34	95	—	—	—
001-8mm	8	36	100	—	—	—
001-9mm	9	38	106	—	—	—
001-10mm	10	40	112	—	—	—
001-11mm	11 (7/16")	42	118	—	—	—
001-12mm	12	45	125	—	—	—
001-13mm	13	57	132	—	—	—
001-14mm	14	55	140	—	—	—
001-15mm	15	63	150	—	—	—
001-16mm	16 (5/8")	57	153	—	—	—
001-17mm	17	60	160	—	—	—
001-18mm	18	70.5	170.5	—	—	—
001-19mm	19 (3/4")	70	175	—	—	—
001-20mm	20	72	185	—	—	—
001-21mm	21	75	198	—	—	—
001-22mm	22	80	200	—	—	—
001-23mm	23	85	210	—	—	—
001-24mm	24	90	225	—	—	—
001-26mm	26	95	245	—	—	—
001-27mm	27	100	250	—	—	—
001-30mm	30	120	290	—	—	—
001-32mm	32	125	315	—	—	—
001-36mm	36	130	320	—	—	—
001-41mm	41	140	390	—	—	—
001-46mm	46	155	410	—	—	—
001-50mm	50	170	430	—	—	—

Tool Type: Straight Type

Handle Type: L-Key

Measurement Type: Metric

Additional Information: L-Key Standard Length

Surface Treatment: Black Parkalized