

HydraTrans[™] \135

Product Description

D-A HydraTrans™ 135 is a proven premium grade transmission and hydraulic fluid providing superior performance for severe service off-highway applications. It is formulated from high-quality base stocks fortified with a high-performance additive system to extend component life and improve performance characteristics. D-A HydraTrans 135 supports the performance requirements for most major construction and agricultural equipment manufacturers, allowing users to stock one fluid to meet both transmission and hydraulic system needs.

Product Features and Benefits

Improves hydraulic pump and gear train life to help reduce maintenance costs.

Improved oxidation stability extends oil life.

Improved frictional properties prevent grabbing or chattering of wet brakes and PTO clutches.

Excellent water tolerance and low temperature fluidity provides protection in all working environments.

Provides rust and corrosion protection for all types of metal surfaces, increasing component life.

Supports the performance requirements of both hydraulic and transmission field service for major construction and agricultural equipment manufacturers reducing the need to inventory separate lubricants.

PRODUCT AT A GLANCE

- Premium Grade Tractor Fluid
- Transmission and Hydraulic Fluid
- Designed for use in Severe Service
- Supports the performance requirements for most major agricultural manufacturers











HydraTrans 135

Typical Applications - Supports the Performance Requirements of:

ACGO Power Fluid 821XL Allis Power Fluid 821 Deutz-Allis 272843, 25741, 246634 Massey Ferguson M1135, M1141, M1143, M1145 Massey Ferguson M1110, 1127A/B, M1129A

CNH

ESN-M2C134-A, B, C ESN-M2C86B, C ESN-M2C43 ESN-M2C41-B JIC 145, 143/144 MAT 3505/MS 1209 (Ultra) MAT 3525/FNHA-2-C-201/Ford ESN M2C134-A/B/C/D MAT 3526/FNHA-2-C-200A MS-1206, 1207, 1209, 1210, 1204

John Deere

J14B, J14C JDM J20A JDM J21A JDM J20C JDT 303

Kubota

Kubota UDT

Q1705, Q1802 Type 55

White Farm/MM/Oliver

Q1826, Q1766, Q1722, Q1766B

Others

Allison C-3, C-4 API GL-4 Komatsu Dresser B-06-0001 Sauer Danfoss (Sundstrand) Sperry-Vickers, I-286-S M-2950-S

Volvo WB101

ZF TEML 03E/05F/06K/17E

Typical Properties

Viscosity

@ 100°C, cSt	ASTM D445	9.5
@ 40°C, cSt	ASTM D445	61.8
@ -18°C, cP	ASTM D5293	3,720
@ -20°C, cP	ASTM D5293	3,800
@ -29°C, cP	ASTM D4684	19,200
@ -35°C, cP	ASTM D2983	57,000
Viscosity Index	ASTM D2270	135
Flash Point,		
°F	ASTM D92	425
°C	ASTM D92	218
APIGravity	ASTM D287	28.0
Pour Point, °C	ASTM D6749	-40
D-A Part Numbers:	Bulk	57501
	Drum, 55 Gal	57502
	Quarter Drum, 16 Gal	57506
	Pail, 5 Gal	57508

To Order D-A Products, Call 1-800-OIL-LUBE (1-800-645-5823) or Fax orders to 765-482-3065 D-A Lubricant Company, Inc.

801 Edwards Drive, Lebanon, IN 46052 • TEL: 317.923.5321 • FAX: 765.482.3065

Email: dalube@dalube.com • www.dalube.com

DA-HT135 rev 7/2015 new 4/03 All Rights Reserved.

© 2015. D-A Lubricant Company, Inc.