


Item No.	Pcs.	H					Inner	W×H×D	g
018-S1	5	2.5	3	4	5	6	5	340×240×95	2,057



Item No.	H	L1	L2	L3
018-2.5	2.5	85	110	150
018-3	3	85	126	167
018-4	4	100	130	180
018-5	5	100	153	203
018-6	6	125	173	233

Tool Type: Straight Type

Handle Type: T-Handle

Measurement Type: Metric

Additional Information: T-Handle Standard Length

Additional Information: Plastic Handle