



Item No.	H	L1	L2	L3	Inner	W×H×D	g
018-2	2	85	71	110	10	140×105×55	282
018-2.5	2.5	85	110	150	10	187×90×70	335
018-3	3	85	126	167	10	200×91×70	373
018-4	4	100	130	180	10	220×106×76	598
018-5	5	100	153	203	10	245×106×76	749
018-6	6	125	173	233	10	284×130×85	1,280
018-8	8	200	184	264	10	305×205×90	2,753
018-10	10	200	204	284	10	336×212×90	3,479

Tool Type: Straight Type

Handle Type: T-Handle

Measurement Type: Metric

Additional Information: T-Handle Standard Length

Additional Information: Plastic Handle