

Safety Data Sheet

Classified in accordance 29 CFR 1910.1200

1. Product Identification

Product Information: 1000034972

Product Identifier: CAMIE 375 SCREEN PRINTERS FLASH CURE ADHESIVE

Recommended Use: Adhesive

Manufacturer/Importer/Distributor Information: PLZ CORP
2651 WARRENVILLE RD, STE 300
DOWNERS GROVE, IL 60515
US
800-332-9000

Emergency Telephone: 866-836-8855

2. Hazard(s) identification

Classification

Flammable Aerosol, category 1
Aspiration Hazard, category 1
Skin Irritation, category 2
Eye Irritation, category 2A
STOT, single exposure, category 3, NE
Reproductive Toxicity, category 2
STOT, repeated exposure, category 2

Label elements

HAZARD PICTOGRAMS



SIGNAL WORD

Danger

GHS HAZARD STATEMENTS

H222 Extremely flammable aerosol.
H304 May be fatal if swallowed and enters airways.
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.
H361 Suspected of damaging fertility or the unborn child.
H373 May cause damage to organs through prolonged or repeated exposure.

GHS PRECAUTIONARY STATEMENTS

Prevention

P201	Obtain special instructions before use.
P202	Do not handle until all safety precautions have been read and understood.
P203	Obtain, read and follow all safety instructions before use.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211	Do not spray on an open flame or other ignition source.
P251	Do not pierce or burn, even after use.
P260	Do not breathe fumes, mists, vapours or spray.
P264+P265	Wash hands thoroughly after handling. Do not touch eyes.
P271	Use only outdoors or in a well-ventilated area.
P280	no information

Response

P301+P316	IF SWALLOWED: Get emergency medical help immediately.
P302+P352	IF ON SKIN: Wash with plenty of soap and water.
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P318	IF exposed or concerned, get medical help.
P319	Get medical help if you feel unwell.
P331	Do NOT induce vomiting.
P332+P317	If skin irritation occurs: Get medical help.
P337+P317	If eye irritation persists: Get medical help.
P362+P364	Take off contaminated clothing and wash it before reuse.

Storage

P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P405	Store locked up.
P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50°C/ 122°F.

Disposal

P501	Dispose of contents/container to an appropriate treatment and disposal facility in accordance with applicable laws and regulations, and product characteristics at time of disposal.
------	--

Other Information

None

3. Composition/Information on Ingredients**Mixtures**

<u>Chemical Identity</u>	<u>CAS Number</u>	<u>Content in Percent (%)*</u>
n-Hexane	110-54-3	10-25
Acetone	67-64-1	10-25
Propane	74-98-6	10-25
Butane	106-97-8	10-25
Methylcyclopentane	96-37-7	2.5-10
Dimethyl Ether	115-10-6	2.5-10
n-Heptane	142-82-5	0.1-1.0
Cyclohexane	110-82-7	0.1-1.0

* All concentrations are percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

Composition Comments: Other components are not hazardous or are below required disclosure limits.
The exact concentration has been withheld as a trade secret.

4. First-aid Measures

SKIN CONTACT: Remove contaminated clothing and wash the skin thoroughly with soap and water after work.

EYE CONTACT: Rinse immediately with plenty of water.

INHALATION: Move to fresh air.

INGESTION: Rinse mouth.

IMPORTANT SYMPTOMS: No data available

INDICATION OF IMMEDIATE MEDICAL ATTENTION AND SPECIAL TREATMENT NEEDED: Get medical attention if symptoms occur.

5. Fire-fighting Measures

EXTINGUISHING MEDIA: Use fire-extinguishing media appropriate for surrounding materials.

UNSUITABLE EXTINGUISHING MEDIA: Do not use water jet as an extinguisher, as this will spread the fire.

UNUSUAL FIRE AND EXPLOSION HAZARDS: No data available

SPECIAL FIREFIGHTING PROCEDURES: No data available

6. Accidental Release Measures

PERSONAL PRECAUTIONS : Ventilate closed spaces before entering them. ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Keep upwind.

METHODS AND MATERIALS FOR CONTAINMENT AND CLEANUP: Stop the flow of material, if this is without risk. Absorb with sand or other inert absorbent.

ENVIRONMENTAL PRECAUTIONS: Avoid release to the environment. Prevent further leakage or spillage if safe to do so. Do not contaminate water sources or sewer. Environmental manager must be informed of all major spillages.

7. Handling and Storage

HANDLING: Keep away from sources of ignition - No smoking. Keep away from open flames, hot surfaces and sources of ignition. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use.

SAFE HANDLING ADVICE: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use.

STORAGE: Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

NFPA 30B: Aerosol Level 3

8. Exposure Controls/Personal Protection

Ingredients with Occupational Exposure Limits

<u>Chemical Name</u>	<u>TLV-TWA</u>	<u>TLV-STEL</u>	<u>PEL-TWA</u>	<u>PEL-CEILING</u>
n-Hexane	50 ppm	N.E.	500 ppm	N.E.
Acetone	250 ppm	500 ppm	1000 ppm	N.E.
Propane	N.E.	N.E.	1000 ppm	N.E.
Butane	N.E.	1000 ppm	N.E.	N.E.
Methylcyclopentane	N.E.	N.E.	N.E.	N.E.
Dimethyl Ether	N.E.	N.E.	N.E.	N.E.
n-Heptane	400 ppm	500 ppm	500 ppm	N.E.

Cyclohexane

100 ppm

N.E.

300 ppm

N.E.

Further Advice: MEL = Maximum Exposure Limit OES = Occupational Exposure Standard SUP = Supplier's Recommendation
Sk = Skin Sensitizer N.E. = Not Established

ENGINEERING CONTROLS: No data available.

Personal Protection

EYE/FACE PROTECTION: Wear goggles/face shield.

SKIN PROTECTION: No data available

RESPIRATORY PROTECTION: Seek advice from local supervisor. In case of inadequate ventilation use suitable respirator.

HYGIENIC PRACTICES: When using do not smoke. Observe good industrial hygiene practices.

9. Physical and Chemical Properties

Appearance:

Physical State:	Liquid
Form:	Spray Aerosol
Color:	No data available
Odor:	No data available
Odor Threshold:	No data available
pH:	No data available
Freeze Point, °C:	No data available
Boiling Point, °C:	56
Flash Point, °C:	-104
Flammability (solid, gas):	No data available
Evaporation Rate:	No data available
Combustibility:	Supports Combustion
Explosive Limits, %:	1.9 - 18.0
Vapor Pressure @20°C, PSI:	28-48
Vapor Density:	No data available
Relative Density:	No data available
Solubility in Water:	No data available
Partition Coefficient, n-octanol/water:	No data available
Auto-Ignition Temperature, °C:	No data available
Decomposition temperature, °C:	No data available
Kinematic Viscosity:	No data available

10. Stability and Reactivity

REACTIVITY: No data available.

STABILITY: Material is stable under normal conditions.

POSSIBILITY OF HAZARDOUS REACTIONS: No data available.

CONDITIONS TO AVOID: Avoid heat or contamination

INCOMPATIBILITY: No data available

HAZARDOUS DECOMPOSITION PRODUCTS: No data available.

11. Toxicological Information

Information on Likely Routes of Exposure

SKIN CONTACT EFFECTS: May cause irritation on prolonged or repeated contact.

EYE CONTACT EFFECTS: May cause slight irritation with tearing.

INHALATION EFFECTS: Inhalation of high concentrations of mists may cause irritation of the nose throat and upper respiratory tract.

INGESTION EFFECTS: Ingestion may cause irritation of the mucous membranes, esophagus and stomach.

Carcinogenicity: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible, or confirmed human carcinogen by IARC, ACGIH, NTP or OSHA.

The following values are calculated based on chapter 3.1 of the GHS document. The product itself has not been tested.

<u>ATE ORAL</u>	4,366 mg/kg
<u>ATE DERMAL</u>	4,366 mg/kg
<u>ATE INHALATION</u>	Not classified for acute toxicity based on available data.

Acute Toxicity Values

The acute effects of this product have not been tested. Data on individual components are tabulated below

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
110-54-3	n-Hexane	2,000 mg/kg	2,000 mg/kg	31.86 mg/l
67-64-1	Acetone	5,800 mg/kg	7,426 mg/kg	50.1 mg/l
74-98-6	Propane	5,000 mg/kg	5,000 mg/kg	100 mg/l
106-97-8	Butane	N.I.	N.I.	658 mg/L Rat
96-37-7	Methylcyclopentane	2,000 mg/kg	2,000 mg/kg	N.I.
115-10-6	Dimethyl Ether	5,000 mg/kg	5,000 mg/kg	N.I.
142-82-5	n-Heptane	5,000 mg/kg	2,000 mg/kg	29.29 mg/l
110-82-7	Cyclohexane	5,000 mg/kg	2,000 mg/kg	32.88 mg/l

N.I. = No Information

Skin Corrosion & Irritation:

Product: No data available

Components:
n-Hexane 110-54-3 Causes skin irritation.

Serious Eye Damage & Irritation:

Product: No data available

Components:
Acetone 67-64-1 Causes serious eye irritation.

Respiratory or Skin Sensitization:

Product: No data available

STOT-Single Exposure:

Product:		No data available
Components:		
n-Hexane	110-54-3	May cause drowsiness or dizziness.
Cyclohexane	110-82-7	May cause drowsiness or dizziness.
n-Heptane	142-82-5	May cause drowsiness or dizziness.
Acetone	67-64-1	May cause drowsiness or dizziness.

STOT-Repeated Exposure:

Product:		No data available
Components:		
n-Hexane	110-54-3	May cause damage to organs through prolonged or repeated exposure.

Aspiration Hazard:

Product:		No data available
Components:		
n-Hexane	110-54-3	May be fatal if swallowed and enters airways.
Methylcyclopentane	96-37-7	May be fatal if swallowed and enters airways.
Cyclohexane	110-82-7	May be fatal if swallowed and enters airways.
n-Heptane	142-82-5	May be fatal if swallowed and enters airways.

Carcinogenicity:

Product:		No data available
-----------------	--	-------------------

Reproductive Toxicity:

Product:		No data available
Components:		
n-Hexane	110-54-3	Suspected of damaging fertility or the unborn child.

Germ Cell Mutagenicity:

Product:		No data available
-----------------	--	-------------------

12. Ecological Information

ECOLOGICAL INFORMATION: No data available

PERSISTENCE: No data available

BIOACCUMULATE: No data available

MOBILITY IN SOIL: No data available

OTHER ECOLOGICAL: No data available

13. Disposal Information

DISPOSAL INFORMATION: Consult with your local, regional and federal agencies for information on proper disposal.

CONTAMINATED PACKAGING : Consult with your local, regional and federal agencies for information on proper disposal.

14. Transport Information

SPECIAL TRANSPORT PRECAUTIONS: No data available

DOT

UN Number: UN1950
Proper Shipping Name: AEROSOLS, FLAMMABLE
Technical Name: N/A
Hazard Class(es)
Class: 2.1
Subsidiary Risk: N/A
Packing Group: N/A

IATA

UN Number: UN1950
Proper Shipping Name: AEROSOLS, FLAMMABLE
Technical Name: N/A
Hazard Class(es)
Class: 2.1
Subsidiary Risk: N/A
Packing Group: N/A

IMDG

UN Number: UN1950
Proper Shipping Name: AEROSOLS, FLAMMABLE
Technical Name: N/A
Hazard Class(es)
Class: 2.1
Subsidiary Risk: N/A
Packing Group: N/A

The classification shown in this section may be eligible for use of an exception, such as 'Limited Quantity', per the dangerous goods regulations. The shipper of this product should consult the applicable mode's regulation for the UN number displayed above to determine if any exceptions are available and may be utilized, at the shipper's discretion.

15. Regulatory Information

CHEMICAL INVENTORY STATUS:

TSCA On or in compliance with the inventory
DSL On or in compliance with the inventory

CALIFORNIA PROPOSITION 65 CARCINOGENS AND REPRODUCTIVE TOXINS:



Warning: This product may contain ingredients known to the state of California to cause Cancer or Reproductive Harm.

<u>Chemical Name</u>	<u>CAS-No.</u>
n-Hexane	110-54-3
Toluene	108-88-3
Benzene	71-43-2
Naphthalene	91-20-3
Ethyl Benzene	100-41-4

16. Other Information

Revision Date: 7/6/2022

Datasheet produced by: Regulatory Department

Legend

N/A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined, N.I. - No Information

TLV - Threshold Limit Values (TLVs®), as established by the American Conference of Governmental Industrial Hygienists (ACGIH®)

PEL - Permissible Exposure Limit, as established by the U.S. Occupational Safety and Health Administration (OSHA), as amended

TSCA - U.S. Toxic Substance Control Act

DSL - Canada Environmental Protection Act: Domestic Substance List

This information is provided without warranty. The information is believed to be correct. This information should be used to make an independent determination of the methods to safeguard workers and the environment.

