



Issue date 11-Oct-2017

Safety Data Sheet

Version 2

1. Identification of the Substance/Preparation and of the Company/Undertaking

Product Identifier

Product name CHAMPION SPRAYON FIELD MARKING & STRIPING PAINT FLAT BLACK
Chemical name 6-6250

Other means of identification

Product code FG 419-4825-5
Synonyms Spray Paint

Recommended use of the chemical and restrictions on use

Recommended Use Field and pavement marking and striping paints.
Uses advised against Do not use on surfaces that are wet, cover with dust, dirt, grease, wax or loose paint.

Details of the supplier of the safety data sheet

Supplier Address	Manufacturer Address
Chase Products Co.	Chase Products Co.
2727 Gardner Road	2727 Gardner Road
Broadview, IL 60155	Broadview, IL 60155
708-273-1121	708-273-1121

Emergency Telephone Number

Company Phone Number 708-865-1000
24 Hour Emergency Phone Number 1-800-255-3924
Emergency telephone ChemTel 1-800-255-3924

2. Hazards Identification

Classification

Serious eye damage/eye irritation	Category 2
Germ cell mutagenicity	Category 1B
Carcinogenicity	Category 1B
Aspiration toxicity	Category 1
FLAMMABLE AEROSOLS	Category 1
Gases Under Pressure	liquefied gas

Label Elements

EMERGENCY OVERVIEW

DANGER

hazard statements

Causes serious eye irritation
May cause genetic defects
May cause cancer
May be fatal if swallowed and enters airways
EXTREMELY FLAMMABLE AEROSOL
Contains gas under pressure; may explode if heated



Appearance Black liquid.

Physical State Aerosol

Odor Characteristic odor of paint.

Precautionary Statements - Prevention

Obtain special instructions before use
 Do not handle until all safety precautions have been read and understood
 Wear protective gloves, protective clothing, eye protection and face protection.
 Wash face, hands and any exposed skin thoroughly after handling
 Keep away from heat, sparks, open flames and hot surfaces. — No smoking
 Pressurized container: Do not pierce or burn, even after use
 Do not spray on an open flame or other ignition source

Precautionary Statements - Response

IF exposed or concerned: Get medical advice/attention
 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 If eye irritation persists: Get medical advice/attention
 IF SWALLOWED: Immediately call a POISON CENTER or doctor
 Do NOT induce vomiting

Precautionary Statements - Storage

Store locked up
 Protect from sunlight. Store in a well-ventilated place
 Do not expose to temperatures exceeding 122 °F (50 °C)

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Other Information

- Causes mild skin irritation
 - Toxic to aquatic life with long lasting effects
- 4.16% of the mixture consists of ingredient(s) of unknown toxicity

3. Composition/information on Ingredients

Synonyms Spray Paint.
Chemical Family MIXTURES.
Formula 6-6250

Chemical name	CAS No	weight-%	Trade secret
Water	7732-18-5	35-40	*
Low Odor Mineral Spirits	64742-47-8	10-15	*
Calcium Carbonate	471-34-1	10-15	*
Acetone	67-64-1	10-15	*
Propane	74-98-6	5-10	*
N-Butane	106-97-8	1-5	*
Light Aliphatic Naphtha	64742-49-0	1-5	*
Carbon BLACK	1333-86-4	1-5	*
Xylenes (o-, m-, p- isomers)	1330-20-7	1-5	*
Solvent Naphtha	64742-89-9	<1	*
Ethylbenzene	100-41-4	<1	*
Petroleum naphtha, light aromatic	64742-95-6	<1	*

* The exact percentage (concentration) of composition has been withheld as a trade secret.

4. First aid measures

FIRST AID MEASURES

Eye Contact	Hold eye open and rinse slowly and gently with water for 15-20 minutes. Remove contact lenses, if present, after the first 5 minutes, then continue rinsing eye. Call a poison control center or doctor for treatment advice.
Skin contact	Take off contaminated clothing. Rinse skin immediately with plenty of water for 15-20 minutes. Call a poison control center or doctor for treatment advice.
Inhalation	If overcome by vapor, move person to fresh air. If person is not breathing, call 911 or an ambulance, then provide artificial respiration, preferably mouth-to-mouth, if possible. Call a poison control center or doctor for further treatment advice.
Ingestion	Call a poison control center or doctor for treatment advice. Have person sip a glass of water if able to swallow. Do not induce vomiting unless told to do so by a poison control center or doctor. Do not give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Symptoms	Acute: Prolonged inhalation of concentrated vapor or mist may cause headaches, dizziness and nausea. Prolonged and repeated contact with skin may cause irritation and reddening. Contact with eyes causes irritation.
-----------------	--

Indication of any immediate medical attention and special treatment needed

Note to physicians	Contains petroleum distillates, do not induce vomiting because of aspiration pneumonia hazard.
---------------------------	--

5. Fire-fighting measures

Suitable extinguishing media

Dry chemical, CO2 or water spray.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

This product is under pressure. Water spray may be used to cool cans in the vicinity of fire or excessive heat to prevent the explosion of the cans.

Hazardous combustion products Thermal decomposition may yield gases like nitrogen oxides, carbon monoxide and carbon dioxide.

Explosion data

Sensitivity to Mechanical Impact Contents under pressure. This product is extremely flammable. Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity).

Sensitivity to Static Discharge Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity).

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

FG 419-4825-5 CHAMPION SPRAYON FIELD MARKING & STRIPING PAINT FLAT BLACK

Personal precautions Use in well-ventilated area ONLY. NOTICE: Reports have associated repeated and prolonged occupational over exposure to solvents with permanent brain and nervous system damage. Intentional misuse by deliberately concentrating and inhaling the contents can be harmful or fatal. To avoid breathing vapor or spray mist open windows and doors or use other means to ensure fresh air entry during application and drying. If you experience eye watering, headaches, or dizziness, increase fresh air or wear an appropriate, properly fitted respirator (NIOSH approved), or leave the area. NOTE: Follow respirator manufacturer's instructions carefully for respirator use.

For emergency responders Remove all sources of ignition.

Environmental precautions

Environmental precautions See Section 12 for additional Ecological Information.

Methods and material for containment and cleaning up

Methods for Containment Provide adequate ventilation to area being treated. Soak up spills with chemically inert, absorbent material.

Methods for cleaning up Clean contaminated surface thoroughly.

7. Handling and Storage

Precautions for safe handling

Advice on safe handling Handle as an extremely flammable material. Avoid contact with skin, eyes and clothing. Store cans in a cool, dry place away from heat and open flame.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). **AEROSOL STORAGE LEVEL III (NFPA-30B).**

Incompatible Materials Avoid heat, open flame and contact with strong acids, strong bases and strong oxidizers.

8. Exposure Controls/Personal Protection

Control parameters

Exposure guidelines See occupational exposure limits listed below.

Chemical name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Calcium Carbonate 471-34-1	-	-	TWA: 10 mg/m ³ total dust TWA: 5 mg/m ³ respirable dust
Acetone 67-64-1	STEL: 500 ppm TWA: 250 ppm	TWA: 1000 ppm TWA: 2400 mg/m ³ (vacated) TWA: 750 ppm (vacated) TWA: 1800 mg/m ³ (vacated) STEL: 2400 mg/m ³ The acetone STEL does not apply to the cellulose acetate fiber industry. It is in effect for all other sectors (vacated) STEL: 1000 ppm	IDLH: 2500 ppm TWA: 250 ppm TWA: 590 mg/m ³
Propane 74-98-6	: See Appendix F: Minimal Oxygen Content	TWA: 1000 ppm TWA: 1800 mg/m ³ (vacated) TWA: 1000 ppm (vacated) TWA: 1800 mg/m ³	IDLH: 2100 ppm TWA: 1000 ppm TWA: 1800 mg/m ³
N-Butane 106-97-8	STEL: 1000 ppm	(vacated) TWA: 800 ppm (vacated) TWA: 1900 mg/m ³	TWA: 800 ppm TWA: 1900 mg/m ³
Carbon BLACK 1333-86-4	TWA: 3 mg/m ³ inhalable fraction	TWA: 3.5 mg/m ³ (vacated) TWA: 3.5 mg/m ³	IDLH: 1750 mg/m ³ TWA: 3.5 mg/m ³ TWA: 0.1 mg/m ³ Carbon black in

FG 419-4825-5 CHAMPION SPRAYON FIELD MARKING & STRIPING PAINT FLAT BLACK

			presence of Polycyclic aromatic hydrocarbons PAH
Xylenes (o-, m-, p- isomers) 1330-20-7	STEL: 150 ppm TWA: 100 ppm	TWA: 100 ppm TWA: 435 mg/m ³ (vacated) TWA: 100 ppm (vacated) TWA: 435 mg/m ³ (vacated) STEL: 150 ppm (vacated) STEL: 655 mg/m ³	-
Ethylbenzene 100-41-4	TWA: 20 ppm	TWA: 100 ppm TWA: 435 mg/m ³ (vacated) TWA: 100 ppm (vacated) TWA: 435 mg/m ³ (vacated) STEL: 125 ppm (vacated) STEL: 545 mg/m ³	IDLH: 800 ppm TWA: 100 ppm TWA: 435 mg/m ³ STEL: 125 ppm STEL: 545 mg/m ³

Appropriate engineering controls

Engineering controls Use with adequate general or local exhaust ventilation.

Individual protection measures, such as personal protective equipment

- Eye/face Protection** Conventional eyeglasses to guard against splashing.
- Skin and Body Protection** Chemical resistant gloves required.
- Respiratory protection** Use in well-ventilated area ONLY. NOTICE: Reports have associated repeated and prolonged occupational over exposure to solvents with permanent brain and nervous system damage. Intentional misuse by deliberately concentrating and inhaling the contents can be harmful or fatal. To avoid breathing vapor or spray mist open windows and doors or use other means to ensure fresh air entry during application and drying. If you experience eye watering, headaches, or dizziness, increase fresh air or wear an appropriate, properly fitted respirator (NIOSH approved), or leave the area. NOTE: Follow respirator manufacturer's instructions carefully for respirator use.

General hygiene considerations Wash hands thoroughly after handling. Wash contaminated clothing before reuse.

9. Physical and Chemical Properties

Information on basic physical and chemical properties

Physical State	Aerosol	Odor	Characteristic odor of paint.
Appearance	Black liquid.	Odor threshold	No information available
Color	Black	Remarks • Method	
Property	Values		
pH	Not applicable		Solvent-based product.
Melting point/freezing point	Not applicable		No information available
Boiling point/boiling range	Acetone 133 °F/56.29 °C		No information available
Flash Point	Not available. This is an aerosol product with a Flame Projection of 18 in. with 3 in. flashback. Temperatures above 120 °F may cause cans to burst.		No information available
Evaporation Rate	Faster than butyl acetate		No information available
Flammability (solid, gas)			No information available
Flammability Limits in Air			No information available
Upper flammability limits	Not available		
Lower Flammability Limit	Not available		
Vapor pressure			No information available
Vapor Density			No information available
Relative Density	1.005 concentrate		No information available
Water solubility	Insoluble in water		No information available
Solubility in other solvents			No information available
Partition coefficient			No information available

FG 419-4825-5 CHAMPION SPRAYON FIELD MARKING & STRIPING PAINT FLAT BLACK

N-Butane 106-97-8	-	-	= 658 g/m ³ (Rat) 4 h
Light Aliphatic Naphtha 64742-49-0	> 5000 mg/kg (Rat)	> 3160 mg/kg (Rabbit)	= 73680 ppm (Rat) 4 h
Carbon BLACK 1333-86-4	> 15400 mg/kg (Rat)	> 3 g/kg (Rabbit)	-
Xylenes (o-, m-, p- isomers) 1330-20-7	= 3500 mg/kg (Rat)	> 1700 mg/kg (Rabbit) > 4350 mg/kg (Rabbit)	= 29.08 mg/L (Rat) 4 h = 5000 ppm (Rat) 4 h
Ethylbenzene 100-41-4	= 3500 mg/kg (Rat)	= 15400 mg/kg (Rabbit)	= 17.2 mg/L (Rat) 4 h
Petroleum naphtha, light aromatic 64742-95-6	= 8400 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	= 3400 ppm (Rat) 4 h

Information on toxicological effects

Symptoms Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation May cause skin irritation and reddening after prolonged or repeated contact with skin.
Serious eye damage/eye irritation Irritating to eyes.
irritation May cause skin and eye irritation.
corrosivity Not applicable.
sensitization No information available.
Germ cell mutagenicity See Section 2 of this SDS.
Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical name	ACGIH	IARC	NTP	OSHA
Carbon BLACK 1333-86-4	A3	Group 2B		X
Xylenes (o-, m-, p- isomers) 1330-20-7		Group 3		
Ethylbenzene 100-41-4	A3	Group 2B		X

Reproductive toxicity See Section 2 of this SDS.
STOT - single exposure No information available.
STOT - repeated exposure No information available.
Aspiration Hazard No information available.

Numerical measures of toxicity - Product Information

Unknown acute toxicity 4.16% of the mixture consists of ingredient(s) of unknown toxicity
The following values are calculated based on chapter 3.1 of the GHS document .
ATEmix (oral) 21118 mg/kg
ATEmix (dermal) 31293 mg/kg
ATEmix (inhalation-gas) 15680 mg/l
ATEmix (inhalation-dust/mist) 15.9 mg/l
ATEmix (inhalation-vapor) 840 mg/l

12. Ecological Information

ecotoxicity

34.08% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical name	Algae/aquatic plants	Fish	Toxicity to Microorganisms	Crustacea
Low Odor Mineral Spirits 64742-47-8		2.2: 96 h Lepomis macrochirus mg/L LC50 static 45: 96 h Pimephales promelas mg/L LC50 flow-through 2.4: 96 h		4720: 96 h Daphnia magna mg/L LC50

FG 419-4825-5 CHAMPION SPRAYON FIELD MARKING & STRIPING PAINT FLAT BLACK

		Oncorhynchus mykiss mg/L LC50 static		
Acetone 67-64-1		4.74 - 6.33: 96 h Oncorhynchus mykiss mL/L LC50 8300: 96 h Lepomis macrochirus mg/L LC50 6210 - 8120: 96 h Pimephales promelas mg/L LC50 static	EC50 = 14500 mg/L 15 min	12600 - 12700: 48 h Daphnia magna mg/L EC50 10294 - 17704: 48 h Daphnia magna mg/L EC50 Static
Light Aliphatic Naphtha 64742-49-0				2.6: 96 h Chaetogammarus marinus mg/L LC50
Carbon BLACK 1333-86-4				5600: 24 h Daphnia magna mg/L EC50
Xylenes (o-, m-, p- isomers) 1330-20-7		30.26 - 40.75: 96 h Poecilia reticulata mg/L LC50 static 780: 96 h Cyprinus carpio mg/L LC50 semi-static 2.661 - 4.093: 96 h Oncorhynchus mykiss mg/L LC50 static 13.4: 96 h Pimephales promelas mg/L LC50 flow-through 23.53 - 29.97: 96 h Pimephales promelas mg/L LC50 static 13.1 - 16.5: 96 h Lepomis macrochirus mg/L LC50 flow-through 7.711 - 9.591: 96 h Lepomis macrochirus mg/L LC50 static 13.5 - 17.3: 96 h Oncorhynchus mykiss mg/L LC50 19: 96 h Lepomis macrochirus mg/L LC50 780: 96 h Cyprinus carpio mg/L LC50	EC50 = 0.0084 mg/L 24 h	3.82: 48 h water flea mg/L EC50 0.6: 48 h Gammarus lacustris mg/L LC50
Ethylbenzene 100-41-4	2.6 - 11.3: 72 h Pseudokirchneriella subcapitata mg/L EC50 static 1.7 - 7.6: 96 h Pseudokirchneriella subcapitata mg/L EC50 static 438: 96 h Pseudokirchneriella subcapitata mg/L EC50 4.6: 72 h Pseudokirchneriella subcapitata mg/L EC50	9.1 - 15.6: 96 h Pimephales promelas mg/L LC50 static 32: 96 h Lepomis macrochirus mg/L LC50 static 4.2: 96 h Oncorhynchus mykiss mg/L LC50 semi-static 11.0 - 18.0: 96 h Oncorhynchus mykiss mg/L LC50 static 7.55 - 11: 96 h Pimephales promelas mg/L LC50 flow-through 9.6: 96 h Poecilia reticulata mg/L LC50 static	EC50 = 9.68 mg/L 30 min EC50 = 96 mg/L 24 h	1.8 - 2.4: 48 h Daphnia magna mg/L EC50
Petroleum naphtha, light aromatic 64742-95-6		9.22: 96 h Oncorhynchus mykiss mg/L LC50		6.14: 48 h Daphnia magna mg/L EC50

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Chemical name	Partition coefficient
Acetone 67-64-1	-0.24
Propane 74-98-6	2.3
N-Butane 106-97-8	2.89
Xylenes (o-, m-, p- isomers) 1330-20-7	2.77 - 3.15
Ethylbenzene 100-41-4	3.118

Other adverse effects No information available

13. Disposal Considerations

Waste treatment methods

Disposal of wastes Dispose of in accordance with federal, state and local regulations.

Contaminated packaging Pressurized container: Do not pierce or burn, even after use. Do not puncture or incinerate container. If empty: Place in trash or offer for recycling if available. If partly filled: Call your local solid waste agency for disposal instructions.

Chemical name	RCRA	RCRA - Basis for Listing	RCRA - D Series Wastes	RCRA - U Series Wastes
Acetone 67-64-1		Included in waste stream: F039		U002
Xylenes (o-, m-, p- isomers) 1330-20-7		Included in waste stream: F039		U239
Ethylbenzene 100-41-4		Included in waste stream: F039		

Chemical name	California Hazardous Waste Status
Acetone 67-64-1	Ignitable
Xylenes (o-, m-, p- isomers) 1330-20-7	Toxic Ignitable
Ethylbenzene 100-41-4	Toxic Ignitable

14. Transport Information

DOT

UN/ID no Limited Quantity
Proper Shipping Name Consumer Commodity
Hazard Class ORM-D

IATA

UN/ID no UN1950
Proper Shipping Name Aerosols, flammable
Hazard Class 2.1

IMDG

UN/ID no UN1950
Proper Shipping Name Aerosols, flammable
Hazard Class 2.1
Marine pollutant This product contains chemicals that are listed as marine pollutants.

15. Regulatory information

International Inventories

TSCA All ingredients of this product are listed or are excluded from listing under the U.S. Toxic Substances Control Act (TSCA) Chemical Substance Inventory.

DSL All ingredients are listed or are excluded from listing on the DSL.

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

FG 419-4825-5 CHAMPION SPRAYON FIELD MARKING & STRIPING PAINT FLAT BLACK

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

This product contains the following toxic chemicals (above the de minimis level) subject to the reporting requirements of Section 313 of the Emergency Planning and Community Right-to-Know Act of 1986 and 40 CFR 372. This information must be included in all SDSs that are copied and distributed for this material.

Chemical name	CAS No	weight-%	SARA 313 - Threshold Values %
Xylenes (o-, m-, p- isomers) - 1330-20-7	1330-20-7	1-5	1.0
Ethylbenzene - 100-41-4	100-41-4	<1	0.1

SARA 311/312 Hazard Categories

Acute Health Hazard	yes
Chronic Health Hazard	yes
Fire Hazard	yes
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

Chemical name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Xylenes (o-, m-, p- isomers) 1330-20-7	100 lb			X
Ethylbenzene 100-41-4	1000 lb	X	X	X

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Acetone 67-64-1	5000 lb		RQ 5000 lb final RQ RQ 2270 kg final RQ
Xylenes (o-, m-, p- isomers) 1330-20-7	100 lb		RQ 100 lb final RQ RQ 45.4 kg final RQ
Ethylbenzene 100-41-4	1000 lb		RQ 1000 lb final RQ RQ 454 kg final RQ

US State Regulations

California Proposition 65

This product contains the following Proposition 65 chemicals. This product contains <0.1% cumene, a chemical known to the State of California to cause cancer.

Chemical name	California Proposition 65
Carbon BLACK - 1333-86-4	Carcinogen
Ethylbenzene - 100-41-4	carcinogen

U.S. State Right-to-Know Regulations

Chemical name	New Jersey	Massachusetts	Pennsylvania
Water 7732-18-5			X
Acetone 67-64-1	X	X	X
Propane 74-98-6	X	X	X
N-Butane	X	X	X

FG 419-4825-5 CHAMPION SPRAYON FIELD MARKING & STRIPING PAINT FLAT BLACK

106-97-8			
Carbon BLACK 1333-86-4	X	X	X
Xylenes (o-, m-, p- isomers) 1330-20-7	X	X	X
Ethylbenzene 100-41-4	X	X	X

U.S. EPA Label information

EPA Pesticide registration number Not applicable

16. Other information

NFPA	Health Hazards 2	Flammability 4	Instability 1	Physical and chemical properties Not applicable
HMIS	Health Hazards 2*	Flammability 4	Physical hazards 1	Personal Protection B - Eyes and hands protection

Prepared by Regulatory Department
 Issue date 11-Oct-2017

Revision note
 This SDS supersedes a previous SDS dated October 9, 2015.

Disclaimer

The information provided in this Material Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet