


Item No.	Pcs.	H						Inner	W×H×D	g
DS-6	6	0.71※	0.89※	1.27	1.5	1.59	2	5	241×93×70	498

※ 0.71 and 0.89 are black parkerized finish blade.



Item No.	H	L1	L2	Φ
D-0.7	0.71 (0.028")	35	74	8
D-0.9	0.89 (0.035")	40	74	8
D-1.3	1.27 (0.05")	60	82	11
D-1.5	1.5	70	87	15
D-1.6	1.59 (1/16")	70	87	15
D-2	2	80	85	18

Tool Type: Straight Type
Handle Type: SCREWDRIVER
Measurement Type: Metric
Additional Information: Plastic Handle