



Issue date 16-Feb-2022

Safety Data Sheet

Version 2

1. Identification of the Substance/Preparation and of the Company/Undertaking

Product Identifier

Product name CHAMPION SPRAYON CINNAMON STICK DRY AIR FRESHENER
Chemical name 7-8193

Other means of identification

Product code FG 438-5362-3
Synonyms Dry Air Freshener

Recommended use of the chemical and restrictions on use

Recommended Use Room Deodorizer.
Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier Address Chase Products Co.
2727 Gardner Road
Broadview, IL 60155
708-865-1000
Manufacturer Address Chase Products Co.
2727 Gardner Road
Broadview, IL 60155
708-865-1000

Emergency Telephone Number

Company Phone Number 708-865-1000
24 Hour Emergency Phone Number 1-800-255-3924
Emergency telephone ChemTel 1-800-255-3924

2. Hazards Identification

Classification

Acute toxicity - Inhalation (Gases)	Category 3
Acute toxicity - Inhalation (Vapors)	Category 4
Serious eye damage/eye irritation	Category 2
Specific target organ toxicity (single exposure)	Category 3
Aspiration toxicity	Category 1
FLAMMABLE AEROSOLS	Category 1
Gases Under Pressure	liquefied gas

Label Elements

EMERGENCY OVERVIEW

DANGER

hazard statements

Toxic if inhaled
Causes serious eye irritation
May cause drowsiness or dizziness
May be fatal if swallowed and enters airways
EXTREMELY FLAMMABLE AEROSOL
Contains gas under pressure; may explode if heated



Appearance Clear liquid that will be aerosolized.

Physical State Aerosol

Odor Perfumed.

Precautionary Statements - Prevention

- Avoid breathing fumes, mist, vapors or spray.
- Use only outdoors or in a well-ventilated area
- Wash face, hands and any exposed skin thoroughly after handling
- Wear protective gloves, protective clothing, eye protection and face protection.
- Keep away from heat, sparks, open flames and hot surfaces. — No smoking
- Pressurized container: Do not pierce or burn, even after use
- Do not spray on an open flame or other ignition source

Precautionary Statements - Response

- Specific treatment: See additional cautionary statements on this label.
- IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
- If eye irritation persists: Get medical advice/attention
- IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
- Call a POISON CENTER or doctor/physician
- IF SWALLOWED: Immediately call a POISON CENTER or doctor
- Do NOT induce vomiting

Precautionary Statements - Storage

- Store locked up
- Store in a well-ventilated place. Keep container tightly closed
- Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

Hazards not otherwise classified (HNOC)

Other Information

- Toxic to aquatic life with long lasting effects
- Toxic to aquatic life

3. Composition/information on Ingredients

Synonyms Dry Air Freshener.
Chemical Family MIXTURES.
Formula 7-8193

Chemical name	CAS No	weight-%	Trade secret
Acetone	67-64-1	35-40	*
Petroleum distillates, hydrotreated light	64742-47-8	25-30	*
Propane	74-98-6	15-20	*
N-Butane	106-97-8	10-15	*

* The exact percentage (concentration) of composition has been withheld as a trade secret.

4. First aid measures

FIRST AID MEASURES

Eye Contact	Hold eye open and rinse slowly and gently with water for 15-20 minutes. Remove contact lenses, if present, after the first 5 minutes, then continue rinsing eye. Call a poison control center or doctor for treatment advice.
Skin contact	In case of contact, immediately flush skin with plenty of water. Wash skin with soap and water. If irritation develops, consult a physician.
Inhalation	If overcome by vapor, move person to fresh air. If person is not breathing, call 911 or an ambulance, then provide artificial respiration, preferably mouth-to-mouth, if possible. Call a poison control center or doctor for further treatment advise.
Ingestion	Ingestion from an aerosol product is unlikely to occur. Contains petroleum distillates. Harmful if swallowed. If accidentally swallowed, do not induce vomiting, call physician immediately.

Most important symptoms and effects, both acute and delayed

Symptoms	Acute: Prolonged inhalation of concentrated vapor or mist may cause headaches, dizziness and nausea. Prolonged and repeated contact with skin may cause irritation and reddening. Contact with eyes causes irritation.
-----------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Indication of any immediate medical attention and special treatment needed

Note to physicians	Contains petroleum distillates, do not induce vomiting because of aspiration pneumonia hazard.
---------------------------	------------------------------------------------------------------------------------------------

5. Fire-fighting measures

Suitable extinguishing media
Dry chemical, CO2 or water spray.

Unsuitable extinguishing media Caution: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical
This product is under pressure. Water spray may be used to cool cans in the vicinity of fire or excessive heat to prevent the explosion of the cans.

Hazardous combustion products Thermal decomposition may release carbon monoxide and carbon dioxide.

Explosion data

Sensitivity to Mechanical Impact Contents under pressure. This product is extremely flammable. Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity).

Sensitivity to Static Discharge Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity).

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions Use with adequate general or local exhaust ventilation.

For emergency responders Remove all sources of ignition.

Environmental precautions

Environmental precautions See Section 12 for additional Ecological Information.

Methods and material for containment and cleaning up

Methods for Containment Provide adequate ventilation to area being treated. Soak up spills with chemically inert, absorbent material.

Methods for cleaning up Clean contaminated surface thoroughly.

7. Handling and Storage

Precautions for safe handling

Advice on safe handling Keep away from heat, sparks, open flames and hot surfaces. — No smoking.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). **AEROSOL STORAGE LEVEL III (NFPA-30B).**

Incompatible Materials Avoid heat, open flame and contact with strong oxidizers, inorganic acids and halogens.

8. Exposure Controls/Personal Protection

Control parameters

Exposure guidelines See occupational exposure limits listed below.

Chemical name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Acetone 67-64-1	STEL: 500 ppm TWA: 250 ppm	TWA: 1000 ppm TWA: 2400 mg/m ³ (vacated) TWA: 750 ppm (vacated) TWA: 1800 mg/m ³ (vacated) STEL: 2400 mg/m ³ The acetone STEL does not apply to the cellulose acetate fiber industry. It is in effect for all other sectors. (vacated) STEL: 1000 ppm	IDLH: 2500 ppm TWA: 250 ppm TWA: 590 mg/m ³
Propane 74-98-6	: See Appendix F: Minimal Oxygen Content, explosion hazard	TWA: 1000 ppm TWA: 1800 mg/m ³ (vacated) TWA: 1000 ppm (vacated) TWA: 1800 mg/m ³	IDLH: 2100 ppm TWA: 1000 ppm TWA: 1800 mg/m ³
N-Butane 106-97-8	STEL: 1000 ppm explosion hazard	(vacated) TWA: 800 ppm (vacated) TWA: 1900 mg/m ³	IDLH: 1600 ppm TWA: 800 ppm TWA: 1900 mg/m ³

Appropriate engineering controls

Engineering controls Use with adequate general or local exhaust ventilation.

Individual protection measures, such as personal protective equipment

Eye/face Protection Conventional eyeglasses to guard against splashing.

Skin and Body Protection Household type gloves.

Respiratory protection Use in a well-ventilated area ONLY. None required if used in a well-ventilated area. Follow label directions for correct use of the product..

General hygiene considerations Wash hands thoroughly after handling. Wash contaminated clothing before reuse.

9. Physical and Chemical Properties

Information on basic physical and chemical properties

Physical State	Aerosol	Odor	Perfumed.
Appearance	Clear liquid that will be aerosolized.	Odor threshold	No information available
Color	Color will vary depending on the perfume in the product.		

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	Not applicable	Solvent-based product.
Melting point/freezing point	Not applicable	No information available
Boiling point/boiling range	Acetone 133 F/56.29 C	No information available
Flash Point	Not Available. This is an aerosol product for which Flame Projection is over 18 inches with 8 in flashback. Temperatures above 120 °F may cause cans to burst.	No information available
Evaporation Rate	Faster than butyl acetate	No information available
Flammability (solid, gas)		No information available
Flammability Limits in Air		No information available
Upper flammability limits	Not available	
Lower Flammability Limit	Not available	
Vapor pressure		No information available
Vapor Density		No information available
Relative Density	0.792 g/ml	No information available
Water solubility	Insoluble in water	No information available
Solubility in other solvents		No information available
Partition coefficient		No information available
Autoignition Temperature		No information available
Decomposition temperature		No information available
Kinematic viscosity		No information available
Dynamic viscosity		No information available
Explosive properties	No information available	
Oxidizing properties	No information available	

Other Information

Softening point	No information available
Molecular weight	No information available
VOC content (%)	29.65%
Density	7.60 lb/gal
Bulk Density	No information available

10. Stability and Reactivity

Reactivity
Not applicable

Chemical stability
Stable.

Possibility of hazardous reactions
Temperatures above 130 °F may cause cans to burst with force.

hazardous polymerization	Hazardous polymerization does not occur.
---------------------------------	------------------------------------------

Conditions to Avoid
Temperatures above 122 °F (50 °C).

Incompatible Materials
Avoid heat, open flame and contact with strong oxidizers, inorganic acids and halogens.

Hazardous decomposition products

Thermal decomposition may yield gases like carbon monoxide and carbon dioxide.

11. Toxicological Information

Information on likely routes of exposure

Product Information	This product has not been tested as whole. See below for information on ingredients.
Inhalation	See data below.
Eye Contact	Not data available.
Skin contact	See data below.
Ingestion	See data below.

Chemical name	Oral LD50	dermal LD50	Inhalation LC50
Acetone 67-64-1	= 5800 mg/kg (Rat)	> 15700 mg/kg (Rabbit)	= 50100 mg/m ³ (Rat) 8 h
Petroleum distillates, hydrotreated light 64742-47-8	> 5000 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	> 5.2 mg/L (Rat) 4 h
Propane 74-98-6	-	-	> 800000 ppm (Rat) 15 min
N-Butane 106-97-8	-	-	= 658 g/m ³ (Rat) 4 h

Information on toxicological effects

Symptoms Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation	May cause skin irritation and reddening after prolonged or repeated contact with skin.
Serious eye damage/eye irritation	Irritating to eyes.
irritation	May cause skin and eye irritation.
corrosivity	Not applicable.
sensitization	No information available.
Germ cell mutagenicity	No information available.
Carcinogenicity	Not known chronic effects based on available data. None of the ingredients present in excess of 0.1% are listed as carcinogenic by NTP, IARC or OSHA.
Reproductive toxicity	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Aspiration Hazard	No information available.

Numerical measures of toxicity - Product Information

Unknown acute toxicity	-
The following values are calculated based on chapter 3.1 of the GHS document	
ATEmix (oral)	5416 mg/kg
ATEmix (dermal)	2000 mg/kg
ATEmix (inhalation-gas)	1379 mg/l
ATEmix (inhalation-dust/mist)	5.2 mg/l
ATEmix (inhalation-vapor)	10.2 mg/l

12. Ecological Information

FG 438-5362-3 CHAMPION SPRAYON CINNAMON STICK DRY AIR FRESHENER

ecotoxicity

See information listed below.

Chemical name	Algae/aquatic plants	Fish	Toxicity to Microorganisms	Crustacea
Acetone 67-64-1		4.74 - 6.33: 96 h Oncorhynchus mykiss mL/L LC50 6210 - 8120: 96 h Pimephales promelas mg/L LC50 static 8300: 96 h Lepomis macrochirus mg/L LC50	EC50 = 14500 mg/L 15 min	10294 - 17704: 48 h Daphnia magna mg/L EC50 Static 12600 - 12700: 48 h Daphnia magna mg/L EC50
Petroleum distillates, hydrotreated light 64742-47-8		2.2: 96 h Lepomis macrochirus mg/L LC50 static 2.4: 96 h Oncorhynchus mykiss mg/L LC50 static 45: 96 h Pimephales promelas mg/L LC50 flow-through		

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Chemical name	Partition coefficient
Acetone 67-64-1	-0.24
Propane 74-98-6	2.3
N-Butane 106-97-8	2.89

Other adverse effects

No information available

13. Disposal Considerations

Waste treatment methods

Disposal of wastes

Dispose of in accordance with federal, state and local regulations.

Contaminated packaging

Pressurized container: Do not pierce or burn, even after use. Do not puncture or incinerate container. If empty: Place in trash or offer for recycling if available. If partly filled: Call your local solid waste agency for disposal instructions.

Chemical name	RCRA	RCRA - Basis for Listing	RCRA - D Series Wastes	RCRA - U Series Wastes
Acetone 67-64-1		Included in waste stream: F039		U002

Chemical name	California Hazardous Waste Status
Acetone 67-64-1	Ignitable

14. Transport Information

DOT

UN/ID no

Limited Quantity

FG 438-5362-3 CHAMPION SPRAYON CINNAMON STICK DRY AIR FRESHENER

Proper Shipping Name Consumer Commodity
Hazard Class NA

IATA

UN/ID no UN1950
Proper Shipping Name Aerosols, flammable
Hazard Class 2.1

IMDG

UN/ID no UN1950
Proper Shipping Name Aerosols, flammable
Hazard Class 2.1

15. Regulatory information

International Inventories

TSCA All ingredients of this product are listed or are excluded from listing under the U.S. Toxic Substances Control Act (TSCA) Chemical Substance Inventory.

DSL All ingredients are listed or are excluded from listing on the DSL.

Legend:

TSCA - *United States Toxic Substances Control Act Section 8(b) Inventory*
 DSL/NDL - *Canadian Domestic Substances List/Non-Domestic Substances List*

US Federal Regulations

SARA 313

This product does not contain toxic chemicals (above the de minimis level) subject to the reporting requirements of Section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 and of 40 CFR 372.

SARA 311/312 Hazard Categories

Acute Health Hazard	yes
Chronic Health Hazard	No
Fire Hazard	yes
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Acetone 67-64-1	5000 lb		RQ 5000 lb final RQ RQ 2270 kg final RQ

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals

U.S. State Right-to-Know Regulations

Chemical name	New Jersey	Massachusetts	Pennsylvania
Acetone 67-64-1	X	X	X
Propane 74-98-6	X	X	X
N-Butane 106-97-8	X	X	X

U.S. EPA Label information

EPA Pesticide registration number Not applicable

16. Other information

NFPA	Health Hazards 2	Flammability 4	Instability 1	Physical and chemical properties Not applicable Personal Protection B - Eyes and hands protection
HMIS	Health Hazards 2	Flammability 4	Physical hazards 1	

Prepared by Regulatory Department
 Issue date 16-Feb-2022
 Revision note
 This SDS supersedes a previous SDS dated January 14, 2021.

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet