



| Item No.       | T   | L   | Inner | W×H×D     | g   |
|----------------|-----|-----|-------|-----------|-----|
| EA-310 T10×100 | T10 | 100 | 10    | 202×65×32 | 163 |
| EA-310 T15×100 | T15 | 100 | 10    | 202×65×32 | 187 |
| EA-310 T20×100 | T20 | 100 | 10    | 202×65×32 | 252 |
| EA-310 T25×100 | T25 | 100 | 10    | 202×65×32 | 329 |
| EA-310 T30×100 | T30 | 100 | 10    | 202×65×32 | 392 |

Tool Type: Torx®

Measurement Type: Torx®

Additional Information: 6.35 mm SHANK

Additional Information: 9 mm & 13mm groove

Additional Information: Torsion processing