



Item No.	H	L1	L2	L3	Inner	W×H×D	g
ST-3/32	3/32"	80	25	190	10	205x95x70	1,078
ST-1/8	1/8"	80	25	190	10	205x95x70	1,107
ST-5/32	5/32"	100	35	200	10	225x110x80	1,203
ST-3/16	3/16"	120	50	250	10	290x135x90	2,175
ST-1/4	1/4"	160	50	250	10	325x177x67	3,564
ST-5/16	5/16"	180	60	300	10	340x215x97	5,446

Tool Type: Straight Type

Handle Type: T-Handle

Measurement Type: Inch

Additional Information: T-Handle Standard Length

Additional Information: Steel Handle