


Item No.	Pcs.	H								Inner	W×H×D	g	
TS-9	9	1.5	2	2.5	3	4	5	6	8	10	5	193x114x77	1,395



Item No.	H	L1	L2
T-1.5	1.5	12	52
T-2	2	12	56
T-2.5	2.5	15	60
T-3	3	20	65
T-4	4	25	72
T-5	5	28	80
T-6	6	32	90
T-8	8	36	100
T-10	10	40	112

Tool Type: Taper Head
 Handle Type: L-Key
 Measurement Type: Metric
 Additional Information: L-Key Standard Length