


SMART PROGRAMMABLE PANEL METERS

Fully Field Configurable, 16-Bit Color Touch Screen Display








SPPM-HSG




SPPM-24 and SPPM-24-C








SPPM-28 and SPPM-28-C







SPPM-35 and SPPM-35-C

The Series SPPM Smart Programmable Panel Meters are configurable full-color touch screen displays that can be used in a variety of applications. By using a USB connection, the panel meter can be configured with downloadable software for any computer running Windows® based software. The display features remarkable graphics that can easily be customized to read and/or graph pressure, temperature, burnishing accompany of the pragmeters. humidity, gas concentration, or many other parameters.

- Available with 2.4", 2.8", or 3.5" color touch screen display
 Free downloadable Windows® software allows the unit to be customized to specific applications

APPLICATIONS

- Tank level
- Power monitoring
- Room pressurization condition
 Indoor air quality conditions

SAMPLE PROGRAMMABLE DISPLAY CONFIGURATIONS



SPPM SPECIFICATIONS

SPECIFICATIONS

Inputs: Current: 0-50 mA, scalable (factory set from 4-20 mA); Voltage: 0-40 VDC, scalable (factory set from 0-10 V). **Accuracy:** 0.1%.

Resolution: 0.3 to 9.8 mV (depending

on input range). **Power Supply:** 4-30 VDC max or via

Current Consumption: 190 mA max. Display: 2.4", 2.8" or 3.5" TFT full color

Display Resolution: 320 x 240 pixels. **Sampling Rate:** 3 samples/s.

Temperature Limits: 32 to 104°F (0 to

40°C). **Warm Up:** 30 s.

Mounting: Panel mount.

Electrical Connection: Screw terminals, pin connection, or USB.

Computer Requirements: Compatible

with Windows® 7, Windows® 8 and Windows® 10.

Weight: 2.8 oz (79.4 g). Compliance: CE

SPPM-HSG SPECIFICATIONS Service: Indoor or outdoor.

Material: Painted aluminum or glass. Enclosure Rating: NEMA 4X (IP66).

A-SPPM-TC SPECIFICATIONS

Probe Measurement Range:
K-type: -328 to 2462°F (-200 to 1350°C);
J-type: -328 to 274°F (-200 to 1190°C);
T-type: -328 to 734°F (-200 to 390°C).
Temperature Limits: 14 to 104°F (-10

Resolution: 1.0°F (0.5°C).
Power Requirements: Powered by USB port through SPPM panel meter. Accuracy: ±2.0°F (±1.0°C). Weight: 0.9 oz (25.5 g).

Compliance: CE.

MODEL CHART		
Model	Display	Input
SPPM-24 SPPM-28 SPPM-35 SPPM-24-C SPPM-28-C SPPM-35-C	2.4" 2.8" 3.5" 2.4" 2.8" 3.5"	Voltage Voltage Voltage Current Current Current

ACCESSORIES		
Model	Description	
	Thermocouple input board Mini USB to full USB cable 2.4" display housing 2.8" display housing	
Note: Additional configurations available		

Windows® is a registered trademark of Microsoft Corporation