



Item No.	H	L1	L2	Φ	Inner	W×H×D	g
BD-1.5	1.5	65	69	18	20	172×99×59	425
BD-2	2	70	69	18	20	172×99×59	448
BD-2.5	2.5	75	84	22	20	196×114×64	715
BD-3	3	80	84	22	20	196×114×64	767
BD-4	4	90	99	26	10	232×136×38	648
BD-5	5	100	99	26	10	232×136×38	745
BD-6	6	110	122	32	10	299×157×56	1,277

Tool Type: Ball Point

Handle Type: SCREWDRIVER

Measurement Type: Metric

Additional Information: Plastic Handle