


| Item No. | Pcs. | H | Inner | W×H×D | g |
|----------|------|-------------------|-------|------------|-------|
| TTS-7 | 7 | 1.5 2 2.5 3 4 5 6 | 10 | 256×160×53 | 1,437 |



| Item No. | H | L1 | L2 |
|----------|-----|----|-----|
| TT-1.5 | 1.5 | 4 | 79 |
| TT-2 | 2 | 5 | 95 |
| TT-2.5 | 2.5 | 6 | 110 |
| TT-3 | 3 | 8 | 126 |
| TT-4 | 4 | 9 | 142 |
| TT-5 | 5 | 11 | 160 |
| TT-6 | 6 | 13 | 180 |

Tool Type: Taper Head
 Handle Type: L-Key
 Measurement Type: Metric
 Additional Information: L-Key Extra Long Length
 Additional Information: L1 Short Arm