

LEVER BODY

Die-cast zinc alloy, epoxy resin coating, orange, red, grey, black colour, matte finish.

STANDARD EXECUTIONS

- **ERM-A:** black-oxide steel clamping element with threaded hole and retaining screw. Steel return spring.
- **ERM-SST:** AISI 303 stainless steel clamping element with threaded hole and retaining screw. AISI 301 stainless steel return spring.
- **ERM-p:** black-oxide steel clamping element with threaded stud and retaining screw. Steel return spring.
- **ERM-SST-p:** AISI 303 stainless steel clamping element with threaded stud and retaining screw. AISI 301 stainless steel return spring.

FEATURES AND APPLICATIONS

Particularly suitable when the lever turning angle is limited owing to lack of space.

SPECIAL EXECUTIONS ON REQUEST

- Lever body in different colours.
- Chrome-plated lever.
- Clamping element with plain hole.


INSTRUCTIONS OF USE

For clamping, lift the lever to disengage the clamping device teeth and bring it back to start position. By releasing the lever, the return spring automatically engages the teeth.

If the lever cannot make a 360° rotation, the clamping element can be easily screwed by means of the hexagon socket front head screw (after having disengaged the lever).



ERGOSTYLE® ELESa Original design



* Complete with colour index of the lever body, example: 90240003-C2 ERM.44-10-32-C2

- C2 RAL2004
- C6 RAL3000
- C8 RAL9006
- C9 RAL9005

INCH

ERM-A

Code	Description	R	d	L	D	H	H1	h	h1	h2	h3	d1	l1	Teeth no.	△
90240003*	ERM.44-10-32*	1.73	10-32	2.05	0.57	1.18	1.3	0.31	0.96	0.14	0.81	0.39	0.43	18	0.04
90240004*	ERM.44-1/4-20*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.31	0.96	0.14	0.81	0.39	0.43	18	0.04
90240014*	ERM.63-1/4-20*	2.48	1/4-20	2.89	0.71	1.5	1.61	0.39	1.22	0.14	1.06	0.53	0.53	24	0.09
90240015*	ERM.63-5/16-18*	2.48	5/16-18	2.89	0.71	1.5	1.61	0.39	1.22	0.14	1.06	0.53	0.53	24	0.08
90240025*	ERM.78-5/16-18*	3.07	5/16-18	3.56	0.85	1.81	1.97	0.55	1.42	0.14	1.36	0.63	0.63	26	0.15
90240026*	ERM.78-3/8-16*	3.07	3/8-16	3.56	0.85	1.81	1.97	0.55	1.42	0.14	1.36	0.63	0.63	26	0.13
90240037*	ERM.95-3/8-16*	3.74	3/8-16	4.29	0.98	2.2	2.4	0.67	1.69	0.2	1.65	0.77	0.71	28	0.23
90240038*	ERM.95-1/2-13*	3.74	1/2-13	4.29	0.98	2.2	2.4	0.67	1.69	0.2	1.65	0.77	0.71	28	0.21


ERM-SST

Code	Description	R	d	L	D	H	H1	h	h1	h2	h3	d1	l1	Teeth no.	△
90241003*	ERM.44-SST-10-32*	1.73	10-32	2.05	0.57	1.18	1.3	0.31	0.96	0.14	0.81	0.39	0.43	18	0.04
90241004*	ERM.44-SST-1/4-20*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.31	0.96	0.14	0.81	0.39	0.43	18	0.03
90241014*	ERM.63-SST-1/4-20*	2.48	1/4-20	2.89	0.71	1.5	1.61	0.39	1.22	0.14	1.06	0.53	0.53	24	0.08
90241015*	ERM.63-SST-5/16-18*	2.48	5/16-18	2.89	0.71	1.5	1.61	0.39	1.22	0.14	1.06	0.53	0.53	24	0.07
90241025*	ERM.78-SST-5/16-18*	3.07	5/16-18	3.56	0.85	1.81	1.97	0.55	1.42	0.14	1.36	0.63	0.63	26	0.13
90241026*	ERM.78-SST-3/8-16*	3.07	3/8-16	3.56	0.85	1.81	1.97	0.55	1.42	0.14	1.36	0.63	0.63	26	0.12
90241036*	ERM.95-SST-3/8-16*	3.74	3/8-16	4.29	0.98	2.2	2.4	0.67	1.69	0.2	1.65	0.77	0.71	28	0.2
90241038*	ERM.95-SST-1/2-13*	3.74	1/2-13	4.29	0.98	2.2	2.4	0.67	1.69	0.2	1.65	0.77	0.71	28	0.19

INOX
STAINLESS
STEEL

INCH





* Complete with colour index of the lever body, example: 90240133-C2 ERM.44-10-32-047-C2


C2 RAL2004 **C6** RAL3000 **C8** RAL9006 **C9** RAL9005

INCH



ERM-p

Code	Description	R	d	L	D	H	H1	h1	h2	h3	d1	l	l1	Teeth no.	△
90240133.*	ERM.44-10-32-047.*	1.73	10-32	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	0.47	0.43	18	0.04
90240135.*	ERM.44-10-32-063.*	1.73	10-32	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	0.63	0.43	18	0.04
90240137.*	ERM.44-10-32-079.*	1.73	10-32	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	0.79	0.43	18	0.04
90240139.*	ERM.44-10-32-098.*	1.73	10-32	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	0.98	0.43	18	0.04
90240141.*	ERM.44-10-32-126.*	1.73	10-32	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	1.26	0.43	18	0.05
90240143.*	ERM.44-10-32-157.*	1.73	10-32	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	1.57	0.43	18	0.05
90240153.*	ERM.44-1/4-20-047.*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	0.47	0.43	18	0.04
90240155.*	ERM.44-1/4-20-063.*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	0.63	0.43	18	0.04
90240157.*	ERM.44-1/4-20-079.*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	0.79	0.43	18	0.05
90240159.*	ERM.44-1/4-20-098.*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	0.98	0.43	18	0.05
90240163.*	ERM.44-1/4-20-126.*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	1.26	0.43	18	0.05
90240165.*	ERM.44-1/4-20-157.*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	1.57	0.43	18	0.05
90240167.*	ERM.44-1/4-20-177.*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	1.97	0.43	18	0.06
90240235.*	ERM.63-1/4-20-079.*	2.48	1/4-20	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	0.79	0.53	24	0.12
90240237.*	ERM.63-1/4-20-098.*	2.48	1/4-20	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	0.98	0.53	24	0.13
90240251.*	ERM.63-5/16-18-047.*	2.48	5/16-18	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	0.47	0.53	24	0.09
90240253.*	ERM.63-5/16-18-063.*	2.48	5/16-18	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	0.63	0.53	24	0.09
90240255.*	ERM.63-5/16-18-079.*	2.48	5/16-18	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	0.79	0.53	24	0.09
90240257.*	ERM.63-5/16-18-098.*	2.48	5/16-18	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	0.98	0.53	24	0.09
90240259.*	ERM.63-5/16-18-126.*	2.48	5/16-18	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	1.26	0.53	24	0.1
90240261.*	ERM.63-5/16-18-157.*	2.48	5/16-18	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	1.57	0.53	24	0.1
90240263.*	ERM.63-5/16-18-177.*	2.48	5/16-18	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	1.77	0.53	24	0.1
90240265.*	ERM.63-5/16-18-197.*	2.48	5/16-18	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	1.97	0.53	24	0.11
90240267.*	ERM.63-5/16-18-248.*	2.48	5/16-18	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	2.48	0.53	24	0.11
90240273.*	ERM.63-3/8-16-079.*	2.48	3/8-16	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	0.79	0.53	24	0.09
90240275.*	ERM.63-3/8-16-098.*	2.48	3/8-16	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	0.98	0.53	24	0.09
90240277.*	ERM.63-3/8-16-126.*	2.48	3/8-16	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	1.26	0.53	24	0.1
90240279.*	ERM.63-3/8-16-157.*	2.48	3/8-16	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	1.57	0.53	24	0.1
90240281.*	ERM.63-3/8-16-177.*	2.48	3/8-16	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	1.77	0.53	24	0.11
90240283.*	ERM.63-3/8-16-197.*	2.48	3/8-16	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	1.97	0.53	24	0.11
90240351.*	ERM.78-3/8-16-063.*	3.07	3/8-16	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	0.63	0.63	26	0.18
90240353.*	ERM.78-3/8-16-079.*	3.07	3/8-16	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	0.79	0.63	26	0.19
90240355.*	ERM.78-3/8-16-098.*	3.07	3/8-16	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	0.98	0.63	26	0.2
90240357.*	ERM.78-3/8-16-126.*	3.07	3/8-16	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	1.26	0.63	26	0.22
90240359.*	ERM.78-3/8-16-157.*	3.07	3/8-16	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	1.57	0.63	26	0.24
90240360.*	ERM.78-3/8-16-177.*	3.07	3/8-16	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	1.77	0.63	26	0.25
90240361.*	ERM.78-3/8-16-197.*	3.07	3/8-16	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	1.97	0.63	26	0.26
90240363.*	ERM.78-3/8-16-248.*	3.07	3/8-16	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	2.48	0.63	26	0.27
90240371.*	ERM.78-1/2-13-126.*	3.07	1/2-13	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	1.26	0.63	26	0.26

Clamping levers



ERM-SST-p



* Complete with colour index of the lever body, example: 90240427-C2 ERM.95-3/8-16-098-C2

C2 RAL2004
 C6 RAL3000
 C8 RAL9006
 C9 RAL9005

ERM-p

INCH

Code	Description	R	d	L	D	H	H1	h1	h2	h3	d1	l	l1	Teeth no.	⚖️
90240427*	ERM.95-3/8-16-098*	3.74	3/8-16	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	0.98	0.71	28	0.25
90240429*	ERM.95-3/8-16-126*	3.74	3/8-16	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	1.26	0.71	28	0.26
90240430*	ERM.95-3/8-16-138*	3.74	3/8-16	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	1.38	0.71	28	0.26
90240431*	ERM.95-3/8-16-157*	3.74	3/8-16	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	1.57	0.71	28	0.27
90240433*	ERM.95-3/8-16-177*	3.74	3/8-16	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	1.77	0.71	28	0.28
90240435*	ERM.95-3/8-16-197*	3.74	3/8-16	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	1.97	0.71	28	0.28
90240437*	ERM.95-3/8-16-248*	3.74	3/8-16	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	2.48	0.71	28	0.29
90240451*	ERM.95-1/2-13-098*	3.74	1/2-13	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	0.98	0.71	28	0.27
90240453*	ERM.95-1/2-13-126*	3.74	1/2-13	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	1.26	0.71	28	0.28
90240454*	ERM.95-1/2-13-138*	3.74	1/2-13	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	1.38	0.71	28	0.28
90240455*	ERM.95-1/2-13-157*	3.74	1/2-13	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	1.57	0.71	28	0.29
90240456*	ERM.95-1/2-13-177*	3.74	1/2-13	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	1.77	0.71	28	0.3
90240457*	ERM.95-1/2-13-197*	3.74	1/2-13	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	1.97	0.71	28	0.31
90240459*	ERM.95-1/2-13-248*	3.74	1/2-13	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	2.48	0.71	28	0.33

ERM-SST-p

INOX STAINLESS STEEL **INCH**

Code	Description	R	d	L	D	H	H1	h1	h2	h3	d1	l	l1	Teeth no.	⚖️
90241155*	ERM.44-SST-1/4-20-063*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	0.63	0.43	18	0.04
90241157*	ERM.44-SST-1/4-20-079*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	0.79	0.43	18	0.05
90241159*	ERM.44-SST-1/4-20-098*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	0.98	0.43	18	0.05
90241161*	ERM.44-SST-1/4-20-126*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	1.26	0.43	18	0.05
90241165*	ERM.44-SST-1/4-20-157*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	1.57	0.43	18	0.05
90241167*	ERM.44-SST-1/4-20-177*	1.73	1/4-20	2.05	0.57	1.18	1.3	0.96	0.14	0.81	0.39	1.77	0.43	18	0.06
90241255*	ERM.63-SST-5/16-18-079*	2.48	5/16-18	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	0.79	0.53	24	0.12
90241259*	ERM.63-SST-5/16-18-126*	2.48	5/16-18	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	1.26	0.53	24	0.13
90241261*	ERM.63-SST-5/16-18-157*	2.48	5/16-18	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	1.57	0.53	24	0.15
90241267*	ERM.63-SST-5/16-18-248*	2.48	5/16-18	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	2.48	0.53	24	0.17
90241273*	ERM.63-SST-3/8-16-079*	2.48	3/8-16	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	0.79	0.53	24	0.1
90241279*	ERM.63-SST-3/8-16-157*	2.48	3/8-16	2.89	0.71	1.5	1.61	1.22	0.14	1.06	0.53	1.57	0.53	24	0.12
90241355*	ERM.78-SST-3/8-16-098*	3.07	3/8-16	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	0.98	0.63	26	0.2
90241357*	ERM.78-SST-3/8-16-126*	3.07	3/8-16	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	1.26	0.63	26	0.22
90241359*	ERM.78-SST-3/8-16-157*	3.07	3/8-16	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	1.57	0.63	26	0.24
90241361*	ERM.78-SST-3/8-16-197*	3.07	3/8-16	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	1.97	0.63	26	0.26
90241363*	ERM.78-SST-3/8-16-248*	3.07	3/8-16	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	2.48	0.63	26	0.27
90241371*	ERM.78-SST-1/2-13-126*	3.07	1/2-13	3.56	0.85	1.81	1.97	1.42	0.14	1.36	0.63	1.26	0.63	26	0.25
90241453*	ERM.95-SST-1/2-13-126*	3.74	1/2-13	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	1.26	0.71	28	0.28
90241457*	ERM.95-SST-1/2-13-197*	3.74	1/2-13	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	1.97	0.71	28	0.31
90241459*	ERM.95-SST-1/2-13-248*	3.74	1/2-13	4.29	0.98	2.2	2.4	1.69	0.2	1.65	0.75	2.48	0.71	28	0.33



Clamping levers