



Item No.	H	L1	L2	Inner	W×H×D	g
T-1.5	1.5	12	52	20	126×65×32	40
T-2	2	12	56	20	126×65×32	60
T-2.5	2.5	15	60	20	126×65×32	85
T-3	3	20	65	20	126×65×32	125
T-4	4	25	72	20	126×65×32	230
T-5	5	28	80	20	126×65×32	380
T-6	6	32	90	20	126×65×32	610
T-8	8	36	100	10	162×68×35	615
T-10	10	40	112	10	162×68×35	1,050
T-12	12	45	125	10	162×111×44	1,695
T-14	14	55	140	10	187×102×59	2,605
T-17	17	60	160	4	187×102×59	1,775
T-19	19 (3/4")	70	175	4	223×99×47	2,440

Tool Type:

Taper Head

Handle Type:

L-Key

Measurement Type:

Metric

Additional Information:

L-Key Standard Length