

**MATERIAL**

Transparent polyamide based (PA-T) technopolymer. Avoid contact with alcohol or detergents containing alcohol.

**STAR-SHAPED CONTRAST SCREEN**

Matte anodised aluminium with red central level point.

**PACKING RING**

NBR synthetic rubber O-ring.

**MAXIMUM CONTINUOUS WORKING TEMPERATURE**

212°F (100°C).

**FEATURES**

The particular shape of the magnifying lens increases and improves visibility even from side positions.

**TECHNICAL DATA**

The tightening torque indicated in the table guarantees an optimal tightness, keeping the packing ring in the correct position.

**NOTE**


For use with fluids containing special additives, please contact ELESA Sales Department.

**ACCESSORIES ON REQUEST**

Brass nut type GH. (see page 1372) for fitting to reservoirs with wall thickness smaller than 0.20 (5 mm).



ELESA Original design



INCH

Code	Description	d1	A	B	D	d	s	△
913691	HFTX.3/4-16 SAE	3/4-16 UNF	0.59	0.31	1.02	0.51	0.87	0.01
913731	HFTX.1 1/16-12 SAE	1 1/16-12 UNF	0.59	0.39	1.38	0.75	1.18	0.02

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- RH

Accessories for hydraulic systems