

I.731+x | Revolving handles

Technopolymer

METRIC

RoHS

PA

+194 °F
-4 °F

MATERIAL

Polyamide based (PA) technopolymer, black colour, matte finish.

STANDARD EXECUTION

Zinc-plated steel shank, hexagon socket at threaded end.


ERGONOMY

The grooves cut into the cylindrical surface allow an effective and ergonomic grip, though necessarily limited to the fingertips, due to the small size of the handle.



ELESA Original design

Conversion Table	
1 mm = 0.039 inch	
L	
mm	inch
20	0.79
23	0.90



METRIC

Code	Description	D	L	d6g	d1	d2	l	s	⚖️
24990	I.731/20+x-M4	13.5	20	M4	11	11	8	2	6
24991	I.731/20+x-M5	13.5	20	M5	11	11	10	2.5	9
24995	I.731/23+x-M5	16	23	M5	12.5	13	10	2.5	11

Fixed & revolving handles