

ERS. Safety adjustable handles

Push action, technopolymer

INCH

RoHS

PA

+266 °F
-22 °F

LEVER BODY

Glass-fibre reinforced polyamide based (PA) technopolymer, grey-black, matte finish. Red writing "PUSH" tampoprinted on the lever body (avoid contact with solvents, alcohol or detergents containing alcohol).

STANDARD EXECUTIONS

Glass-fibre reinforced technopolymer, black colour, with knurling on the protruding part to make initial tightening easier. Black-oxide steel retaining screw, AISI 302 stainless steel return spring.

STRESS RESISTANCE

See ERX. on page 264.

INSTRUCTIONS OF USE

For clamping push the lever to engage the clamping device toothing and turn it. By releasing the lever, the return spring automatically disengages the toothing and lever return to its rest position.


In case of accidental shocks, the lever turns freely without affecting the clamping action.

OTHER EXECUTIONS ON REQUEST

Standard metric holes.



ERGOSTYLE® ELESA Original design



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15

INCH

Code	Description	R	d	L	D	H	h	h1	h2	h3	d1	l1	Teeth no.	⚖️
90236904	ERS.44 A-1/4-20	1.73	1/4-20	2.05	0.61	1.42	0.39	1.14	0.35	1.1	0.47	0.43	18	0.03
90236914	ERS.63 A-5/16-18	2.48	5/16-18	2.89	0.75	1.89	0.51	1.46	0.47	1.46	0.59	0.53	20	0.06

Clamping levers