

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10**
- 11
- 12
- 13
- 14
- 15

## MATERIAL


Glass-fibre reinforced polyamide based (PA) technopolymer, black colour, matte finish.

## STANDARD EXECUTIONS

- **TSLA-A**: zinc-plated steel M10 screw, nut and washer.
- **TSLA-SST**: AISI 304 stainless steel M10 screw, nut and washer.

## FEATURES

Maximum tightening torque for screw assembly 35 Nm.



Conversion Table	
1 mm = 0,039 inch	
d	
mm	inch
48.3	1.90

## TSLA-A

METRIC

Code	Description	d Tube (mm)	d Tube (BSP/GAS)	⚖
419648	TSLA-48-A	48.3	1"1/2	320

## TSLA-SST

INOX STAINLESS STEEL METRIC

Code	Description	d Tube (mm)	d Tube (BSP/GAS)	⚖
419649	TSLA-48-SST	48.3	1"1/2	320