

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- RH
-

MATERIAL

High-resilience polypropylene based (PP) technopolymer, coated with "soft-touch" thermoplastic elastomer (TPE) chemically bonded, hardness 70 Shore A, black colour, matte finish.
Produced from FDA compliant raw material (FDA CFR.21 and EU 10/2011).

STANDARD EXECUTIONS

Zinc-plated steel shank, hexagon socket at threaded end.
- **IEL+x:** without ring.
- **IEL+x-A:** with matte anodised aluminium ring (ELESA original design).

FEATURES AND APPLICATIONS


The coating, with "soft-touch" elastomer, improves the grip even in the presence of oils, greases and sweat from the hand. For this reason it is suitable for fitness machines, tools and machines for gardening and goods transport, high-precision instruments and disability aids.

SPECIAL EXECUTIONS ON REQUEST

IEL+x-H: with magnifying lens for labels with marks and symbols.



ELESA Original design



| Conversion Table | |
|-------------------|------|
| 1 mm = 0.039 inch | |
| mm | inch |
| 47 | 1.85 |
| 65 | 2.56 |

METRIC

| Code | Description | D | L | d6g | d1 | l | s | ⚖ |
|-------|---------------------|----|----|-----|----|----|---|-----|
| 26651 | IEL.47+x-M10 SOFT | 45 | 47 | M10 | 28 | 17 | 5 | 80 |
| 26679 | IEL.65+x-M8 SOFT | 45 | 65 | M8 | 23 | 17 | 5 | 102 |
| 26681 | IEL.65+x-M10 SOFT | 45 | 65 | M10 | 23 | 17 | 5 | 99 |
| 26691 | IEL.65+x-M10-A SOFT | 45 | 65 | M10 | 23 | 17 | 5 | 99 |